



YA34L, 350 kcmil G,H,I,K,M, 373 DLO, CU, 2-Hole, Std, Narrow

By Burndy
Catalog # [YA34L2NT38FX](#)

350 kcmil G,H,I,K,M,373 DLO, CU, 2 Hole, 3/8 Stud, 1 IN Spacing, Standard Barrel, Inspection Window, Narrow Tongue

Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- 2-Hole design prevents rotation

Application

Wire Termination

Specifications

| | |
|------------------------------------|----------------------|
| Buy American Compliant | Contact Manufacturer |
| Certification - cULus | No |
| EU RoHS Indicator | Yes |
| Certification - UL Recognized | No |
| Industry Standard(s) | UL 486A-486B |
| Certification - ETL | No |
| Standards - RoHS Compliance Status | CM |
| Certification - CSA Approved | Yes |
| UL Listed | Yes |

Conductor

| | |
|--------------------------------------|-----------|
| Conductor - Material | COPPER |
| Wire Size | 350 KCMIL |
| Conductor - Copper Str Size | 350 KCMIL |
| Conductor - Copper Flex I Size Range | 350 kcmil |
| Conductor - Copper Flex K Size | 350 KCMIL |
| Conductor - Copper Flex K Size Range | 350 kcmil |
| Conductor - Copper Flex M Size | 350 KCMIL |
| Conductor - Copper Flex M Size Range | 350 kcmil |
| Conductor - Copper DLO Size | 373 KCMIL |
| Conductor - Copper DLO Size Range | 373 kcmil |
| Conductor - Copper Flex G Size | 350 KCMIL |
| Conductor - Copper Flex G Size Range | 350 kcmil |

| | |
|--------------------------------------|-----------|
| Conductor - Copper Flex H Size | 350 KCMIL |
| Conductor Size | 350 KCMIL |
| Conductor - Copper Str Size Range | 350 kcmil |
| Conductor - Copper Flex H Size Range | 350 kcmil |
| Conductor Type | FLEX |
| Conductor - Copper Flex I Size | 350 KCMIL |

Configuration

| | |
|--------------------------------------|-----------------|
| Physical Attribute - Number of Holes | 2 |
| Connector Type | STANDARD BARREL |

Current

| | |
|-------------------|-------|
| Voltage - Maximum | 35000 |
| Voltage Rating | 35 kV |

Dimensions

| | |
|-----------------------------------|-----------|
| Package Length | 0.000 in |
| Package Width | 0.000 in |
| Package Weight | 0.000 lb. |
| Dimension - Outside Diameter inch | 1.06 in |
| Dimension - L Length Overall mm | 99 mm |
| Dimension - Pad Width inch | 0.96 in |
| Package Height | 0.000 in |
| Dimension - Hole Size fraction | 3/8 |
| Dimension - Hole Size inch | 0.41 |
| Dimension - Hole Size mm | 10.4 mm |
| Dimension - Strip Length inch | 1-5/16 |
| Dimension - Stud Size fraction | 3/8 |
| Dimension - Stud Size inch | 3/8 |
| Dimension - B Length fraction | 1-1/4 in |
| Dimension - B Length inch | 1.27 in |
| Dimension - Z inch | 0.42 in |
| Physical Attribute - Tongue Angle | Straight |
| Dimension - Bolt Hole Size inch | 0.39 in |
| Dimension - Bolt Size fraction | 3/8 |
| Dimension - Bolt Size inch | 0.38 |
| Dimension - Length Overall inch | 3.88 in |
| Dimension - D inch | 1.83 in |
| Dimension - N inch | 0.41 in |

General

| | |
|----------------------------------|------------------------------|
| Die Index | 19 |
| Trade Name | HYLUG™ |
| Sub Brand | HYLUG |
| Color Code | Blue |
| Physical Attribute - Tongue Type | Standard |
| Plated | Y |
| Feature - Barrel Type | Standard |
| Feature - Barrel Style | Chamfered |
| Type | YA-L-2TC-FX, Standard Barrel |
| UPC 14 Digit GTIN | 00781810020371 |
| Material | COPPER |

| | |
|--------------|----------------------|
| Plating Type | Tin - Electro Plated |
| Finish Type | Tin-Plated |
| UPC | 781810020371 |

Logistics

| | |
|-----------------------|------|
| Minimum Pack Quantity | 1 |
| Carton Quantity | 50 |
| Pallet Quantity | 6000 |

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)
- [Installation Manual \[English\]](#)



© 2026 Hubbell Incorporated. All rights reserved
BRDY-YA34L2NT38FX-SPEC-EN | REV 4/2026