

This information is given as an indication. In the continual goal to improve our products, we reserve the right to make any modifications judged necessary



RADIAL[®]
Microwave components

TECHNICAL DATA SHEET

R412500124

1 W

DC- 3 GHz


TNC

COAXIAL ATTENUATOR

issue
13.Nov.01

Page
1 / 1

DRAWING



General tolerances: +/- 0.5 mm

R F CHARACTERISTICS

FREQUENCY RANGE : DC - 3 GHz
IMPEDANCE : 50 Ohms
ATTENUATION - NOMINAL : 0 dB

FREQUENCY	DC- 2 GHz	2 - 3 GHz
V.S.W.R	<= 1.20	<= 1.30
DEVIATION (dB)	+ 0.3 / 0	+ 0.5 / 0

PEAK POWER at 25°C (1μs,1%) : 100 W
AVERAGE POWER at 25°C : 1 W


MECHANICAL CHARACTERISTICS

CONNECTORS : TNC male/female per MIL-C 39012
WEIGHT : < 17 g

ENVIRONMENTAL CHARACTERISTICS

OPERATING TEMPERATURE RANGE (°C) : -40 , +85
STORAGE TEMPERATURE RANGE (°C) : -40 , +85

Power derating
Versus temperature



CREATION

N° :
PEN/EP:CAT
Name:AF
Date:13.Nov.01
APP.:FG

ISSUE

REVISIONS

NAME

APPR.

RADIAL[®]

101. rue P. Hoffmann -Z.I Ouest-
93116 ROSNY/BOIS Cedex-FRANCE
Phone:33(1)49353535
Fax :33(1)48546363
Twx RADIA 235220F