

**BeStar Technologies Inc.**

Address: 761 N. 17th Street Unit 4, St. Charles, IL 60174

Tel : 847-261-2850 E-mail : sales@bestartech.com Web : www.bestartech.com

Document Number : 0004-82
Revision : A4
Total Pages : 4
Prepare by : Holmes, Poon
Date : 18 November, 2011

SoniCrest Brand Acoustic Componentswww.jlsonicrest.com

Document Type : Specification
Product Type : Electro-magnetic Sound Generator Component
Part Number : HC12G-1P/002

A3 - Update format and layout by Ting Lok, Ngan on 9 Dec., 2003		
A4 - Updated section 4 by Holmes, Poon on 18 Nov., 2011		

This material is the property of BeStar Technologies Inc.
Unauthorized copying or use of this material is prohibited.

1. Purpose and Scope

This document contains both general requirements, qualification requirements, and those specific electrical, mechanical requirements for this part.

2. Description

Ø12mm electro-magnetic sound generator with silver marking of part number, date code and polarity mark.

3. Application

Telecommunication Equipment, Computers and Peripherals, Portable Equipment, Automobile Electronics, POS System, etc.

4. Component Requirement

4.1 General Requirement

4.1.1.	Operating Temperature Range	: -25°C to +70°C
4.1.2.	Storage Temperature Range	: -30°C to +85°C
4.1.3.	Weight	: Approx. 2g
4.1.4.	Housing Material	: Noryl SE1

4.2 Electrical Requirement

4.2.1.	Rated Voltage	: 1.5V
4.2.2.	Operating Voltage	: 1 ~ 5 V
4.2.3.	Rated Current	: <=30mA
4.2.4.	Coil Resistance	: $16 \pm 2 \Omega$
4.2.5.	Rated Frequency	: 2048Hz
4.2.6.	Sound Pressure Level at 10cm (Applying rated voltage and rated frequency)	: >=85dB




Figure 1. Frequency Response

4.3 Mechanical Requirement

4.3.1.	Layout and Dimension	: See Section 6, Figure 3
--------	----------------------	---------------------------

4.4 Test Setup




Figure 2. Test Setup

Notes : Apply 2.5V_{0-p} from Signal Generator, set 2048Hz from Signal Generator. Measure SPL using a calibrated SPL meter 10cm from the sound port. Sound level meter to be in accordance with IEC651 (1979) Type 1 and/or ANSI S1.4-1983. The meter must be checked on a daily basis using a calibrated acoustic calibrator recommended by the manufacturer. Measurement should be carried out in a free field environment or at least 40cm from any surface.

5. Reliability Test

- 5.1. **Operating Life** : Subject samples to room condition for 96 hours under rated voltage and frequency. Components must be fully stabilized before data is taken, which may require up to a 2 hours soak.
- 5.2. **High Temperature** : Subject samples to +70°C and operate for 96 hours with rated voltage and frequency. Components must be fully stabilized at temperature extremes before data is taken, which may require up to a 2 hours soak.
- 5.3. **Low Temperature** : Subject samples to -25°C and operate for 96 hours with rated voltage and frequency. Components must be fully stabilized at temperature extremes before data is taken, which may require up to a 2 hours soak.
- 5.4. **Temperature Shock** : Each temperature cycle shall consist of 1 hour at -25°C followed by 1 hour at +70°C with 20 seconds maximum transition time between temperature extremes. Test duration is for 32 cycles. Components must be fully stabilized at temperature extremes before data is taken, which may require up to a 2 hours soak.
- 5.5. **Static Humidity** : Precondition at room temperature for 1 hour. Then expose to +40°C with 90 to 95% relative humidity for 96 hours. Finally dry at room ambient for 2 hours before taking final measurement.
- 5.6. **Drop Test** : Drop samples naturally from the height of 1m onto a wooden board six times.

6. Mechanical Layout

Unit : mm
Tolerance : Linear XX.X = ±0.3
 XX.XX = ±0.05
 Angular = ±0.25°
(unless otherwise specified)




Figure 3. HC12G-1P/002 Mechanical Layout