


Scotch® Vinyl Color Coding Electrical Tape 35, 3/4 in x 66 ft, Red, 10 rolls/carton, 100 rolls/Case

Part Number 35-3/4X66FT-RD, 3M ID 700006094, UPC 00054007108108

★★★★★ 5.0 (3)

Details Typical Properties Resources Reviews



The combination of the pressure-sensitive, rubber-resin adhesive and the PVC backing offers excellent electrical and mechanical protection

Flame-retardant and highly resistant to UV rays, abrasion, moisture, alkalis, solvents and many acids

Suitable for use in phase identification, color-coding of motor leads and piping systems and for marking safety areas

[View more details](#)

**Frequently viewed resources**

- [Tech Data Sheet \(PDF, 368KB\)](#)
- [User Instructions \(HTML, 2KB\)](#)
- [View all resources](#)

[View legal disclaimer](#)

*For industrial/occupational use only. Not for consumer sale or use.*

|                                             |          |
|---------------------------------------------|----------|
| Overall Width (Metric)                      | 19 mm    |
| Total Tape Thickness without Liner (Metric) | 0.178 mm |
| Overall Width (Imperial)                    | 0.75 in  |
| Product Color                               | Red      |
| Overall Length (Metric)                     | 201 m    |
| Overall Length (Imperial)                   | 66 ft    |

Details

|                                                                                                                                            |                                                                                                       |                                                                                                                       |
|--------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------|
| The combination of the pressure-sensitive, rubber-resin adhesive and the PVC backing offers excellent electrical and mechanical protection | Flame-retardant and highly resistant to UV rays, abrasion, moisture, alkalis, solvents and many acids | Suitable for use in phase identification, color-coding of motor leads and piping systems and for marking safety areas |
| Made of durable PVC                                                                                                                        | Withstands a temperature range of 14 to 221 °F (-10 to 105 °C)                                        | UL Listed, VDE, CSA Certified and RoHS 2015/863/EU Compliant                                                          |

Scotch® Vinyl Multi-Colored Electrical Tape 35 is a 7 mil thick, premium grade, electrical tape that comes in various colors. This flame retardant tape is suitable for wire and phase identification, color coding of motor leads and piping systems, and for marking safety areas. This tape is 600V rated and withstands a temperature range of 14 to 221 °F (-10 to 105 °C).

Scotch® Vinyl Multi-Colored Electrical Tape 35 provides electrical and mechanical protection with the combination of an aggressive, pressure sensitive, rubber resin adhesive and an elastic PVC backing. This tape is flame retardant and is highly resistant to UV rays, abrasion, moisture, alkalis, acids, solvents and varying weather conditions. It stretches easily and adheres virtually in any shape. Ideal for insulating electrical wires and is compatible with synthetic cable insulations, jackets and splicing compounds. UL Listed, VDE, CSA Certified and RoHS 2011/65/EU Compliant.

Typical properties

| Details                                       |                                                           |
|-----------------------------------------------|-----------------------------------------------------------|
| Adhesive Type                                 | Rubber                                                    |
| Application                                   | Electrical Maintenance                                    |
| Backing (Carrier) Material                    | PVC                                                       |
| Brands                                        | Scotch®                                                   |
| Dielectric Strength                           | 1255 mV                                                   |
| Electrolytic Corrosion Factor                 | 0.9                                                       |
| Elongation at Break                           | 225.0 %                                                   |
| Flame Retardant                               | Yes                                                       |
| Insulation Resistance                         | > 10*6 megohms                                            |
| Maximum Operating Temperature (Celsius)       | 105 °C                                                    |
| Maximum Operating Temperature (Fahrenheit)    | 221 °F                                                    |
| Minimum Operating Temperature (Celsius)       | 0 °C                                                      |
| Minimum Operating Temperature (Fahrenheit)    | 32 °F                                                     |
| Product Color                                 | Red                                                       |
| Rolls per Carton                              | 10                                                        |
| Rolls per Case                                | 100                                                       |
| Shelf Life                                    | 5 Year                                                    |
| Specifications Met                            | CSA Certified, RoHS 2011/65/EU, UL Listed, VDE 0340-TEIL1 |
| Tape Grade                                    | Professional                                              |
| Total Tape Thickness without Liner (Imperial) | 7 mil                                                     |
| Total Tape Thickness without Liner (Metric)   | 0.178 mm                                                  |
| Voltage Rating                                | 600 V                                                     |
| eClass 14 Classification Group                | 27144427                                                  |
| Dimensions and Classifications                |                                                           |
| Overall Length (Imperial)                     | 66 ft                                                     |
| Overall Length (Metric)                       | 201 m                                                     |
| Overall Width (Imperial)                      | 0.75 in                                                   |
| Overall Width (Metric)                        | 19 mm                                                     |

Resources

[Regulatory Data Sheet \(1\)](#) [Data Sheets \(1\)](#) [Article Information Sheet \(1\)](#) [Brochures \(3\)](#) [Catalogs \(1\)](#) [Instructions \(1\)](#) [Product Selection Guides \(2\)](#) [Technical Papers \(1\)](#)

[Scotch® Vinyl Electrical Color Coding Tape 35 \(Blue, Brown, Gray, Green, Orange, Pink, Red, Violet, White, Yellow\)](#)

Regulatory Data Sheet  
Document Number:  
MSDS\_0935221\_US\_EN\_RDS  
(PDF, .0B)

Reviews

### Review Highlights

Pros

Satisfaction 2 reviews  
"I bought this to tape my marching snare sticks, and I love the strength. I am buying a case to provide for the ENTIRE drumline so we can get all of our sticks taped."

Cons

There are not enough reviews to display Cons at this time.

[SEE ALL REVIEWS](#)

### Reviews

Rating Snapshot

Select a row below to filter reviews.

|         |   |
|---------|---|
| 5 stars | 3 |
| 4 stars | 0 |
| 3 stars | 0 |
| 2 stars | 0 |
| 1 star  | 0 |

Overall Rating

5.0 ★★★★★

3 Reviews

Review this Product

☆☆☆☆☆

Adding a review will require a valid email for verification

Average Customer Ratings

|                    |                  |
|--------------------|------------------|
| Quality of Product | Value of Product |
| ★★★★★ 5.0          | ★★★★ 4.7         |

Customer Images

Filter Reviews

Rating

1 - 3 of 3 Reviews

Sort by: Most Recent

★★★★★

Good For Drum Corps

Agamnon

4 years ago

I bought this to tape my marching snare sticks, and I love the strength. I am buying a case to provide for the ENTIRE drumline so we can get all of our sticks taped. I love the quality, it doesnt make the sticks too bulky, and doesnt add too much weight. 10/10 WILL buy again.

Yes, I recommend this product.

Originally posted on [Scotch® Vinyl Color Coding Electrical Tape 35](#)

Helpful? (5) (1) Report

★★★★★

Superior color coded vinyl electrical tape

TNTMAC

5 years ago

I tried a white electrical tape that was made in China. It didn't stick well and became brittle. (see first 2 pictures) I bought 5 rolls of color coded 3M Scotch Vinyl Electrical Tape to replace the old tape. The Scotch sticks securely to plastic and is superior. (see last picture) Scotch is the only electrical tape I will purchase!

Yes, I recommend this product.

Originally posted on [Scotch® Vinyl Color Coding Electrical Tape 35](#)

Helpful? (3) (1) Report

★★★★★

Best tape

Randy3030

5 years ago

I've been using your tapes for decades. I don't even consider other brands anymore.

Yes, I recommend this product.

Originally posted on [Scotch® Vinyl Color Coding Electrical Tape 35](#)

Helpful? (4) (0) Report

Legal disclaimer

Manufacturing Origin: USA

The designation that a product is Manufactured in the USA means the product undergoes substantial transformation in one of our U.S. Manufacturing plants. Some products contain imported components.

Note: 3M products offered on a government contract that require country of origin representation must be certified by 3M Trade Compliance. Contact customer service at 800-245-3573 to request a certificate.

For industrial/occupational use only. Not for consumer sale or use.

3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and other limitations, and the user must take any action required under any recall, field action, or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, death, or property damage. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert.

OUR COMPANY

About 3M  
3M Careers  
Investor Relations  
Partners & Suppliers  
Sustainability / ESG  
Equity and Community  
Ethics & Compliance

NEWS

News Center  
Press Releases

REGULATORY

SDS, RDS, More Regulatory & Compliance Information  
Transport Information Search  
CPSIA Certification Search  
Lithium Battery UN 38.3 Test Summary Search  
Transparency in Supply Chains and Modern Slavery Disclosures  
US Ingredient Communication  
Product Recalls

HELP

Help Center  
Site Map  
Where to Buy

FOLLOW US

Twitter LinkedIn YouTube Facebook Instagram

Legal | Privacy | HIPAA Privacy | DMCA | Accessibility Statement | Your Privacy Choices

3M

© 3M 2024. All Rights Reserved.

The brands listed above are trademarks of 3M.