





APPROVED: _____
 DATE: _____ TITLE: _____

| Rev | AWO # | Description | Date | Appr |
|-----|-------|----------------|---------|-------|
| - | | RELEASED | 7/24/12 | |
| A | | UPDATE DRAWING | 7/1/15 | AY/RT |
| B | | UPDATE DIM. | 6/14/16 | AY |

D



C



B

SECTION A-A

Aseemble state

SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-0

Insulator color: Nature

Contact: Brass

Plating:

Tin over Nickel underplate overall

Electrical:

Rated Voltage: 250V AC/DC

Rated Current: 3A AC/DC

Contact Resistance: 20 mohms max.

Insulation resistance: 1,000 Mohms min.

Withstand voltage: 1000V AC for 1 minute.

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant

Positions: 2 thru 20

A = .098 [2.50] x No. of Spaces

B = .098 [2.50] x No. of Spaces + .197 [5.00]

C = .098 [2.50] x No. of Spaces + .138 [3.50]



UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE INCHES [MM]
 TOLERANCES: EXCEPT AS NOTED
 INCHES HOLES
 .X ± .10 ØX ± .10
 .XX ± .020 ØXX ± .015
 .XXX ± .015 ØXXX ± .010

APPROVALS

DATE

DRAWN

AY

CHECKED

LW

APPROVED

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE: WIRE TO BOARD PITCH: 2.50MM

WAFER STRAIGHT TYPE W/ KINK & PEG

| SIZE | PART NO. | REV. |
|------|----------------|--------------|
| X | 25SH-B-XX-TS-P | B |
| | REF: S00124T | SCALE: NTS |
| | | SHEET 1 OF 1 |