

Ha-VIS RJ45 Jack HIFF Set AWG 26/27

[Spotted an error?](#) |  [Print page](#) | [Back](#)



Image is for illustration purposes only.
Please refer to product description:

Tools

- [Features](#)
- [Dimensions and weight](#)
- [Ethernet Ports \(Twisted Pair\)](#)
- [Connection data](#)
- [Norms and specifications](#)

Part number:	20 82 001 0002
Description:	Ha-VIS RJ45 Jack HIFF Set AWG 26/27
Type sheet:	 PDF
Data sheet:	 PDF

Features

Connector:	RJ45 acc. to IEC 60 603-7
Gender:	female
Mechanical working life - mating cycles:	ca. 750
RoHS conformity:	Yes
Serie Data connectors:	HIFF
Transmission characteristics:	Category 6a / Class EA up to 500 MHz, according to ISO/IEC 11 801:2002 and EN 50 173-1
Termination method:	IDC Insulation displacement terminal
Number of contacts:	8
Operating temperature, min.:	-40 °C
Operating temperature, max.:	70 °C

Top

Connection data

Wire diameter, min.:	0.7 mm
Wire diameter, max.:	1.15 mm
Cable diameter, min.:	5 mm
Cable diameter, max.:	9 mm
Wire gauge mm² min.:	0.102 mm2
Wire gauge, max.:	0.128 mm2
Wire gauge AWG, min.:	AWG 27
Wire gauge AWG, max.:	AWG 26

Top

Dimensions and weight

Net Weight:	24.75 g
-------------	---------

Top

Norms and specifications

Degree of protection acc. to DIN EN 60 529:	IP20
---	------

Top

Ethernet Ports (Twisted Pair)

Data rate copper:	10/100/1000 Mbit/s, 10 Gbit/s
-------------------	-------------------------------

Top

[Login to MyHARTING](#)
for pricing and stock check

Quantity:

Shopping cart

Email inquiry

Catalogue

HARTING Device Connectivity -
Page 28



[Browse](#)

 [Download](#)

Downloads

Title	Download
Type sheet	 PDF
Data sheet	 PDF
Type sheet	 DXF
Type sheet	 CGM
CAD data 3D	 STEP
CAD data 3D	 JT
HARTING Device Connectivity - Page 28	 PDF

Tools

Image	Part number	Description	Tech. info	Quantity
	20 82 000 9901	HA-VIS PRELINK ASSEMBLY TOOL		1 Shopping cart

Recently viewed - [Delete](#)



Ha-VIS RJ45 Jack HIFF Set AWG 26/27

[Show product details](#)

Recently searched

No searches have been done yet.

