




APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO#	Description	Date	Appr
-		RELEASED	4/21/10	



RECOMMENDED PCB LAYOUT



D C B A

C B A

C B A

SPECIFICATIONS:

Material:
Insulator: Nylon 66, rated UL 94V-2
Insulator color: Natural
Contacts: Brass

Plating:
Tin over nickel underplate

Electrical:
Operation voltage: 250V AC,DC
Current rating: 5A AC,DC
Contact resistance: 10 mohms max
Insulation resistance: 1000 Mohms min
Dielectric withstand voltage: 800V AC/minute

Temperature rating:
Operating temperature: -25°C to +85°C
Environmental:
Lead Free, RoHS compliant

ROHS
COMPLIANT

ADAM TECH

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
 X $\pm .10$ $\varnothing X$ $\pm .10$
 XX $\pm .020$ $\varnothing XX$ $\pm .015$
 XXX $\pm .015$ $\varnothing XXX$ $\pm .010$

TITLE

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

A B C D

APPROVALS	DATE	SIZE		PART NO.		REV.
DRAWN	DY	4/21/10	.200 [5.08]	DDS-02	-	
APPROVED			X	REF: S0099T	SCALE: NTS	SHEET 1 OF 1
CHECKED						