

Features

- Trench Power LV MOSFET Technology
- High Density Cell Design for Low $R_{DS(ON)}$
- High Speed Switching
- Moisture Sensitivity Level 1
- Epoxy Meets UL 94 V-0 Flammability Rating
- Halogen Free. "Green" Device^(Note 1)
- Lead Free Finish/RoHS Compliant ("P" Suffix Designates RoHS Compliant. See Ordering Information)

Maximum Ratings


- Operating Junction Temperature Range : -55°C to +150°C
- Storage Temperature Range: -55°C to +150°C
- Thermal Resistance: 60°C/W Junction to Ambient^(Note 2)

Parameter		Symbol	Rating	Unit
Drain-Source Voltage		V _{DS}	30	V
Gate-Source Voltage		V _{GS}	±20	V
Continuous Drain Current	T _A =25°C	I _D	18	A
	T _A =70°C		14.5	
Pulsed Drain Current ^(Note 3)		I _{DM}	65	A
Total Power Dissipation ^(Note 4)		P _D	2.1	W
Single Pulsed Avalanche Energy ^(Note 5)		E _{AS}	121	mJ

Note:


1. Halogen free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
2. The value of $R_{\theta JA}$ is measured with the device mounted on 1in² FR-4 board with 2oz. Copper, in a still air environment with $T_A=25^\circ\text{C}$. The Power dissipation P_{DSM} is based on $R_{\theta JA} \leq 10\text{s}$ and the maximum allowed junction temperature of 150°C. The value in any given application depends on the user's specific board design.
3. Repetitive rating; pulse width limited by max. junction temperature.
4. P_D is based on max. junction temperature, using junction-Ambient thermal resistance.
5. $T_J=25^\circ\text{C}$, $V_{DD}=25\text{V}$, $V_{GS}=10\text{V}$, $L=0.5\text{mH}$.

Internal Structure and Marking Code




N-CHANNEL MOSFET

SOP-8



DIM	INCHES		MM		NOTE
	MIN	MAX	MIN	MAX	
A	0.053	0.069	1.35	1.75	
B	0.004	0.010	0.10	0.25	
C	0.053	0.061	1.35	1.55	
D	0.013	0.020	0.33	0.51	
E	0.007	0.010	0.17	0.25	
F	0.185	0.200	4.70	5.10	
G	0.050		1.270		TYP.
H	0.228	0.244	5.80	6.20	
J	0.150	0.157	3.80	4.00	
K	0.016	0.050	0.40	1.27	
θ	0°	8°	0°	8°	

Suggested Solder Pad Layout



Electrical Characteristics @ 25°C (Unless Otherwise Specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Static Characteristics						
Drain-Source Breakdown Voltage	V _{(BR)DSS}	V _{GS} =0V, I _D =250μA	30			V
Gate-Source Leakage Current	I _{GSS}	V _{DS} =0V, V _{GS} =±20V			±100	nA
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} =30V, V _{GS} =0V			1	μA
Gate-Threshold Voltage	V _{GS(th)}	V _{DS} =V _{GS} , I _D =250μA	1	1.3	2.5	V
Drain-Source On-Resistance	R _{DS(on)}	V _{GS} =10V, I _D =18A		4.8	7	mΩ
		V _{GS} =4.5V, I _D =10A		7	10	
Gate Resistance	R _g	F=1MHZ, Open drain		2.3		Ω
Diode Characteristics						
Continuous Body Diode Current	I _S				18	A
Diode Forward Voltage	V _{SD}	V _{GS} =0V, I _S =12A		0.85	1.2	V
Reverse Recovery Time	t _{rr}	I _S =12A,di/dt=100A/μs		23		ns
Reverse Recovery Charge	Q _{rr}			10		nC
Dynamic Characteristics						
Input Capacitance	C _{iss}	V _{DS} =15V,V _{GS} =0V,f=1MHz		1765		pF
Output Capacitance	C _{oss}			298		
Reverse Transfer Capacitance	C _{rss}			266		
Total Gate Charge	Q _g	V _{DS} =15V,V _{GS} =10V,I _D =12A		38		nC
Gate-Source Charge	Q _{gs}			4		
Gate-Drain Charge	Q _{gd}			10		
Turn-On Delay Time	t _{d(on)}	V _{GS} =10V,V _{DD} =20V, I _D =4A, R _{GEN} =3Ω		7.8		ns
Turn-On Rise Time	t _r			10		
Turn-Off Delay Time	t _{d(off)}			35		
Turn-Off Fall Time	t _f			20		

Curve Characteristics

Fig. 1 - Typical Output Characteristics




Fig. 2 - Transfer Characteristics




Fig. 3 - $R_{DS(ON)}-V_{GS}$




Fig. 4 - $R_{DS(ON)}-I_D$




Fig. 5 - Capacitance Characteristics





Fig. 6 - Gate Charge



Curve Characteristics

Fig. 7 - Normalized Threshold Voltage




Fig. 8 - Normalized On Resistance Characteristics




Fig. 9 - $I_S - V_{SD}$




Fig. 10 - Drain Current





Fig.11 - PD Dissipation



Curve Characteristics

Fig. 12 - Safe Operation Area





Fig. 13 - Normalized Transient Thermal Impedance



Ordering Information

Device	Packing
Part Number-TP	Tape&Reel: 4Kpcs/Reel

IMPORTANT NOTICE

Micro Commercial Components Corp. reserves the right to make changes without further notice to any product herein to make corrections, modifications , enhancements , improvements , or other changes . **Micro Commercial Components Corp** . does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights ,nor the rights of others . The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp** . and all the companies whose products are represented on our website, harmless against all damages. **Micro Commercial Components Corp.** products are sold subject to the general terms and conditions of commercial sale, as published at <https://www.mccsemi.com/Home/TermsAndConditions>.

LIFE SUPPORT

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

CUSTOMER AWARENESS

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. **MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources.** MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.