

Johanson Part Number SCDR302W472K4GV001E

Johanson Part Number:
SCDR302W472K4GV001E

Johanson Company: JDI

Legacy P/N:
302S43W472KV3E-****-SC

Size for Capacitors (EIA):
1812

Description: Capacitors
Safety Caps, 1812, X7R,
250.0V, 4700.000pF±10%,
Ni/Sn (RoHS), 7" Reel
Embossed Tape

Specification Number:
UL60950,EN/UL/IEC60384-
14

Life Cycle Stage: Active

NCNR: No

AEC Q200 Qualified: No

Thickness (Max): 0.115

Schedule B: 8532

Thickness (Min): None

ITAR: No

End Band(Min): 0.01

ECCN: EAR99

End Band (max): 0.040

RoHS Compliance: Yes,
RoHS 10/10

Standard Item: Yes

REACH: Yes

Lead Time Typical (Weeks)*:
10

Country of Origin: None

Length (Min): 0.165

Product Family: Capacitors

Length (Max): 0.185

Product Subfamily:
Capacitors Safety Caps

Width (Min):0.115

Capacitance Value: 4700.000

Width (Max): 0.135

Cap Unit of Meas: pF

Part Weight (mg): 150.00

Tolerance: ±10%

Packaged Width (lb) Arm:
None

Voltage: 250.0

Packaging: 7" Reel
Embossed Tape

Dielectric Temp Coefficient:
X7R

Packaging Qty: 500

Termination: 68

Operating Temp Range:
-55 °C to +125 °C

Marking: Required Safety
Mark

Storage Temp Range
(Packaged): -65 °C to
+125 °C

Product Release Date: Jan.
3, 2006, 8 a.m.

Storage Temp Range (None
Operating): +5 °C to +40 °C
with RH 20% to 70%

*This can vary significantly so it is important to obtain a quotation with lead time for production planning purposes.

Web Page Link: <https://www.johansondielectrics.com/ac-safety-capacitors>

Printed from: www.johansontechnology.com/search/pn-detail/?s=SCDR302W472K4GV001E