

**Part Number :** [513470600](#)

**Product Description :** 3.30mm Pitch Wire-to-Wire Receptacle Housing, Positive Lock, Dual Row, 6 Circuits

**Series Number :** 51347

**Status :** Obsolete

**Product Category :** Connector Housings

---

## Documents and Resources

### Drawings

[513470600 sd.pdf](#)

[SPK-51347-001-001.pdf](#)

[SPK-51347-001-002.pdf](#)


### Specifications

[PS-51347-001-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

## Part Details

### General

Status	Obsolete
Category	Connector Housings
Series	51347
Description	3.30mm Pitch Wire-to-Wire Receptacle Housing, Positive Lock, Dual Row, 6 Circuits
Application	Signal, Wire-to-Wire
Product Name	N/A
UPC	800756599007

### Physical

Circuits (maximum)	6
Color - Resin	Natural
Gender	Receptacle
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Resin	Nylon
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.30mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-25° to +85°C

## Mates With / Use With

**Use with Part(s)**

Description	Part Number
3.30mm Pitch Terminal Position Assurance (TPA) Retainers	<u>51348</u>
3.30mm Pitch Female Crimp Terminals	<u>56187</u>

---

This document was generated on May 06, 2026

Obsolete