



## Data Sheet | Item Number: 289-179

Interface module; RJ-45; with power jumper contacts; PCB terminal blocks, double-row; Cat. 5; in mounting carrier; with shield connection; with shield clamping saddle; 1,50 mm<sup>2</sup>



<https://www.wago.com/289-179>



### Electrical data

Operating voltage	≤ 35 VAC; ≤ 50 VDC
Nominal current	2.1 A
Insulation resistance	≥ 500 MΩ
Specialty functions	With power jumper contacts With shield connection With shield clamping saddle

### Safety and protection

Dielectric strength (contact/contact) (AC, 1 min)	1 kVrms
---	---------

### Connection Data

Mating cycles	1000
Transmission length (max.)	100 m
Connection Cable	Cat. 5 (min.)
WAGO shield clamping saddle	11 mm wide; cable diameter up to 8 mm

### Connection 1

Pluggable connector	Shielded RJ-45; with two additional power jumper contacts
Pole number 1	10
Connection type	System

### Connection 2

Design	PCB terminal blocks (double-row)
Pole number	11
Connection type	System
Connection technology	CAGE CLAMP®
WAGO connector	WAGO 739 Series
Solid conductor	0.08 ... 1.5 mm <sup>2</sup> / 28 ... 14 AWG
Fine-stranded conductor	0.08 ... 1.5 mm <sup>2</sup> / 28 ... 14 AWG
Strip length	5 ... 6 mm / 0.2 ... 0.24 inches

### Physical data

Width	30 mm / 1.181 inches
Height	85 mm / 3.346 inches
Depth from upper-edge of DIN-rail	67 mm / 2.638 inches

### Mechanical data

Mounting type	DIN-35 rail
Housing design	Mounting carrier
Mating cycles	1000

### Material data

Fire load	0.503 MJ
Weight	52.5 g

### Environmental requirements

Ambient temperature (operation)	-40 ... +85 °C (Actuation: -35 ... +85 °C)
Ambient temperature (storage)	-40 ... +85 °C
Relative humidity	≤ 85 % (non-condensing)

### Commercial data

Product Group	6 (INTERFACE ELECTRONIC)
PU (SPU)	10 (1) pcs
Packaging type	Box
Country of origin	DE
GTIN	4045454326197
Customs tariff number	85366990990

### Product Classification

UNSPSC	39121421
eCl@ss 10.0	19-17-90-01
eCl@ss 9.0	19-17-90-01
ETIM 9.0	EC001121
ETIM 10.0	EC001121
ECCN	NO US CLASSIFICATION

### Environmental Product Compliance

RoHS Compliance Status	Compliant, No Exemption
------------------------	-------------------------

## Downloads

### Environmental Product Compliance

#### Compliance Search

Environmental Product Compliance 289-179



## Documentation

### Bid Text

289-179	19.02.2019	xml 3.82 KB	
289-179	09.02.2015	doc 26.00 KB	

### Instruction Leaflet

Operation and Assembly Instructions Interface	V 1.0.0 02.04.2025	pdf 1246.19 KB	
---	-----------------------	-------------------	--

## CAD/CAE-Data

### CAD data

2D/3D Models 289-179



### CAE data

EPLAN Data Portal 289-179	
WSCAD Universe 289-179	
ZUKEN Portal 289-179	

## 1 Compatible Products

### 1.1 Optional Accessories

#### 1.1.1 Marking

##### 1.1.1.1 Marking strip



#### Item No.: 709-196

Marking strips; for laser printer; translucent



#### Item No.: 709-177

Marking strips; on reel; 7.5 mm wide; not stretchable; plain; snap-on type; translucent



#### Item No.: 709-178

Marking strips; on reel; 7.5 mm wide; not stretchable; plain; snap-on type; white

### 1.1.2 Tool

#### 1.1.2.1 Operating tool



#### Item No.: 210-719

Operating tool; Blade: 2.5 x 0.4 mm; with a partially insulated shaft

Subject to changes. Please also observe the further product documentation!

Current addresses can be found at: [www.wago.com](http://www.wago.com)