



+ CONNECTORS

SCREENED



✓ Active

TE CONNECTIVITY (TE)
208M710-19B06
[Raychem](#) | [Magnaform Backshells](#)

208M710-19B06
TE Internal Number: 116237-000
Alias ID: 8-1190846-6

[Not EU RoHS Compliant](#)
[Not EU ELV Compliant](#)

Cable Diameter Range 48 – 76 mm [188 – 3 in]

Adapter Entry Size 06

Material Aluminum

Adapter Plating Material Cadmium per SAE AMS-QQ-P-416, Type II, Class 3, over appropriate under plate, per SAE AS85049 (500 Hour Salt Spray)

Style Shielded Boot

 **PRODUCT DRAWING**
English

 **3D PDF**

DOCUMENTATION

Product Drawings

BRAID TAIL BACKSHELL
PDF
English

CAD Files

3D PDF
PDF
3D

Customer View Model
2D_DXF.ZIP

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Catalog Pages/Data Sheets

5-1654025-5_sec6_Adapters

PDF

English

Product Specifications

Product Specification

General Harness Repair Manual

PDF

English

General Information Package For Solid, Spin Coupling And Shielded Adapters

PDF

English

Adapter Finish Specifications

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Style Shielded Boot

Termination Device Type Magneform Ring

Body Features

Adapter Entry Size 06

Material Aluminum

Adapter Plating Material Cadmium per SAE AMS-QQ-P-416, Type II, Class 3, over appropriate under plate, per SAE AS85049 (500 Hour Salt Spray)

Dimensions

Cable Diameter Range 48 – 76 mm [188 – 3 in]

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
