

# Product data sheet

Specifications



## MGE Galaxy 3500 10kVA 400V with 2 Battery Modules Expandable to 4, Start-up 5X8

G35T10KH2B4S

⚠ Discontinued on: Jul 5, 2021

⚠ To be end-of-service on: Dec 31, 2031

⚠ Discontinued - Service only

### Overview

Lead time Usually Ships within 2 Weeks

### Main

Main Input Voltage	400 V 3 phases
Other Input Voltage	380 V 415 V
Main Output Voltage	400 V 3 phases
Other Output Voltage	380 V 415 V
Rated power in W	8000 W
Rated power in VA	10000 VA
Output connector type	Hard wire 4-wire (3P + E) 1 Hard wire 5-wire (3P + N + E) 1
Connections - terminals	1 screw terminals
Battery type	Lead-acid battery
Provided equipment	Battery modules ship installed Bolt down brackets CD with software Installation guide Network management card Power modules ship installed Smart UPS signalling RS-232 cable Start-up service User manual

### Batteries & Runtime

Run Time	<a href="#">View Runtime Graph</a>
Efficiency	<a href="#">View Efficiency Graph</a>
Number of battery filled slots	2
Number of battery free slots	2
Battery recharge time	5 h
Number of battery replacement quantity	2
Additional information	Configurable for 380 : 400 or 415 V 3 Phase nominal output voltage
Battery voltage	+/- 192 V (split battery referenced to neutral)
Discharge battery voltage	+/- 154 V

Battery overload operation	10 minutes at 125% and 60 seconds at 150%
Battery charger power	995 W rated
Battery power in VAH	4983 VAh runtime
Battery life	3...5 year(s)
Battery graph comments	Estimated runtimes based on battery vendor data, at typical environmental conditions, with no electrical input and balanced PF = 0.8 output.
Extended runtime	0

## General

Number of power module free slots	0
Number of power module filled slots	0
Redundant	No

## Physical

Height	149.1 cm
Width	52.3 cm
Depth	83.8 cm
Net weight	443 kg
Mounting preference	No preference
USB compatible	No

## Input

Network frequency	40...70 Hz auto-sensing
Number of input connectors	1 hard wire 5-wire (3P + N + E)
Input voltage limits	340...460 V adjustable 400 V 304...477 V
Maximum input current	14 A
Switching current capacity	16 A
Input harmonic distortion	Less than 5 % for full load
Input protection type	3-pole circuit breaker
Inrush current	200 A peak
Load power factor	0.5 leading to 0.5 lagging
Input Power Factor at Full Load	0.98

## Output

Maximum configurable power in W	8000 W
Output frequency	47...53 Hz for 50 Hz nominal sync to mains 50 Hz +/- 0.1 % for 50 Hz nominal unsynchronised
Crest factor	Unlimited
Wave type	Sine wave
Output voltage tolerance	+/- 5% static and 100% load step
Output harmonic distortion	< 2% for 0 to 100% linear load and < 5% for full non-linear load
Output overload operation	10 minutes at 125% and 60 seconds at 150%

<b>Required output current protection</b>	16 A
<b>Bypass type</b>	Built-in maintenance bypass Built-in static bypass
<b>Efficiency</b>	94.1 % (in battery operation)
<b>Maximum configurable power in VA</b>	10000 VA

## Conformance

<b>Product certifications</b>	CE
<b>Standards</b>	EN 50091-2 EN/IEC 62040-3 EN/IEC 62040-1-1 IEC 61000-3-2 IEC 61000-3-3 ISO 14001 ISO 9001 VFI-SS-111

## Environmental

<b>Ambient air temperature for operation</b>	0...40 °C
<b>Relative humidity</b>	0...95 %
<b>Operating altitude</b>	0...3333 ft
<b>Ambient air temperature for storage</b>	-15...45 °C
<b>Storage Relative Humidity</b>	0...95 %
<b>Storage altitude</b>	0...15240 m
<b>Acoustic level</b>	51.3 dBA
<b>Heat dissipation</b>	1583 Btu/h
<b>IP degree of protection</b>	IP51

## Communications & Management

<b>Free slots</b>	0
<b>Preinstalled device</b>	Network management card 2 with environmental monitoring
<b>Control panel</b>	Multifunction LCD status and control console
<b>Emergency power off</b>	Yes

## Packing Units

<b>Unit Type of Package 1</b>	PCE
<b>Number of Units in Package 1</b>	1
<b>Package 1 Height</b>	164.3 cm
<b>Package 1 Width</b>	106.2 cm
<b>Package 1 Length</b>	65 cm
<b>Package 1 Weight</b>	474 kg

## Contractual warranty

<b>Warranty</b>	1 year repair or replace
-----------------	--------------------------

## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

### Use Better

#### Materials and Substances

EU RoHS Directive

Not applicable, out of EU RoHS legal scope

### Use Again

#### Repack and remanufacture

WEEE Label



The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins