

Color: ■ black

This unmanaged industrial ETHERNET switch (852-1111) has 5 Gigabit ETHERNET ports for easily setting up small- to medium-sized networks. Its slim design paired with a DIN-rail adapter simplifies installation in the control cabinet and provides high vibration and shock resistance. Additionally, automatic transmission rate detection (auto-negotiation) and automatic identification of the transmit and receive lines (Auto MDI-X) allow simple plug-and-play operation, saving time and money during commissioning.

Features:

- 5 ETHERNET ports 10/100/1000 Mbit/s Autonegotiation
- Front-panel diagnostic LEDs
- Supports Auto-MDI/MDI-X functions
- Full/half-duplex transfer modes for each port
- Store-and-forward switching method
- Integrated address look-up table, supports up to 8000 absolute MAC addresses
- Overvoltage protection
- Data flow control, per IEEE 802.3x Flow Control, in full-duplex mode
- Prioritization of ETHERNET data packets (PROFINET protocol, EtherType=0x8892) per IEEE802.1p
- DIN-35 rail mounting

Technical data	
Switching mode	Store-and-forward; non-blocking
Number of 1 Gb/s ports	5
Communication standards	IEEE 802.3 10BASE-T IEEE 802.3u 100BASE-TX IEEE 802.3ab 1000BASE-T IEEE 802.3x Flow Control IEEE 802.1p Prioritization
MAC table (size)	8000 addresses
Jumbo frame size	9000 bytes
Supply voltage	9 ... 48 VDC
Power consumption (max.)	3 W
Current consumption (max.)	500 mA
ESD (contact/air discharge)	4 KV / 8 KV
Transmission rate	Copper cable: 10/1000 Mbit/s
Transmission medium (communication/fieldbus)	Copper cable: Cat. 5 or higher, 100 m maximum cable length
Topology	Star
Indicators	Device: LED (PWR) green: Power supply; per port: LED (100, 1000) green: Status 100 Mbps, 1000 Mbps ports 1 ... 5




Connection data	
Connection technology: communication/fieldbus	Copper cable: 5 x RJ-45
Connection technology: supply	1 x Built-in male connector: 231-433/001-000; included female connector (MCS Connectors): 231-103/026-000
Physical data	
Width	23.4 mm / 0.921 inches
Height	109.2 mm / 4.299 inches
Depth	73.8 mm / 2.906 inches
Depth from upper-edge of DIN-rail	81 mm / 3.189 inches
Mechanical data	
Weight	190 g
Color	black
Housing material	Sheet steel
Conformity marking	CE
Environmental requirements	
Ambient temperature (operation)	-40 ... +70 °C
Ambient temperature (storage)	-40 ... +80 °C
Protection type	IP30
Relative humidity (without condensation)	95 %
Mounting type	DIN-35 rail
Vibration resistance	per IEC 60068-2-6
Shock resistance	per IEC 60068-2-27
Fire load	0 MJ
Commercial data	
Product Group	27 (special components I/O)
PU (SPU)	1 pcs
Packaging type	Box
Country of origin	TW
GTIN	4066966216639
Customs tariff number	85176200000
End of Sale	2024-04-01
End of Production	2024-04-02
End of Delivery	2024-04-03
End of Service and Repair	2026-04-01
Product classification	
UNSPSC	43222612
eCl@ss 10.0	19-17-01-30
eCl@ss 9.0	19-17-01-06
ETIM 9.0	EC000734
ETIM 8.0	EC000734
ECCN	5A992.C




Environmental Product Compliance	
RoHS Compliance Status	Compliant,No Exemption


Approvals / Certificates

General approvals			Declarations of conformity and manufacturer's declarations		
					
Approval	Standard	Certificate Name	Approval	Standard	Certificate Name
KC National Radio Research Agency	Article 58-2, Clause 3	MSIP-REM-W43-ISW852	EU-Declaration of Conformity WAGO GmbH & Co. KG	-	-
UL Underwriters Laboratories Inc. (ORDINARY LOCATIONS)	UL 61010-2-201	E175199	UK-Declaration of Conformity WAGO GmbH & Co. KG	-	-

Approvals for marine applications

		
Approval	Standard	Certificate Name
DNV DNV GL SE	-	TAA0000239

Downloads

Environmental Product Compliance	
Compliance Search	
Environmental Product Compliance 852-1111	


Documentation

Manual

Product Manual 5-Port 1000BASE-T Industrial ECO Switch

V 1.4.0  
17.12.2019


pdf  
798.25 KB



System Description

Industrial Switches – General Product Information

pdf  
1873.93 KB




Bid Text

852-1111

19.02.2019


xml  
5.39 KB




852-1111

09.10.2017

doc  
27.50 KB



ausschreiben.de  
852-1111






















CAD/CAE-Data	
<div>CAD data</div> <div>2D/3D Models 852-1111</div> <div>↓</div>	<div>CAE data</div> <div>EPLAN Data Portal 852-1111</div> <div>↓</div>
	<div>WSCAD Universe 852-1111</div> <div>↓</div>
	<div>ZUKEN Portal 852-1111</div> <div>↓</div>

1 Compatible Products

1.1 Optional Accessories

1.1.1 Cables and connectors

1.1.1.1 Connector plug

 <a href="#">Item No.: 750-979/000-011</a> Connector ETHERNET; RJ-45; Cat. 6A; angled; Code T568A; AWG 22; Strain relief	 <a href="#">Item No.: 750-979/000-021</a> Connector ETHERNET; RJ-45; Cat. 6A; angled; Code T568A; AWG 24; Strain relief	 <a href="#">Item No.: 750-979/000-012</a> Connector ETHERNET; RJ-45; Cat. 6A; angled; Code T568B; AWG 22; Strain relief	 <a href="#">Item No.: 750-979/000-022</a> Connector ETHERNET; RJ-45; Cat. 6A; angled; Code T568B; AWG 24; Strain relief
 <a href="#">Item No.: 750-977/000-011</a> Connector ETHERNET; RJ-45; Cat. 6A; straight; Code T568A; AWG 22	 <a href="#">Item No.: 750-978/000-011</a> Connector ETHERNET; RJ-45; Cat. 6A; straight; Code T568A; AWG 22; Strain relief	 <a href="#">Item No.: 750-977/000-021</a> Connector ETHERNET; RJ-45; Cat. 6A; straight; Code T568A; AWG 24	 <a href="#">Item No.: 750-978/000-021</a> Connector ETHERNET; RJ-45; Cat. 6A; straight; Code T568A; AWG 24; Strain relief
 <a href="#">Item No.: 750-977/000-012</a> Connector ETHERNET; RJ-45; Cat. 6A; straight; Code T568B; AWG 22	 <a href="#">Item No.: 750-978/000-012</a> Connector ETHERNET; RJ-45; Cat. 6A; straight; Code T568B; AWG 22; Strain relief	 <a href="#">Item No.: 750-977/000-022</a> Connector ETHERNET; RJ-45; Cat. 6A; straight; Code T568B; AWG 24	 <a href="#">Item No.: 750-978/000-022</a> Connector ETHERNET; RJ-45; Cat. 6A; straight; Code T568B; AWG 24; Strain relief
 <a href="#">Item No.: 750-979/000-013</a> Connector PROFINET; RJ-45; Cat. 6A; angled; AWG 22; Strain relief	 <a href="#">Item No.: 750-977/000-013</a> Connector PROFINET; RJ-45; Cat. 6A; straight; AWG 22	 <a href="#">Item No.: 750-978/000-013</a> Connector PROFINET; RJ-45; Cat. 6A; straight; AWG 22; Strain relief	 <a href="#">Item No.: 750-975</a> ETHERNET RJ-45 connector, IP20; ETHERNET 10/100 Mbit/s; for field assembly
 <a href="#">Item No.: 750-976</a> PROFINET RJ-45 connector, IP20; ETHERNET 10/100 Mbit/s; for field assembly			

1.1.2 Installation

1.1.2.1 Mounting accessories

 <a href="#">Item No.: 852-9101</a> DNV Carrier rail adapter; for ETHERNET Switches 852-1111/ 852-1111 marine approval; -
--



1.1.3 Interface module

1.1.3.1 Interface module



**Item No.: 289-195**  
Interface module; RJ-45; IDC technology; Cat. 6; in mounting carrier; with shield connection



**Item No.: 289-175**  
Interface module; RJ-45; PCB terminal blocks, double-row; Cat. 5; in mounting carrier; with shield connection; with shield clamping saddle; 1,50 mm<sup>2</sup>



**Item No.: 289-172**  
Interface module; RJ-45; RJ-45; Cat. 5; in mounting carrier



**Item No.: 289-196**  
Interface module; RJ-45; with power jumper contacts; PCB terminal blocks; Cat. 5

1.1.4 Power supply

1.1.4.1 Power supply



**Item No.: 787-1102**  
Switched-mode power supply; Compact; 1-phase; 24 VDC output voltage; 1.3 A output current; DC-OK LED



**Item No.: 787-1112**  
Switched-mode power supply; Compact; 1-phase; 24 VDC output voltage; 2.5 A output current; DC-OK LED



**Item No.: 787-1122**  
Switched-mode power supply; Compact; 1-phase; 24 VDC output voltage; 4 A output current; DC-OK LED



**Item No.: 787-1226**  
Switched-mode power supply; Compact; 1-phase; 24 VDC output voltage; 6 A output current; DC-OK LED



**Item No.: 787-1702**  
Switched-mode power supply; Eco; 1-phase; 24 VDC output voltage; 1.25 A output current; DC-OK LED



**Item No.: 787-1712**  
Switched-mode power supply; Eco; 1-phase; 24 VDC output voltage; 2.5 A output current; DC-OK LED



**Item No.: 787-1722**  
Switched-mode power supply; Eco; 1-phase; 24 VDC output voltage; 5 A output current; DC-OK LED