Product data sheet
33 57 851 5000 002
Hyb.Cab.2XFO MM 50µm+3x2,5qmm;reel 500M
This product is not orderable anymore. Please contact your local distribution partner.

Pushing Performance
Since 1945

Hyb.Cab.2XFO MM 50µm+3x2,5qmm;reel 500M




Image is for illustration purposes only. Please refer to product description.

Part number	33 57 851 5000 002
Specification	Hyb.Cab.2XFO MM 50µm +3x2,5qmm;reel 500M
HARTING eCatalogue	https://b2b.harting.com/33578515000002

Identification

Category	System cabling
Element	Bulk cables
Specification	Not assembled
Type of cable	Hybrid cable (copper/FO)
Description of the cable	Multimode

Version

Cable length	500 m
Core structure	2x G50 / 125 µm 3x 2.5 mm²

Technical characteristics

Cable diameter	12.6 mm
Minimum bending radius	10x Cable diameter (repeated bending) 5x Cable diameter (singular bending)

Material properties

Material (cable)	PVC
Colour (cable)	Black
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained

HARTING Customised Solutions GmbH & Co. KG | In der Tütenbeke 22 | 32339 Espelkamp | Germany
Phone +49 5772 47-0 | info@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.

Pushing Performance
Since 1945

Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Commercial data

Packaging size	1
Net weight	110 kg
Net weight	217 g/m
Country of origin	Germany
European customs tariff number	85447000
GTIN	5713140794887
ETIM	EC001579
eCl@ss	27060501 Hybrid cable

HARTING Customised Solutions GmbH & Co. KG | In der Tütenbeke 22 | 32339 Espelkamp | Germany
Phone +49 5772 47-0 | info@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.