
Part Number : 848548026
Product Description : DeviceNet Micro-Change Single-Ended, 5 Poles, A-Coded, Male (Straight) to Pigtail, 5.0m (16.40') Length
Series Number : 84854
Status : Active
Product Category : Industrial Cable Assemblies
Engineering Part Number : NMEA-DND02NB-M050



Documents and Resources

Drawings

848548026_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Downloaded from Arrow.com.

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Industrial Cable Assemblies
Series	84854
Description	DeviceNet Micro-Change Single-Ended, 5 Poles, A-Coded, Male (Straight) to Pigtail, 5.0m (16.40') Length
IP Rating	IP67
Product Name	Micro-Change (M12)
Protocol	N/A
Type	Single Ended
UPC	822350909174

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V

Physical

Cable Diameter	5.72mm (.225")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Gray
Connector End A	Micro-Change (M12)
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Male-Pigtail
Keyway	A-Coded
LED Indicator	None
Material - Cable Jacket	PVC
Material - Connector Body	PVC
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold

Downloaded from Arrow.com.

Orientation	Straight to Pigtail
Poles	5
Temperature Range - Operating	-20° to +80°C
Wire/Cable Type	Thin Standard Cable
Wire Size (AWG)	22

Downloaded from Arrow.com.