



Part Number : [1200680139](#)
Product Description : Micro-Change (M12) Solid Body Splitter, 1 x 5-Pole Male to 2 x 5-Pole Females, Black Overmold
Series Number : 120068
Status : Active
Product Category : Industrial Tees and Splitters
Engineering Number : 081205EMF00000



Documents & Resources

Drawings
[1200680139 sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not saleable
China RoHS	per SJ/T 11365-2006
EU ELV	Not saleable
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Industrial Tees and Splitters
Series	120068
Description	Micro-Change (M12) Solid Body Splitter, 1 x 5-Pole Male to 2 x 5-Pole Females, Black Overmold
IP Rating	IP67
Product Name	Micro-Change (M12)
Type	Splitter - Solid Body
UPC	78678886655

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	30V AC / 36V DC

Physical

Drop Connector	N/A
Drop Gender	N/A
Keyway	Single
LED Indicator	None
Left Trunk Connector	Micro-Change (M12)
Left Trunk Gender	Male
Leg 1 Length	N/A
Leg 2 Length	N/A
Material - Cable Jacket	N/A
Material - Connector Body	PUR

Material - Coupling Nut	Nickel-plated Brass
Net Weight	29.470/g
Poles	5
Right Trunk Connector	Micro-Change (M12)
Right Trunk Gender	Female
Temperature Range - Operating	-25°C to +90°C

This document was generated on Sep 25, 2025