



**Series
DSX**

**SIZE 22 CRIMP PIN CONTACT
WIRE SIZE AWG 22-24-26
COMPLIANT TO M39029/11-144**

**Issue:
Nov. 07, 2014**

**Page
1/1**



**MATERIAL : LEAD NICKEL COPPER
FINISH : GOLD PER MIL-G-45204 TYPE I OR II GRADE C OR D CLASS 1 50 MICROINCHES OVER NICKEL PLATE PER QQ-N-290**

**WIRES ACCOMODATED : AWG 22-24-26
INSULATOR DIAMETER : .055 MAX (1,40)
STRIP LENGHT : .138 (3,50)**


**CRIMP CONTACT TENSILE REQUIREMENTS USING MIL SPEC TOOLING AND WIRE SPEC
M22520/2-01 22 GA. 11 LBS (5,5 daN)**

CRIMPED CONTACTS WILL SHOW NO CRACK WHEN INSPECTED PER MIL-C-22520 AT 10X

**RADIAL TOOLING RECOMMENDATION
CRIMPING TOOL : M22520/2-01 (RADIAL 282 281)
SELECTOR POSITION : 4 FOR AWG 22
3 FOR AWG 24
3 FOR AWG 26
POSITIONER : M22520/2-23 (RADIAL 282 970)**

**INSERTION/EXTRACTION TOOL : M81969/1-01 (RADIAL 282 885) OR M81969/14-01 (RADIAL 282522)
SPL RADIAL INS. 282 880 / EXT. 282 890**

DIMENSIONS : mm (inch are given for information only)



Estimated weight : 0.13 g

CREATION

PEN:

NOM: MACARI

DATE: May 29, 1980

APPR.:

Nov. 07, 14	Added M81969/14-01 (RADIAL 282522)	Zuniga	Dupuis	
Dec. 02, 13	Add M39029/11-144 in the title	Moutault	Dupuis	
Jan. 04,07	Added tolerance on dimensions	DUPUIS	MONDOT	
Issue	Revisions	Name	Approved	

616200EN

RADIAL PROPRIETARY INFORMATION

This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from RADIAL. This information is given as an indication. In the continual goal to improve our products, we reserve the right to make any modifications judged necessary.

4112_9311