760239976 | FACT-2ENG4



FACT® NG4 Fiber Chassis, gray with 4 unloaded trays, 2E high, for holding 8 NG4 adapter packs or 4 NG4 MPO modules or 4 NG4 cabled LC/SC modules or 4 NG4 value added modules

- Designed for use with the all-purpose all-front-access FACT frames and FIST-GR3 frames supporting up to 2,688 LC or 1,344 SC connections in a single frame (FACT-IC frame 2880 LC or 1440 SC)
- Reduced installation and maintenance time via the toolless snap-on design supporting both interconnect and cross-connect applications
- Flexible customization enabled by 4 chassis types (patch-only, patch-splice, pre-cabled and splice-only) to support all ODF applications
- High density through the single FACT element height (1E) being 30% less tall compared to the industry standard panel height (1HU)

Product Classification

Regional Availability	Asia | Australia/New Zealand | EMEA | Latin America | North America
Portfolio	CommScope®
Product Type	Fiber VAM chassis | Fiber patch chassis
Product Brand	FACT®
Product Series	FACT

General Specifications

Functionality	Multiplexing | Patching | Splitting
Application	For use with FACT frames | Compatible with FIST-GR3-R frames when backplate is used (optional)
Body Style	Symmetrical
Color	Gray
Growth Configuration	Unloaded
Interface, front	Unloaded
Patch Cord Routing	Left sided | Right sided
Rack Type	FACT | FIST-GR3

©2026 CommScope Technologies LLC, an Amphenol company. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners.
Revised: July 17, 2026

COMMSCOPE® an Amphenol company


Downloaded from Arrow.com.

Rack Units	1.4
Shelf Movement	Sliding
Splicing Capacity, maximum	0
Total Ports, quantity	0
Transmission Standards	ETSI EN 300 019-1-3 | IEC 61300-3-30

Dimensions

Height	61.9 mm | 2.437 in
Width	524 mm | 20.63 in
Depth	283 mm | 11.142 in

Ordering Tree



Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Storage Temperature	-20 °C to +85 °C (-4 °F to +176 °F)
Flammability Rating	UL 94 V-0

©2026 CommScope Technologies LLC, an Amphenol company. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners.
Revised: July 17, 2026
Downloaded from Arrow.com.

Packaging and Weights

Included	Mounting hardware for FACT frame
Packaging quantity	1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



©2026 CommScope Technologies LLC, an Amphenol company. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners.
Revised: July 17, 2026

COMMSCOPE® an Amphenol company

Downloaded from Arrow.com.