

DAISY-7X1-WW-D

~80° wide beam. Variant with diffused lenses.
Choose SHD with no lips or SHD2 with narrow lips and square openings. SHD3 with narrow lips and round openings.

SPECIFICATION:

Dimensions	279.5 x 39.6
Height	20.3 mm
Fastening	pin, screw, clips
ROHS compliant	yes ⓘ



MATERIALS:

Component	Type	Material	Colour	Finish	Length (mm)
DAISY-7X1-WW-D	Linear lens	PMMA	milky		
DAISY-7X1-SHD2-MET-MATT	Shade	PC-ABS	metal	matt	
DAISY-7X1-SHD2-MET	Shade	PC	metal	gloss	
DAISY-7X1-SHD2-MATT-WHT	Shade	PC	white	matt	
DAISY-7X1-SHD2-WHT	Shade	PC	white	gloss	
DAISY-7X1-SHD2-MATT	Shade	PC-ABS	black	matt	
DAISY-7X1-SHD2	Shade	PC	black	gloss	
DAISY-7X1-SHD3-MATT-GLD	Shade	PC	gold	matt	
DAISY-7X1-SHD3-MATT-RED	Shade	PC	red	matt	
DAISY-7X1-SHD3-MATT-GR	Shade	PC	grey	matt	
DAISY-7X1-SHD-MATT-GLD	Shade	PC	gold	matt	
DAISY-7X1-SHD-MATT-GR	Shade	PC	grey	matt	
DAISY-7X1-SHD-MATT-RED	Shade	PC	red	matt	
DAISY-7X1-SHD3-MET-MATT	Shade	PC	metal	matt	
DAISY-7X1-SHD3-MET	Shade	PC	metal	gloss	
DAISY-7X1-SHD3-WHT-MATT	Shade	PC	white	matt	
DAISY-7X1-SHD3-WHT	Shade	PC	white	gloss	

DAISY-7X1-SHD	Shade	PC	black	gloss
DAISY-7X1-SHD-MET-MATT	Shade	PC	metal	matt
DAISY-7X1-SHD-MET	Shade	PC	metal	gloss
DAISY-7X1-SHD-WHT-MATT	Shade	PC	white	matt
DAISY-7X1-SHD-MATT	Shade	PC	black	matt
DAISY-7X1-SHD-WHT	Shade	PC	white	gloss
DAISY-7X1-SHD	Shade	PC	black	gloss

ORDERING INFORMATION:


Quantities for one set:


Linear lens 1

Shade 1

Component		Qty in box	MOQ	MPQ	Box weight (kg)
C17361_DAISY-7X1-WW-D » Box size: 400 x 300 x 300 mm	Linear lens	312	312	24	5.5
C19853_DAISY-7X1-SHD3-MATT-GR » Box size: 595 x 360 x 230 mm	Shade	156	312	24	7.1
C19312_DAISY-7X1-SHD3 » Box size: 595 x 360 x 230 mm	Shade	156	312	24	6.1
L20012_DAISY-7X1-SHD2-WHT » Box size: 595 x 360 x 230 mm	Shade	156	312	24	7.2
C19642_DAISY-7X1-SHD3-MET-MATT » Box size: 595 x 360 x 230 mm	Shade	156	312	24	5.7
C17225_DAISY-7X1-SHD-WHT-MATT » Box size: 595 x 360 x 230 mm	Shade	156	312	24	7.6
C19854_DAISY-7X1-SHD3-MATT-RED » Box size: 595 x 360 x 230 mm	Shade	156	312	24	6.2
C19313_DAISY-7X1-SHD3-MATT » Box size: 595 x 360 x 230 mm	Shade	156	312	24	5.8
L20013_DAISY-7X1-SHD2-MATT-WHT » Box size: 595 x 360 x 230 mm	Shade	156	312	24	7.1
C19763_DAISY-7X1-SHD-MATT-RED » Box size: 595 x 360 x 230 mm	Shade	156	312	24	7.1
C19855_DAISY-7X1-SHD3-MATT-GLD » Box size: 595 x 360 x 230 mm	Shade	156	312	24	6.2
C19314_DAISY-7X1-SHD3-WHT » Box size: 595 x 360 x 230 mm	Shade	156	312	24	6.3
C16872_DAISY-7X1-SHD » Box size: 595 x 360 x 230 mm	Shade	156	312	24	7.1
L20014_DAISY-7X1-SHD2-MET » Box size: 595 x 360 x 230 mm	Shade	156	312	24	7.0
C19764_DAISY-7X1-SHD-MATT-GR » Box size: 595 x 360 x 230 mm	Shade	156	312	24	5.7
C18167_DAISY-7X1-SHD-MET » Box size: 595 x 360 x 230 mm	Shade	156	312	24	7.0
L20010_DAISY-7X1-SHD2 » Box size: 595 x 360 x 230 mm	Shade	156	312	24	6.9
C19315_DAISY-7X1-SHD3-WHT-MATT » Box size: 595 x 360 x 230 mm	Shade	156	312	24	6.2
C16876_DAISY-7X1-SHD-WHT » Box size: 595 x 360 x 230 mm	Shade	156	312	24	7.6

C19852_DAISY-7X1-SHD-MATT-GLD » Box size: 595 x 360 x 230 mm	Shade	156	312	24	7.1
C18409_DAISY-7X1-SHD-MET-MATT » Box size: 595 x 360 x 230 mm	Shade	156	312	24	7.0
L20011_DAISY-7X1-SHD2-MATT » Box size: 595 x 360 x 230 mm	Shade	156	312	24	6.7
C19641_DAISY-7X1-SHD3-MET » Box size: 595 x 360 x 230 mm	Shade	156	312	24	6.1
C17051_DAISY-7X1-SHD-MATT » Box size: 595 x 360 x 230 mm	Shade	156	312	24	7.3






See also our general installation guide: www.ledil.com/installation_guide

OPTICAL RESULTS (MEASURED):





LED LIGHT ENGINE DAISY 28 LEDs 277.5mm x 20mm
 FWHM / FWTM 74.0° / 94.0°
 Efficiency 91 %
 Peak intensity 0.7 cd/lm
 LEDs/each optic 4
 Light colour/type White
 Required components:
 C17533_DAISY-7X1-SHD-MET-MATT



Light distribution files





LED LIGHT ENGINE DAISY 28 LEDs 277.5mm x 20mm
 FWHM / FWTM 75.0° / 93.0°
 Efficiency 79 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 4
 Light colour/type White
 Required components:
 C16872_DAISY-7X1-SHD



Light distribution files



LED LIGHT ENGINE DAISY 28 LEDs 277.5mm x 20mm
 FWHM / FWTM 74.5° / 92.0°
 Efficiency 78 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 4
 Light colour/type White
 Required components:
 C17051_DAISY-7X1-SHD-MATT





Light distribution files

OPTICAL RESULTS (MEASURED):





LED LIGHT ENGINE DAISY 28 LEDs 277.5mm x 20mm
 FWHM / FWTM 74.0° / 93.0°
 Efficiency 94 %
 Peak intensity 0.7 cd/lm
 LEDs/each optic 4
 Light colour/type White
 Required components:
 C18167_DAISY-7X1-SHD-MET



Light distribution files





LED LIGHT ENGINE DAISY 28 LEDs 277.5mm x 20mm
 FWHM / FWTM 75.5° / 96.0°
 Efficiency 93 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 4
 Light colour/type White
 Required components:
 C16876_DAISY-7X1-SHD-WHT



Light distribution files



LED LIGHT ENGINE DAISY 28 LEDs 277.5mm x 20mm
 FWHM / FWTM 75.5° / 96.0°
 Efficiency 92 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 4
 Light colour/type White
 Required components:
 C17225_DAISY-7X1-SHD-WHT-MATT





Light distribution files

OPTICAL RESULTS (MEASURED):

inventronics


LED PL-LIN-2000 280x24mm
 FWHM / FWTM 74.0° / 93.0°
 Efficiency 77 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 4
 Light colour/type White
 Required components:
 C17051_DAISY-7X1-SHD-MATT



Light distribution files

LUMILEDS



LED LUXEON 2835 Line
 FWHM / FWTM 75.5° / 95.5 + 97.0°
 Efficiency 93 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 4
 Light colour/type White
 Required components:
 C16876_DAISY-7X1-SHD-WHT



Light distribution files

LUMILEDS

LED LUXEON 2835 Line
 FWHM / FWTM 75.5° / 95.5 + 97.0°
 Efficiency 92 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 4
 Light colour/type White
 Required components:
 C17225_DAISY-7X1-SHD-WHT-MATT




Light distribution files

OPTICAL RESULTS (MEASURED):





LED LUXEON 2835 Line
FWHM / FWTM 74.0° / 93.5 + 94.5°
Efficiency 91 %
Peak intensity 0.7 cd/lm
LEDs/each optic 4
Light colour/type White
Required components:
C17533_DAISSY-7X1-SHD-MET-MATT



Light distribution files





LED LUXEON 2835 Line
FWHM / FWTM 74.5° / 92.0 + 93.0°
Efficiency 79 %
Peak intensity 0.6 cd/lm
LEDs/each optic 4
Light colour/type White
Required components:
C16872_DAISSY-7X1-SHD



Light distribution files



LED LUXEON 2835 Line
FWHM / FWTM 74.5° / 92.0 + 92.5°
Efficiency 78 %
Peak intensity 0.6 cd/lm
LEDs/each optic 4
Light colour/type White
Required components:
C17051_DAISSY-7X1-SHD-MATT





Light distribution files

OPTICAL RESULTS (MEASURED):





LED LUXEON 2835 Line
 FWHM / FWTM 73.5° / 93.0 + 93.5°
 Efficiency 94 %
 Peak intensity 0.7 cd/lm
 LEDs/each optic 4
 Light colour/type White
 Required components:
 C17532_DAISSY-7X1-SHD-MET



Light distribution files





LED LinLED 280x28mm 1100lm 8x0 2C 42V DAISY-7X1 G1
 FWHM / FWTM 74.0° / 93.0°
 Efficiency 93 %
 Peak intensity 0.7 cd/lm
 LEDs/each optic 4
 Light colour/type White
 Required components:
 C18167_DAISSY-7X1-SHD-MET



Light distribution files



LED LinLED 280x28mm 1100lm 8x0 2C 42V DAISY-7X1 G1
 FWHM / FWTM 76.0° / 97.0°
 Efficiency 91 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 4
 Light colour/type White
 Required components:
 C16876_DAISSY-7X1-SHD-WHT





Light distribution files

OPTICAL RESULTS (MEASURED):

MST | Your solutions



LED LinLED 280x28mm 1100lm 8x0 2C 42V DAISY-7X1 G1
 FWHM / FWTM 74.0° / 94.0°
 Efficiency 90 %
 Peak intensity 0.7 cd/lm
 LEDs/each optic 4
 Light colour/type White
 Required components:
 C17533_DAISY-7X1-SHD-MET-MATT



Light distribution files

MST | Your solutions



LED LinLED 280x28mm 1100lm 8x0 2C 42V DAISY-7X1 G1
 FWHM / FWTM 75.0° / 97.0°
 Efficiency 91 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 4
 Light colour/type White
 Required components:
 C17225_DAISY-7X1-SHD-WHT-MATT



Light distribution files

MST | Your solutions

LED LinLED 280x28mm 1100lm 8x0 2C 42V DAISY-7X1 G1
 FWHM / FWTM 74.0° / 93.0°
 Efficiency 78 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 4
 Light colour/type White
 Required components:
 C16872_DAISY-7X1-SHD





Light distribution files

OPTICAL RESULTS (MEASURED):

MST | Your solutions



LED LinLED 280x28mm 1100lm 8x0 2C 42V DAISY-7X1 G1
 FWHM / FWTM 75.0° / 93.0°
 Efficiency 76 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 4
 Light colour/type White
 Required components:
 C17051_DAISY-7X1-SHD-MATT



Light distribution files

MST | Your solutions



LED LinLED 280x28mm 1600lm 840 4C 21V DAISY 7x1(ZT25)
 FWHM / FWTM 77.0° / 89.0°
 Efficiency 77 %
 Peak intensity 0.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C16872_DAISY-7X1-SHD



Light distribution files

MST | Your solutions

LED LinLED 280x28mm 2x550lm 827-865 2x2C 42V DAISY-7X1
 FWHM / FWTM 75.0° / 94.0°
 Efficiency 78 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 4
 Light colour/type Tunable White
 Required components:
 C17051_DAISY-7X1-SHD-MATT





Light distribution files

OPTICAL RESULTS (MEASURED):

MST | Your solutions



LED LinLED 280x28mm 2x550lm 827-865 2x2C 42V DAISY-7X1-WW-D
 FWHM / FWTM 74.0° / 94.0°
 Efficiency 94 %
 Peak intensity 0.7 cd/lm
 LEDs/each optic 4
 Light colour/type Tunable White
 Required components:
 C18167_DAISY-7X1-SHD-MET



Light distribution files

MST | Your solutions


LED LinLED 280x28mm 2x550lm 827-865 2x2C 42V DAISY-7X1-WW-D
 FWHM / FWTM 77.0° / 98.0°
 Efficiency 93 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 4
 Light colour/type Tunable White
 Required components:
 C16876_DAISY-7X1-SHD-WHT



Light distribution files

MST | Your solutions

LED LinLED 280x28mm 2x550lm 827-865 2x2C 42V DAISY-7X1-WW-D
 FWHM / FWTM 77.0° / 98.0°
 Efficiency 92 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 4
 Light colour/type Tunable White
 Required components:
 C17225_DAISY-7X1-SHD-WHT-MATT





Light distribution files

OPTICAL RESULTS (MEASURED):

MST | Your solutions



LED LinLED 280x28mm 2x550lm 827-865 2x2C 42V DAISY-7X1
FWHM / FWTM 75.0° / 95.0°
Efficiency 92 %
Peak intensity 0.7 cd/lm
LEDs/each optic 4
Light colour/type Tunable White
Required components:
C17533_DAISY-7X1-SHD-MET-MATT



Light distribution files

MST | Your solutions


LED LinLED 280x28mm 2x550lm 827-865 2x2C 42V DAISY-7X1
FWHM / FWTM 75.0° / 93.0°
Efficiency 79 %
Peak intensity 0.6 cd/lm
LEDs/each optic 4
Light colour/type Tunable White
Required components:
C16872_DAISY-7X1-SHD



Light distribution files

MST | Your solutions

LED LinLED 560x28mm 2200lm 840 4C 42V DAISY-7X1 G1
FWHM / FWTM 75.0° / 97.0°
Efficiency 91 %
Peak intensity 0.6 cd/lm
LEDs/each optic 4
Light colour/type White
Required components:
C17225_DAISY-7X1-SHD-WHT-MATT




Light distribution files

OPTICAL RESULTS (MEASURED):





LED LinLED 560x28mm 2200lm 840 4C 42V DAISY-7X1 G1
 FWHM / FWTM 75.0° / 93.0°
 Efficiency 76 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 4
 Light colour/type White
 Required components:
 C17051_DAISY-7X1-SHD-MATT



Light distribution files





LED NF2W757G-MT (Tunable White)
 FWHM / FWTM 80.0° / 90.0°
 Efficiency 79 %
 Peak intensity 0.5 cd/lm
 LEDs/each optic 1
 Light colour/type Tunable White
 Required components:
 C16872_DAISY-7X1-SHD



Light distribution files



LED NF2W757G-MT (Tunable White)
 FWHM / FWTM 80.0° / 95.0°
 Efficiency 93 %
 Peak intensity 0.5 cd/lm
 LEDs/each optic 1
 Light colour/type Tunable White
 Required components:
 C16876_DAISY-7X1-SHD-WHT




Light distribution files

OPTICAL RESULTS (MEASURED):

OSRAM
Opto Semiconductors



LED OSCONIQ E 2835
FWHM / FWTM 74.0° / 93.0°
Efficiency 77 %
Peak intensity 0.6 cd/lm
LEDs/each optic 4
Light colour/type White
Required components:
C17051_DAISY-7X1-SHD-MATT



Light distribution files

SAMSUNG



LED LM28xB Series
FWHM / FWTM 78.0° / 91.0°
Efficiency 79 %
Peak intensity 0.5 cd/lm
LEDs/each optic 2
Light colour/type White
Required components:
C16872_DAISY-7X1-SHD



Light distribution files

SAMSUNG

LED LM28xB Series
FWHM / FWTM 78.0° / 95.0°
Efficiency 93 %
Peak intensity 0.6 cd/lm
LEDs/each optic 2
Light colour/type White
Required components:
C16876_DAISY-7X1-SHD-WHT





Light distribution files

OPTICAL RESULTS (MEASURED):

SAMSUNG

LED LM28xB Series
FWHM / FWTM 75.0° / 89.0°
Efficiency 73 %
Peak intensity 0.5 cd/lm
LEDs/each optic 2
Light colour/type White
Required components:
C17051_DAISY-7X1-SHD-MATT





Light distribution files

SEITEC

Elektronik GmbH

LED LED-St-L28W2c4-xxx-C015-55 (DAISY-7x1)
FWHM / FWTM 74.0° / 94.0°
Efficiency 92 %
Peak intensity 0.7 cd/lm
LEDs/each optic 4
Light colour/type White
Required components:
C17533_DAISY-7X1-SHD-MET-MATT





Light distribution files

SEITEC

Elektronik GmbH

LED LED-St-L28W2c4-xxx-C015-55 (DAISY-7x1)
FWHM / FWTM 76.0° / 98.0°
Efficiency 92 %
Peak intensity 0.6 cd/lm
LEDs/each optic 4
Light colour/type White
Required components:
C16876_DAISY-7X1-SHD-WHT




Light distribution files

OPTICAL RESULTS (MEASURED):





LED LED-St-L28W2c4-xxx-C015-55 (DAISY-7x1)
 FWHM / FWTM 76.0° / 97.0°
 Efficiency 92 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 4
 Light colour/type White
 Required components:
 C17225_DAISY-7X1-SHD-WHT-MATT



Light distribution files





LED LED-St-L28W2c4-xxx-C015-55 (DAISY-7x1)
 FWHM / FWTM 75.0° / 92.0°
 Efficiency 78 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 4
 Light colour/type White
 Required components:
 C16872_DAISY-7X1-SHD



Light distribution files



LED LED-St-L28W2c4-xxx-C015-55 (DAISY-7x1)
 FWHM / FWTM 75.0° / 93.0°
 Efficiency 77 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 4
 Light colour/type White
 Required components:
 C17051_DAISY-7X1-SHD-MATT





Light distribution files

OPTICAL RESULTS (MEASURED):





LED LED-St-L28W2c4-xxx-C015-55 (DAISY-7x1)
 FWHM / FWTM 74.0° / 93.0°
 Efficiency 94 %
 Peak intensity 0.7 cd/lm
 LEDs/each optic 4
 Light colour/type White
 Required components:
 C18167_DAISY-7X1-SHD-MET



Light distribution files





LED PassivePAQ-L-1F35-SSA3-2.7K-840-3-DC
 FWHM / FWTM 75.0° / 96.0°
 Efficiency 76 %
 Peak intensity 0.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C17051_DAISY-7X1-SHD-MATT



Light distribution files



LED PassivePAQ-L-1F35-SSA3-2.7K-840-3-DC
 FWHM / FWTM 75.0° / 96.0°
 Efficiency 76 %
 Peak intensity 0.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C16872_DAISY-7X1-SHD





Light distribution files

OPTICAL RESULTS (MEASURED):





LED PassivePAQ-L-1F35-SSA3-2.7K-840-3-DC
 FWHM / FWTM 76.0° / 100.0°
 Efficiency 90 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C17225_DAISY-7X1-SHD-WHT-MATT



Light distribution files





LED PassivePAQ-L-1F35-SSA3-2.7K-840-3-DC
 FWHM / FWTM 76.0° / 100.0°
 Efficiency 91 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C16876_DAISY-7X1-SHD-WHT



Light distribution files



LED LLE 24x280mm 750lm 8x0 LVD ADV1
 FWHM / FWTM 75.0° / 94.0°
 Efficiency 77 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 4
 Light colour/type White
 Required components:
 C17051_DAISY-7X1-SHD-MATT





Light distribution files

OPTICAL RESULTS (MEASURED):

TRIDONIC



LED LLE 24x280mm 750lm 8x0 LVD ADV1
 FWHM / FWTM 75.0° / 93.0°
 Efficiency 78 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 4
 Light colour/type White
 Required components:
 C16872_DAISY-7X1-SHD



Light distribution files

TRIDONIC



LED LLE 24x280mm 750lm 8x0 LVD ADV1
 FWHM / FWTM 76.0° / 98.0°
 Efficiency 91 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 4
 Light colour/type White
 Required components:
 C17225_DAISY-7X1-SHD-WHT-MATT



Light distribution files

TRIDONIC

LED LLE 24x280mm 750lm 8x0 LVD ADV1
 FWHM / FWTM 75.0° / 98.0°
 Efficiency 91 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 4
 Light colour/type White
 Required components:
 C16876_DAISY-7X1-SHD-WHT





Light distribution files

OPTICAL RESULTS (MEASURED):

LEDiL®



LED BLX-LN-560-24-C2-2400 (Daisy-7x1)
 FWHM / FWTM 75.0° / 98.0°
 Efficiency 92 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C16876_DAISY-7X1-SHD-WHT



Light distribution files

LEDiL®

LED BLX-LN-560-24-C2-2400 (Daisy-7x1)
 FWHM / FWTM 74.0° / 93.0°
 Efficiency 78 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C16872_DAISY-7X1-SHD




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED SMD 3838 RGBW 3V
FWHM / FWTM 77.0° / 92.0°
Efficiency 80 %
Peak intensity 0.6 cd/lm
LEDs/each optic 1
Light colour/type RGBW
Required components:
C16872_DAISY-7X1-SHD



Light distribution files




LED J Series 2835
FWHM / FWTM 74.0° / 92.0°
Efficiency 78 %
Peak intensity 0.6 cd/lm
LEDs/each optic 4
Light colour/type White
Required components:
C17051_DAISY-7X1-SHD-MATT



Light distribution files



LED J Series 2835
FWHM / FWTM 74.0° / 92.0°
Efficiency 85 %
Peak intensity 0.7 cd/lm
LEDs/each optic 4
Light colour/type White
Required components:
C17225_DAISY-7X1-SHD-WHT-MATT




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED J Series 2835
FWHM / FWTM 74.0° / 92.0°
Efficiency 84 %
Peak intensity 0.6 cd/lm
LEDs/each optic 4
Light colour/type White
Required components:
C18167_DAISY-7X1-SHD-MET



Light distribution files




LED J Series 2835
FWHM / FWTM 75.0° / 94.0°
Efficiency 78 %
Peak intensity 0.6 cd/lm
LEDs/each optic 4
Light colour/type White
Required components:
C16872_DAISY-7X1-SHD



Light distribution files



LED LUXEON 2835 Line
FWHM / FWTM 74.0° / 91.0°
Efficiency 88 %
Peak intensity 0.7 cd/lm
LEDs/each optic 3
Light colour/type RGB
Required components:
C17225_DAISY-7X1-SHD-WHT-MATT




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED LUXEON 2835 Line
FWHM / FWTM 76.0° / 92.0°
Efficiency 75 %
Peak intensity 0.5 cd/lm
LEDs/each optic 3
Light colour/type RGB
Required components:
C17051_DAISY-7X1-SHD-MATT



Light distribution files




LED LUXEON 2835 Line
FWHM / FWTM 75.0° / 92.0°
Efficiency 90 %
Peak intensity 0.7 cd/lm
LEDs/each optic 3
Light colour/type RGB
Required components:
C18167_DAISY-7X1-SHD-MET



Light distribution files



LED LinLED 280x28mm 1100lm 8x0 2C 42V DAISY-7X1 G1
FWHM / FWTM 74.0° / 92.0°
Efficiency 84 %
Peak intensity 0.7 cd/lm
LEDs/each optic 4
Light colour/type White
Required components:
C17225_DAISY-7X1-SHD-WHT-MATT




Light distribution files

OPTICAL RESULTS (SIMULATED):

MST | Your solutions


LED LinLED 280x28mm 1100lm 8x0 2C 42V DAISY-7X1 G1
 FWHM / FWTM 74.0° / 92.0°
 Efficiency 75 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 4
 Light colour/type White
 Required components:
 C17051_DAISY-7X1-SHD-MATT



Light distribution files

MST | Your solutions


LED LinLED 280x28mm 1100lm 8x0 2C 42V DAISY-7X1 G1
 FWHM / FWTM 74.0° / 91.0°
 Efficiency 84 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 4
 Light colour/type White
 Required components:
 C16876_DAISY-7X1-SHD-WHT



Light distribution files

MST | Your solutions

LED LinLED 280x28mm 1100lm 8x0 2C 42V DAISY-7X1 G1
 FWHM / FWTM 74.0° / 92.0°
 Efficiency 76 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 4
 Light colour/type White
 Required components:
 C16872_DAISY-7X1-SHD




Light distribution files

OPTICAL RESULTS (SIMULATED):

OSRAM
Opto Semiconductors


LED Duris E 2835
FWHM / FWTM 74.0° / 94.0°
Efficiency 85 %
Peak intensity 0.7 cd/lm
LEDs/each optic 4
Light colour/type White
Required components:
C17051_DAISY-7X1-SHD-MATT



Light distribution files

OSRAM
Opto Semiconductors


LED Duris E 2835
FWHM / FWTM 74.0° / 94.0°
Efficiency 92 %
Peak intensity 0.7 cd/lm
LEDs/each optic 4
Light colour/type White
Required components:
C17225_DAISY-7X1-SHD-WHT-MATT



Light distribution files

OSRAM
Opto Semiconductors

LED Duris S8
FWHM / FWTM 76.0° / 90.0°
Efficiency 79 %
Peak intensity 0.6 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:
C16872_DAISY-7X1-SHD




Light distribution files

OPTICAL RESULTS (SIMULATED):

OSRAM
Opto Semiconductors


LED OSCONIQ S 5050
FWHM / FWTM 76.0° / 90.0°
Efficiency 78 %
Peak intensity 0.6 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:
C16872_DAISSY-7X1-SHD



Light distribution files

OSRAM
Opto Semiconductors


LED OSLON PURE 1010
FWHM / FWTM 74.0° / 86.0°
Efficiency 86 %
Peak intensity 0.7 cd/lm
LEDs/each optic 4
Light colour/type White
Required components:
C17225_DAISSY-7X1-SHD-WHT-MATT



Light distribution files

OSRAM
Opto Semiconductors

LED OSLON PURE 1010
FWHM / FWTM 74.0° / 92.0°
Efficiency 82 %
Peak intensity 0.6 cd/lm
LEDs/each optic 8
Light colour/type White
Required components:
C16872_DAISSY-7X1-SHD




Light distribution files

OPTICAL RESULTS (SIMULATED):

SAMSUNG


LED LH231B
FWHM / FWTM 73.0° / 92.0°
Efficiency 80 %
Peak intensity 0.6 cd/lm
LEDs/each optic 4
Light colour/type White
Required components:
C17225_DAISY-7X1-SHD-WHT-MATT



Light distribution files

SAMSUNG


LED LH231B
FWHM / FWTM 74.0° / 90.0°
Efficiency 81 %
Peak intensity 0.6 cd/lm
LEDs/each optic 2
Light colour/type White
Required components:
C17225_DAISY-7X1-SHD-WHT-MATT



Light distribution files

SAMSUNG

LED LM101B
FWHM / FWTM 74.0° / 88.0°
Efficiency 86 %
Peak intensity 0.7 cd/lm
LEDs/each optic 4
Light colour/type White
Required components:
C17225_DAISY-7X1-SHD-WHT-MATT




Light distribution files

OPTICAL RESULTS (SIMULATED):

SAMSUNG


LED LM101B
FWHM / FWTM 76.0° / 88.0°
Efficiency 75 %
Peak intensity 0.6 cd/lm
LEDs/each optic 4
Light colour/type White
Required components:
C17051_DAISY-7X1-SHD-MATT



Light distribution files

SAMSUNG


LED LM101B
FWHM / FWTM 75.0° / 88.0°
Efficiency 88 %
Peak intensity 0.7 cd/lm
LEDs/each optic 4
Light colour/type White
Required components:
C18167_DAISY-7X1-SHD-MET



Light distribution files

SAMSUNG

LED LM301D
FWHM / FWTM 74.0° / 90.0°
Efficiency 91 %
Peak intensity 0.7 cd/lm
LEDs/each optic 2
Light colour/type White
Required components:
C17225_DAISY-7X1-SHD-WHT-MATT




Light distribution files

OPTICAL RESULTS (SIMULATED):

SAMSUNG


LED LM301D
FWHM / FWTM 74.0° / 92.0°
Efficiency 91 %
Peak intensity 0.7 cd/lm
LEDs/each optic 4
Light colour/type White
Required components:
C17225_DAISY-7X1-SHD-WHT-MATT



Light distribution files

SAMSUNG


LED LM301Z Plus
FWHM / FWTM 74.0° / 92.0°
Efficiency 75 %
Peak intensity 0.6 cd/lm
LEDs/each optic 4
Light colour/type White
Required components:
C17051_DAISY-7X1-SHD-MATT



Light distribution files

SAMSUNG

LED LM301Z Plus
FWHM / FWTM 74.0° / 92.0°
Efficiency 88 %
Peak intensity 0.7 cd/lm
LEDs/each optic 4
Light colour/type White
Required components:
C18167_DAISY-7X1-SHD-MET




Light distribution files

OPTICAL RESULTS (SIMULATED):

SAMSUNG


LED LM301Z Plus
FWHM / FWTM 74.0° / 92.0°
Efficiency 86 %
Peak intensity 0.7 cd/lm
LEDs/each optic 4
Light colour/type White
Required components:
C17225_DAISY-7X1-SHD-WHT-MATT



Light distribution files




LED SEOUL DC 3030C
FWHM / FWTM 75.0° / 94.0°
Efficiency 80 %
Peak intensity 0.6 cd/lm
LEDs/each optic 4
Light colour/type White
Required components:
C16872_DAISY-7X1-SHD



Light distribution files



LED SEOUL DC 3528
FWHM / FWTM 78.0° / 90.0°
Efficiency 78 %
Peak intensity 0.5 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:
C16872_DAISY-7X1-SHD




Light distribution files

OPTICAL RESULTS (SIMULATED):

TRIDONIC


LED LLE 24x280mm 750lm 8x0 LVD ADV1
 FWHM / FWTM 72.0° / 92.0°
 Efficiency 88 %
 Peak intensity 0.7 cd/lm
 LEDs/each optic 4
 Light colour/type White
 Required components:
 C17533_DAISSY-7X1-SHD-MET-MATT



Light distribution files

TRIDONIC


LED LLE 24x280mm 750lm 8x0 LVD ADV1
 FWHM / FWTM 74.0° / 94.0°
 Efficiency 79 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 4
 Light colour/type White
 Required components:
 C17051_DAISSY-7X1-SHD-MATT



Light distribution files

TRIDONIC

LED LLE 24x280mm 750lm 8x0 LVD ADV1
 FWHM / FWTM 72.0° / 94.0°
 Efficiency 93 %
 Peak intensity 0.7 cd/lm
 LEDs/each optic 4
 Light colour/type White
 Required components:
 C17225_DAISSY-7X1-SHD-WHT-MATT



Light distribution files

GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy

Joensuunkatu 7
FI-24100 SALO
Finland

LEDiL Inc.

228 West Page Street
Suite D
Sycamore IL 60178
USA

Ledil Optics Technology (Shenzhen) Co., Ltd.

405 , Block B
Casic Motor Building
Shenzhen 518057
P.R.CHINA

Local sales and technical support

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)

Shipping locations

Poznan, Poland
Hong Kong, China

Distribution Partners

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)