




# Multilayer Ceramic Chip Capacitor

**Part Number:** 060332000102JXT

**Description:** 0603 200Vdc 1.0nF  $\pm 5\%$  X7R - Non Mag (CTI  $\geq 600$ )

A range of X7R and X5R MLC capacitors with a guaranteed non-magnetic / relative permeability of 1.000 for critical applications such as NMR / MRI. Available with a variety of termination options including FlexiCap™, the world's first commercially available flexible termination.

AF9 suffix parts using palladium silver (PdAg) termination are unplated, suitable for mounting using conductive adhesive.



## Mechanical Specification

Size Code	0603
Length (L1) in mm (")	1.6 +0.25/-0.15 (0.063 +0.01/-0.006)
Width (W) in mm (")	0.8 $\pm$ 0.15 (0.032 $\pm$ 0.006)
Thickness (T) in mm (")	0.9 Max (0.035 Max)
Minimum Termination Band (L2,L3) in mm (")	0.20 (0.008)
Maximum Termination Band (L2,L3) in mm (")	0.40 (0.016)
Termination Material	FlexiCap™ Polymer termination, Copper barrier, Sn Plated Solder (Non-Mag, RoHS compliant)
Solderability	IEC-60068-2-58
Packaging	7" Reel Horizontal Orientation, 4000 per reel

## General Electrical Specification

Rated Voltage	200Vdc
Nominal Capacitance Value	1.0nF
Capacitance Tolerance	$\pm 5\%$
Tangent of Loss Angle (Tan $\delta$ )	$\leq 0.025$
Capacitance and Tan $\delta$ Test Conditions	1.0Vrms @ 1kHz
Voltage Proof	500Vdc
(Voltage applied for 5 secs max. @ 50mA max. charge current. 50% Max, RH)	100.00GOhm @ 100Vdc
Min Insulation Resistance (IR)	X7R - Non Mag (CTI $\geq 600$ )
Dielectric Classification	-55°C / +125°C
Rated Temperature Range	No DC Voltage $\pm 15\%$
Maximum Capacitance Change over Temperature Range	Rated DC Voltage -
Climatic Category (IEC)	55/125/56
Ageing Characteristic	<2% per decade (nominal capacitance is 1000 hour value)

## Knowles Precision Devices - Sales

Europe: KPD-Europe-sales@knowles.com

Asia: KPD-Asia-sales@knowles.com

USA: KPD-NA-sales@knowles.com

[www.knowlescapacitors.com](http://www.knowlescapacitors.com)

This datasheet is for a standard item and is confirmed valid on the date generated, the latest published data for this part may differ and is available at <http://www.knowlescapacitors.com> or by contacting us.

© The information contained on this drawing is confidential and may not be copied in whole or part in any form or disclosed to a third party without the consent of Knowles and any customer mentioned within this specification.

Data is correct to the best of our knowledge, errors and omissions excepted.

Date: Tuesday, June 03, 2025

20250603 080917394UTC



# Multilayer Ceramic Chip Capacitor

**Part Number:** 06032000102JXT

**Description:** 0603 200Vdc 1.0nF  $\pm 5\%$  X7R - Non Mag (CTI  $\geq 600$ )

## Environmental

RoHS Compliant to 2011/65/EC as amended by 2015/863/EU

Compliant

REACH Compliant

247 compliant

California Proposition 65


No exposure risk

## Board Layout

Knowles' conventional 2-terminal chip capacitors can generally be mounted using pad designs in accordance with international specification IPC-7351, Generic Requirements for Surface Mount Design and Land Pattern Standards, but there are some other factors that have been shown to reduce mechanical stress, such as reducing the pad width to less than the chip width. In addition, the position of the chip on the board should be considered.


IPC-7351 pad design

0603		
C	1.60mm	0.063"
Y	0.85mm	0.033"
X	1.00mm	0.039"



## Packaging


Tape packaging information for tape-and-reel parts:



Tape and reel packing of surface mounting chip capacitors for automatic placement are in accordance with IEC60286-3.

## Soldering

Reflow solder in accordance with IPC-A-610. Recommended reflow profile as laid down in IPC/JEDEC J-STD-020.



Wave soldering is also possible, but care must be taken for case sizes 1210 and larger and component thickness >1.0mm. Trials are encouraged.

Hand soldering is not recommended and can lead to component damage through thermal shock.

PdAg terminations are primarily intended for conductive epoxy attachment - they may be suitable for soldering but trials are recommended.

Application notes with mounting and handling guidance are available on request.

Compex

DLI

Johanson MFG

Novacap

Syfer

Voltronics

### Knowles Precision Devices - Sales

Europe: KPD-Europe-sales@knowles.com

This datasheet is for a standard item and is confirmed valid on the date generated, the latest published data for this part may differ and is available at <http://www.knowlescapacitors.com> or by contacting us.

Asia: KPD-Asia-sales@knowles.com

© The information contained on this drawing is confidential and may not be copied in whole or part in any form or disclosed to a third party without the consent of Knowles and any customer mentioned within this specification.

Data is correct to the best of our knowledge, errors and omissions excepted.

USA: KPD-NA-sales@knowles.com

[www.knowlescapacitors.com](http://www.knowlescapacitors.com)

Date: Tuesday, June 03, 2025

20250603 080917394UTC





# Multilayer Ceramic Chip Capacitor

Part Number: 060332000102JXT

Description: 0603 200Vdc 1.0nF  $\pm 5\%$  X7R - Non Mag (CTI  $\geq 600$ )

## DC Bias Characteristics



The curves represent the 'typical worst case' curve – i.e. the typical curve of a 'worst case' component having the most capacitance loss delivered against the specification.

Knowles Precision Devices reserve the right to substitute any component with a similar component of the same or higher specification. In some cases this may mean that the capacitance drop with applied voltage is, in practice, less than the curve shown

Compex

DLI

Johanson MFG

Novacap

Syfer

Voltronics

## Knowles Precision Devices - Sales

Europe: KPD-Europe-sales@knowles.com

Asia: KPD-Asia-sales@knowles.com

USA: KPD-NA-sales@knowles.com

[www.knowlescapacitors.com](http://www.knowlescapacitors.com)

This datasheet is for a standard item and is confirmed valid on the date generated, the latest published data for this part may differ and is available at <http://www.knowlescapacitors.com> or by contacting us.

© The information contained on this drawing is confidential and may not be copied in whole or part in any form or disclosed to a third party without the consent of Knowles and any customer mentioned within this specification.

Data is correct to the best of our knowledge, errors and omissions excepted.

Date: Tuesday, June 03, 2025

20250603 080917394UTC




# Multilayer Ceramic Chip Capacitor

Part Number: 060332000102JXT


Description: 0603 200Vdc 1.0nF ±5% X7R - Non Mag (CTI ≥ 600)

## Typical Capacitance Change vs Temperature




Typical TC Curves for X7R capacitors showing different dielectric types


### Stable X7R Dielectric



### Stable X7R Dielectric — 10nF



### Stable X7R Dielectric



Typical Performance Data - X7R

For part specific data, please contact your local sales office

This data is for reference only and does not constitute a specification.

Compex

DLI

Johanson MFG

Novacap

Syfer

Voltronics

### Knowles Precision Devices - Sales

Europe: KPD-Europe-sales@knowles.com

Asia: KPD-Asia-sales@knowles.com

USA: KPD-NA-sales@knowles.com

[www.knowlescapacitors.com](http://www.knowlescapacitors.com)

This datasheet is for a standard item and is confirmed valid on the date generated, the latest published data for this part may differ and is available at <http://www.knowlescapacitors.com> or by contacting us.

© The information contained on this drawing is confidential and may not be copied in whole or part in any form or disclosed to a third party without the consent of Knowles and any customer mentioned within this specification.

Data is correct to the best of our knowledge, errors and omissions excepted.

Date: Tuesday, June 03, 2025

20250603 080917394UTC