

BGA Heat Sink - High Performance Device Specific - NXP



ATS Part#: **ATS-59001-C1-R0**
 Description: 28.00 x 45.00 x 11.00 mm BGA Heat Sink - High Performance Device Specific - NXP
 Heat Sink Type: **NXP**
 Heat Sink Attachment: **maxiGRIP**
 Equivalent Part Number: **ATS-59001-C2-R0 Discontinued**

**Image above is for illustration purpose only.*

Features & Benefits

- Designed for flip-chip processors such as NXP MPCs
- maxiGRIP™** attachment applies steady, even pressure to the component and does not require holes in the PCB
- Comes preassembled with high performance, phase changing, thermal interface material

Thermal Performance

AIR VELOCITY		@200 LFM 1.0 M/S	@300 LFM 1.5 M/S	@400 LFM 2.0 M/S	@500 LFM 2.5 M/S	@600 LFM 3.0 M/S	@700 LFM 3.5 M/S	@800 LFM 4.0 M/S
THERMAL RESISTANCE	Unducted Flow	4.5 °C/W	3.6 °C/W	3.2 °C/W	2.9 °C/W	2.7 °C/W	2.5 °C/W	2.4 °C/W
	Ducted Flow	3	N/A	N/A	N/A	N/A	N/A	N/A

Product Detail

Schematic Image	Dimension A	Dimension B	Dimension C	Dimension D	TIM	Finish
	28.00 mm	45.00 mm	11.00 mm	59 mm	T766	BLACK-ANODIZED
Notes: - Dimension A and B refer to component size. - Dimension C is the heat sink height from the bottom of the base to the top of the fin field. - ATS-59001-C2-R0 is the exact heat sink assembly with an equivalent thermal interface material (Saint Gobain C1100F). NOTE: Saint Gobain C1100F is discontinued effective 12/31/10. - Thermal performance data are provided for reference only. Actual performance may vary by application. - ATS reserves the right to update or change its products without notice to improve the design or performance. - ATS certifies that this heat sink assembly is RoHS-6 and REACH compliant. - Optional maxiGRIP™ Installation/Removal Tool Set P/N: MGT170 - Contact ATS to learn about custom options available. <i>*Image above is for illustration purpose only.</i>						

For more information, to find a distributor or to place an order, please contact us at 781-769-2800 (North America), sales@qats.com or www.qats.com.

© 2013 Advanced Thermal Solutions, Inc. | 89-27 Access Road | Norwood MA | 02062 | USA



Rev - 230517