

Part Number : 1202300002
Product Description : Brad M23 Signal Connector, Straight Female, Solder Contacts, 6 Poles, Cable Diameter 7.00-12.00mm
Series Number : 120230
Status : Obsolete
Product Category : Industrial Connectors
Engineering Part Number : KAS6S00-555

Obsolete

Documents and Resources

Drawings

1202300002_sd.pdf

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Downloaded from Arrow.com.

Part Details

General

Status	Obsolete
Category	Industrial Connectors
Series	120230
Description	Brad M23 Signal Connector, Straight Female, Solder Contacts, 6 Poles, Cable Diameter 7.00-12.00mm
Comments	Solder Contacts 0.75-2.50mm^2
IP Rating	IP67
Product Name	Brad M23
Type	Field Attachable Connector
UPC	883906298036

Electrical

Current - Maximum per Contact	20.0A
Voltage - Maximum	300V

Physical

Cable Diameter	7.00-12.00mm (.276-.472")
Coupling Type	N/A
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Female
Keyway	None
Material - Connector Body	Nylon
Material - Contact	Brass
Material - Coupling Nut	N/A
Material - Plating Mating	Gold
Orientation	Straight
Poles	6
Temperature Range - Operating	-40° to +125°C
Wire Size (AWG)	N/A

Obsolete

Downloaded from Arrow.com.

This document was generated on Aug 27, 2026

Obsolete

Downloaded from Arrow.com.