



LOADING PATTERN MATING SIDE

f	4	5	5	5	5	5	5	5	5	5	5	5	6	6	6	6	6	6	6	6	6	6
e	4	G	G	G	G	G	G	G	G	G	G	G	G	G	G	G	G	G	G	G	G	G
d	4	G	G	G	G	G	G	G	G	G	G	G	G	G	G	G	G	G	G	G	G	G
c	4	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A
b	4	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A
a	4	K	K	K	K	K	K	K	K	K	K	K	K	K	K	K	K	K	K	K	K	K
z	4	K	K	K	K	K	K	K	K	K	K	K	K	K	K	K	K	K	K	K	K	K
P	0												1									
O	1												5									
S																						


LOADED CONNECTOR ASSEMBLY
(FOR EXAMPLE)



CONTACT OVERVIEW



LAY-OUT P.C.B.-HOLE



HM2P08PNH3W5

LEAD FREE INDICATOR : LF = LEAD FREE
(DIGIT 15 & 16)

PLATING CODE (DIGIT 13 AND 14)
(REF DRW NO. BS,C , 201844 , 003)

NOTES

1. THIS PRODUCT IS CSA APPROVED.
 2. THIS PRODUCT IS UL RECOGNIZED.
 3. MEASURED AT THE BOTTOM.
 4. MATERIAL CONTACT: PHOSPHORBRONZE
HOUSING: CREAM WHITE GLASS FILLED POLYESTER UL-94V0
 5. CONNECTOR PRINTED WITH P/N AND DATE CODE.
 6. FOR ACTUAL CONTACT LOADINGS, SEE LOADING PATTERN MATING SIDE.
 7. SHAPE OF CONNECTOR HOUSING CAN ALTER DEPENDING ON PRODUCTION LOCATION
 8. THE PRODUCT (LF) MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
 9. FOR RECOMMENDED PTH DIMENSIONS REFER DRAWING : BS, A , 201572 , 001
- CATALOG NO: HM2P08PNH3W5----

mat'l. code SEE NOTE 4				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection MM	product family MILLIPACS			
ltr	ecn no	dr	date	tolerances unless otherwise specified		MM	title MPACS 5+2R STR HDR PF CONN TYPE B			
A	106-0070	MINI	07/062006	angles	linear					
				0°±1°						
				dr	MINI K VANDANATH	07/062006	dwg no sheet 1 of 1 size BS, C ,203028, 707 A3			
				engr	BIJU K PAUL	07/062006				
				chr	BIJU K PAUL	07/062006				
				appd	K SOMASUNDARAM	07/062006				
sheet index	revision sheet	A	1				type Product Customer Drawing			