

**Part Number :** [1200895003](#)

**Product Description :** Y Nano-Change (M8) Splitter to Nano-Change (M8) 4 Pole Female to 4 Pole Male

**Series Number :** 120089

**Status :** Active

**Product Category :** Industrial Tees and Splitters

**Engineering Part Number :** 0808 04LMF 00001




## Documents and Resources

### Drawings

[1200895003\\_sd.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Industrial Tees and Splitters
Series	120089
Description	Y Nano-Change (M8) Splitter to Nano-Change (M8) 4 Pole Female to 4 Pole Male
IP Rating	IP67
Product Name	Nano-Change (M8)
Type	Splitter - Solid Body
UPC	883906319472

### Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	60V AC / 75V DC

### Physical

Drop Connector	Nano-Change (M8)
Drop Gender	Male
Keyway	None
Left Trunk Connector	Nano-Change (M8)
Left Trunk Gender	Female
Leg 1 Length	N/A
Leg 2 Length	N/A
Material - Cable Jacket	N/A
Material - Connector Body	PUR
Material - Coupling Nut	Nickel-plated Brass
Net Weight	1.000/g
Poles	3
Right Trunk Connector	Nano-Change (M8)

Right Trunk Gender	Female
Temperature Range - Operating	-20°C to +90°C

---

This document was generated on Dec 25, 2025