







REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	REVISED PER ECR-16-005516	25APR2016	DLD	CJS




ISOMETRIC VIEW
SCALE 10:1



SECTION AF-AF
SCALE 20:1



SECTION N-N
SCALE 20:1



2.06 MAX	2.43	1.00	1.96	FIGURE 2		0.75	18	2098165-4
1.50-1.85	2.23	0.80	1.82	FIGURE 2		0.35-0.50	20-22	2098165-3
2.06 MAX	2.43	1.00	1.96	FIGURE 1		0.75	18	2098165-2
1.50-1.85	2.23	0.80	1.82	FIGURE 1		0.35-0.50	20-22	2098165-1
INSULATION DIAMETER	L	K	J	REELING DIRECTION	FINISH	mm ²	AWG	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN F. KINSEY 16JAN2009	CHK F. KINSEY 16JAN2009	TE Connectivity		
DIMENSIONS:				APVD C. SCHMID 07MAY2009	NAME	CONTACT, FEMALE, 0.64mm CuNiSi, SIDE ORIENTATION Sn PLATE, HIGH FORCE		
mm				TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		
				0 PLC ±		APPLICATION SPEC		
				1 PLC ±		114-13183		
				2 PLC ±		WEIGHT		
				3 PLC ±		CUSTOMER DRAWING		
				4 PLC ±		SCALE 15:1		
ANGLES				FINISH		SHEET 1 OF 1		
MATERIAL				-		REV C		
				-				
				-				

- 1 MATERIAL: 0.2mm THICK CuNiSi ALLOY
- 2 FINISH: PRE-PLATED WITH 1.00µm MIN BRIGHT TIN.
- 3 MATERIAL ID FEATURE IN "DOWN" POSITION.
4. THIS PRODUCT WAS VALIDATED TO GMW3191, DEC 2007, VI, T3, S2.
5. THIS PRODUCT IS DESIGNED TO BE COMPATIBLE WITH SEALED APPLICATIONS.
6. NORMAL FORCE 350 GRAMS REFERENCE.
- 7 STAMPED WITH LETTER "H" TO INDICATE HIGH FORCE ON THIS GENERAL SURFACE.
8. TERMINAL HAS NYE LUBRICANTS NYETACT 568J-50-UV PERFORMANCE LUBE/GREASE APPLIED. THIS IS A WHITISH COLORED LUBE. AMOUNT AND VISIBILITY MAY VARY.