



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	E	PRODUCTION ISSUE	31JAN2019	PNT	MT

a) Part as supplied.



b) Part after unrestricted recovery.

DIMENSIONS in millimetres
[in inches, for reference]

Part No.	H		J		P	R	S	T	JO	HW	JW
	Min	Max	Min	Max	±10%	±10%	±10%	±10%	±10%	±20%	±20%
	a	b	a	b	b	b	b	b	b	b	b
262W014	55 [2.17]	38.7 [1.52]	38 [1.50]	17.2 [.68]	84 [3.31]	25 [.98]	3.0 [.12]	1.5 [.06]	37.5 [1.47]	2.0 [.08]	1.27 [.050]

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

COPYRIGHT - TE Connectivity Ltd.

DIMENSIONS:
mm [INCHES]DWN
PRAVEEN N T 31JAN2019MATERIAL
SEE SHEET 2FINISH
—TOLERANCES UNLESS
OTHERWISE SPECIFIED:CHK
N NAGAR 31JAN2019APVD
M TAYLOR 31JAN2019PRODUCT SPEC
—APPLICATION SPEC
—WEIGHT
—

CUSTOMER DRAWING

TE


TE Connectivity Ltd.

NAME
BOOT, 145 DEGREE WITH LIP

—

SIZE
A4CAGE CODE
00779DRAWING NO
C-262W014-XX-0RESTRICTED TO
—SCALE
DNSSHEET
1 OF 2REV
E

0 PLC	± —
1 PLC	± 0.50[.1]
2 PLC	± 0.25[.01]
3 PLC	± 0.13[.005]
4 PLC	± —
ANGLES	± 1°



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

COMPATIBILITY CHART

Material Dash Number	Material Description	RT Spec	Coating Slash No.	Coating S No.
—3	POLYOLEFIN, SEMI—RIGID	RT—301	/42, /86, /180	S1017; S1048; S1030
—4	POLYOLEFIN, FLEXIBLE	RT—1304	/42, /86, /180	S1017; S1048; S1030
—12	FLUOROELASTOMER, FLEXIBLE	RT—1312	N/A	N/A
—25	ELASTOMER, FLUID RESISTANT	RW—2070	/42, /86, /225	S1017; S1048; S1206
—100	POLYOLEFIN, SEMI—FLEXIBLE ZEROHAL	RW—2082	/86; /180	S1048; S1030

Ordering Information

BASE PART NUMBER 262W014
 MATERIAL DASH NUMBER —XX
 ADHESIVE SLASH NUMBER —/XX
 SEE COMPATIBILITY CHART
 COLOR DESIGNATOR —0

NOTES:


- DIMENSIONS APPEARING IN TABLE ARE AS FOLLOWS:
 a - AS SUPPLIED
 b - AFTER UNRESTRICTED RECOVERY
- COATING IS OPTIONAL.
 AS SUPPLIED DIMENSIONS APPEARING IN TABLE ARE FOR UNCOATED PARTS.
 WHEN COATING IS ADDED, ENTRY DIAMETER WILL BE REDUCED BY 1.5 [.06] MAX.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

COPYRIGHT - TE Connectivity Ltd.

THIS DRAWING IS UNPUBLISHED.

DIMENSIONS: mm [INCHES]	DWN PRAVEEN N T	31JAN2019	MATERIAL —	FINISH —
	CHK N NAGAR	31JAN2019	 TE Connectivity Ltd.	
TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD M TAYLOR	31JAN2019		
0 PLC ± — 1 PLC ± 0.50[.1] 2 PLC ± 0.25[.01] 3 PLC ± 0.13[.005] 4 PLC ± — ANGLES ± 1°	PRODUCT SPEC —	NAME BOOT, 145 DEGREE WITH LIP —		
	APPLICATION SPEC —			
	WEIGHT	SIZE A4	CAGE CODE 00779	DRAWING NO C—262W014—XX—0
	CUSTOMER DRAWING			RESTRICTED TO —
SCALE DNS			SHEET 2	OF 2
REV E				