





REVISION RECORD			
REV	ECN	DESCRIPTION	DRFT DATE



NOTES1:


- UL Standard
 - 1. Rated Voltage/Current : 300V / 15A
 - 2. Torque Value : M2.5, 2.60Lb.in
 - 3. Wire Range : 22~14AWG
- IEC Standard
- 1. Rated Voltage/Current : 250V / 17.5A
 - 2. Torque Value : M2.5, 0.29N.m
 - 3. Wire Range : 0.75~1.5mm²

NOTES2:

- 1. Dimension shall be interpreted per ASME Y14.5-2009
- 2. Pitch : 5.0mm, Poles : N=02~24P
- 3. Stripping length : 5~6mm
- 4. Withstanding Voltage : AC2000V/1min.
- 5. Operating temperature : -30°C~+120°C
- 6. Undimensioned Tolerances:

Pitch Range	In mm		Nominal Dimension		Range		mm	
	Over	TO	Over	TO	Over	TO		
6	10	24	30	60	100	150	0.1/10	
±0.15	±0.20	±0.30	±0.30	±0.50	±0.70	±1.00	±1.30	±2°

7. RoHS Compliance



- 1. (Grey)
- 2. (Blue)
- 3. (Black)
- 4. (Green)
- 5. (Orange)
- 6. (Red)
- 7. (Transparent)
- 8. (Yellow)
- 9. (White)

DETACHED LISTS			
PART NO.:	/	NAME:	DEGSON NINGBO DEGSON ELECTRICAL CO., LTD 宁波高松电子有限公司
APPD:	/	CHKD:	/
DRFT:	/	TITLE:	CUSTOMER DRAWING
THIRD ANGLE PROJECTION		DRAWING NO.:	/
		DO NOT SCALE DRAWING	SCALE
			1:1

A 8 7 6 5 4 3 2 1