

COAXIAL CONNECTOR, BNC, 50 Ohm, Right angle cable plug (male)
16_BNC-50-3-5/133_N

Properties

- Useful for frequently coupled and uncoupled connections
- Available for 50 ohm and 75 ohm applications
- Applicable in frequencies up to 4 GHz



Product configuration		
Interface type	Gender	Standard
BNC	plug	IEC 60169-8_MIL-STD-348A/301_CECC 22120

Interface and material data		
Piece parts	Material	Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Electrical data	
Impedance	50 Ω
Interface frequency	4 GHz

Mechanical data	
Weight	0.0172 kg
Mating cycles	500
Cable entry centre contact	soldered
Cable entry outer contact	crimped

Environmental data	
Operation temperature	-65 °C ... 165°C

COAXIAL CONNECTOR, BNC, 50 Ohm, Right angle cable plug (male)

16_BNC-50-3-5/133_N

Ordering Information Table

Item number	Item description	Packaging type
22540185	16_BNC-50-3-5/133_NE	Single

Suitable cables

Cable group	U7 - 3 mm / 50 Ohm
Suitable cables	RG_58_C/U
	GX_03272

Additional Information

Only as assembly	No
------------------	----

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P3157 / Date of publication: 25.11.2023 / uncontrolled copy