molex



Part Number : 1202300164
Product Description : Brad M23 Signal Connector, Straight Male, Crimp Contacts, 19 (16+3) Poles, Cable Diameter 7.00-12.00mm
Series Number : 120230
Status : Obsolete
Product Category : Circular Industrial Connectors
Engineering Part Number : KASLS06-115

Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Obsolete

Downloaded from Arrow.com.

Part Details

General

Status	Obsolete
Category	Circular Industrial Connectors
Series	120230
Description	Brad M23 Signal Connector, Straight Male, Crimp Contacts, 19 (16+3) Poles, Cable Diameter 7.00-12.00mm
Comments	Crimp Range 0.14-1.00mm² / 0.56-1.50mm²
IP Rating	IP67
Product Name	Brad M23
Type	Field Attachable Connector
UPC	883906299712

Electrical

Current - Maximum per Contact	10.0A, 8.0A
Voltage - Maximum	150V

Physical

Cable Diameter	7.00-12.00mm (.276-.472")
Coupling Type	N/A
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Male
Keyway	None
Material - Connector Body	Nylon
Material - Contact	Brass
Material - Coupling Nut	N/A
Material - Plating Mating	Gold
Net Weight	1.000/g
Orientation	Straight
Poles	19 (16+3)
Temperature Range - Operating	-40° to +125°C
Wire Size (AWG)	N/A

Obsolete

Downloaded from Arrow.com.

This document was generated on May 20, 2026

Obsolete

Downloaded from Arrow.com.