




REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
A	PROPOSAL	APR 07/13	L.CHAN
B	ADD DIMENSION ABOUT HOUSING PEGS	MAR 02/17	L.CHAN




FRONT VIEW



SIDE VIEW



RECOMMENDED PANEL CUTOUT



RECOMMENDED P.C.B. LAYOUT
(COMPONENT SIDE OF BOARD)

LOCATE HOLES
 $\phi .005 [0.13]$
 HOLE DIMENSIONS ARE BASIC

MATERIALS:

CONTACTS: PHOSPHOR BRONZE, SELECTIVELY PLATED WITH 50 MICRO" GOLD ON MATING AREAS. 50 MICRO" MIN. NICKEL OVERALL. 100 MICRO" MIN. MATTE TIN OR GOLD FLASH ON TAILS.

HOUSING: HIGH TEMPERATURE THERMOPLASTIC
 COLOR: BLACK.
 FLAMMABILITY RATING UL 94V-0

SHIELD: COPPER ALLOY

PLATING: NICKEL WITH TIN DIPPED PCB TAILS.

RECOMMENDED SOLDERING TEMPERATURE:

WAVE SOLDERING AT 260°C MAX. FOR 5 SEC MAX.

PART NO.: RJSBE-5380-C1

UNLESS SPECIFIED OTHERWISE		DRAWN	G.HSIA	APR 07/13	Amphenol Canada Corp. www.amphenolcanada.com	
PRIMARY UNITS	INCHES	CHECKED	L.CHAN	APR 07/13		
SECONDARY	MILLIMETERS	M.E. APP'D			TITLE RJ45 MODULAR JACK 8 POSITION, 8 CONTACTS, SHIELDED - RoHS COMPLIANT	
REFERENCE IN PARENTHESES		Q.A. APP'D				
1 DECIMAL PLACE		DWG APP'D			DWG NO. P-RJSBE-5380-C1	
2 DECIMAL PLACES		ENG. REL. NO.				
3 DECIMAL PLACES ±0.015		REF.			CODE ID NO. 03554 DWG SIZE SCALE SHEET 1 OF 1	
ANGULAR DEGREES ±1.5°		THIRD ANGLE PROJECTION				