




2043 Series

P.C.B. Socket 2.54mmX2.54mm(0.100"X0.100")



Material:

Housing: High Temperature Plastic UL94V-0.

Contacts: Copper Alloy.

Electrical Characteristics:

Current Rating: 2 A.

Dielectric Withstanding Voltage: AC 1000V.

Insulator Resistance: 1000MΩ min.



Contact Resistance: 20mΩ max.

Operating Temperature: -55°C~+105°C.


Features:

- * Available in Surface Mount.
- * Low profile 7.10mm (0.280").
- * Choice of alignment post.
- * Dual beam contacts offer ultimate performance.
- * Pass through or Top Entry.
- * Additional plating options available.

Mates with: 2011,2012,2015.



Pass through only available from top side



P.C. Board Layout

Position	4 Thru 80
Dimension	
A	2.54 X No. of Positions /2
B	2.54 X No. of Positions /2-2.54
C	2.54 X No. of Positions /2-5.08

Ordering information

<u>2043-</u>	<u>2</u>	<u>X</u>	<u>40</u>	<u>G</u>	<u>00</u>	<u>D</u>	<u>N</u>	<u>T</u>	-	<u>P</u>
Series	Double Row	No. of Pin Per Row	G: Gold Plated	00: G/F	D: SMD Type	P: With Post N: Without Post	T: Tube Package T: Tape & Reel Package			Blank: W/O Pad P: Plastic Pad

Information including designs, specifications and components may be changed or updated without notice.

A076