





Color: ■ black



Dimensions in mm
R = feed direction



Dimensions in mm

PCB terminal block, 2059 Series, 0° conductor entry to board

This PCB terminal block (item number 2059-322/998-403) is designed for quick and simple connections. It is a universal connector that can be used practically anywhere, for example, as a pluggable PCB connector, panel feedthrough header, connector for rail-mount terminal blocks, or a floating connector for different mounting methods. Our PCB terminal block is rated for 160 V and is designed to handle a rated current of up to 3 A. Ensure that the strip lengths are between 4 mm and 5.5 mm when connecting conductors to this PCB terminal block. Featuring one conductor terminal along with PUSH WIRE®, this product delivers reliable performance. Our trusted PUSH WIRE® connection offers the fastest method for clamping conductors. It utilizes the conductor's stiffness to overcome the clamping spring's contact force. The dimensions are 5.9 x 2.7 x 7.9 mm (width x height x depth). Depending on the type of conductor, this PCB terminal block is ideal for conductor cross sections ranging from 0.14 mm² to 0.34 mm² on one side and for conductor cross sections from 0.5 mm² to 0.5 mm² on the other side. It comes with one level and two clamping points for connecting two potentials / 2 poles. The black housing is made of polyphthalamide (PPA GF) for insulation and the contacts are made of copper alloy. The contact surface is coated with tin. This PCB terminal block is operated with an operating tool. SMD is used to solder the PCB terminal block. The conductor is designed to be inserted into the board at a 0° angle..

Notes	
Note	<p>Application notes:</p> <p>Suitable for lead-free, reflow-soldering profiles per DIN EN 61760-1 and IEC 60068-2-58 up to max. 260°C peak temperature. Due to application-specific variables (component configuration and orientation, type of soldering machine, solder paste), trial runs are recommended to ensure product and process compatibility under actual manufacturing conditions.</p> <p>Depending on reflow soldering temperatures and times, color deviations may occur. These deviations will have no impact on functionality.</p>
Recommendation	<p>Recommendation for stencil:</p> <p>150 µm material thickness; Pattern layout identical to solder pad layout</p>



Electrical data				
Ratings per		IEC/EN 60664-1		
Overvoltage category	III	III	II	
Pollution degree	3	2	2	
Nominal voltage	63 V	160 V	320 V	
Rated surge voltage	2.5 kV	2.5 kV	2.5 kV	
Rated current	3 A	3 A	3 A	
Approvals per				
Rated voltage		250 V		
Rated current		3 A		

Connection data				
Clamping units		2		
Total number of potentials		2		
Number of connection types		1		
Number of levels		1		
Connection 1				
Connection technology		PUSH WIRE®		
Actuation type		Operating tool		
Solid conductor		0.14 ... 0.34 mm² / 26 ... 22 AWG		
Note (conductor cross-section)		For conductors (26 AWG) that are not rigid enough, the clamping unit must be opened using an operating tool.		
Strip length		4 ... 5.5 mm / 0.16 ... 0.22 inches		
Conductor connection direction to PCB		0 °		
Pole number		2		

Connection 2	
Solid conductor	0.5 mm² / 20 AWG
Note (conductor cross-section)	No reconnection of smaller conductor cross-sections (0.5 mm²/20 AWG)
Strip length	6 ... 7.5 mm / 0.24 ... 0.3 inches

Physical data	
Pin spacing	3 mm / 0.118 inches
Width	5.9 mm / 0.232 inches
Height	2.7 mm / 0.106 inches
Depth	7.9 mm / 0.311 inches
Reel diameter of tape-and-reel packaging	330 mm
Tape width	16 mm

PCB contact	
PCB contact	SMD
Solder pin arrangement	over the entire terminal strip (in-line)
Number of solder pins per potential	2

Material data	
Note (material data)	Information on material specifications can be found here
Color	black
Material group	I
Insulation material (main housing)	Polyphthalamide (PPA GF)
Flammability class per UL94	V0
Contact material	Copper alloy
Contact Plating	Tin
Fire load	0.002 MJ
Weight	0.2 g



Environmental requirements

Limit temperature range	-60 ... +105 °C
-------------------------	-----------------

Environmental Testing	
Test specification: Railway applications – Rolling stock – Electronic equipment	DIN EN 50155 (VDE 0115-200):2022-06
Test procedure: Railway applications – Rolling stock equipment – Vibration and shock tests	DIN EN 61373 (VDE 0115-0106):2011-04
Spectrum/Mounting location	Service life test, Category 1, Class A/B
Functional test with noise-like oscillations	Test passed according to Section 8 of the standard
Frequency	f ₁ = 5 Hz to f ₂ = 150 Hz
Acceleration	0.101g (highest test level used for all axes)
Test duration per axis	10 min.
Test directions	X, Y and Z axes
Monitoring of contact faults and interruptions	Passed
Voltage drop measurement before and after each axis	Passed
Simulated service life test through increased levels of noise-like oscillations	Test passed according to Section 9 of the standard
Frequency	f ₁ = 5 Hz to f ₂ = 150 Hz
Acceleration	0.572g (highest test level used for all axes)
Test duration per axis	5 h
Test directions	X, Y and Z axes
Extended testing: Monitoring of contact faults and interruptions	Passed
Extended testing: Voltage drop measurement before and after each axis	Passed
Shock test	Test passed according to Section 10 of the standard
Shock pulse form	Half sine
Acceleration	5g (highest test level used for all axes)
Shock duration	30 ms
Number of shocks (per axis)	3 pos. und 3 neg.
Test directions	X, Y and Z axes
Extended testing: Monitoring of contact faults and interruptions	Passed
Extended testing: Voltage drop measurement before and after each axis	Passed
Vibration and shock stress for rolling stock equipment	Passed



Commercial data


PU (SPU)	21000 (1750) pcs
Packaging type	Box
Country of origin	CH
GTIN	4055143476560
Customs tariff number	85369010000




Product Classification		
UNSPSC		39121409
eCl@ss 10.0		27-14-11-06
eCl@ss 9.0		27-14-11-06
ETIM 9.0		EC001284
ETIM 8.0		EC001284
ECCN		NO US CLASSIFICATION

Environmental Product Compliance		
RoHS Compliance Status		Compliant,No Exemption

Approvals / Certificates					
General approvals			Declarations of conformity and manufacturer's declarations		
					
Approval	Standard	Certificate Name	Approval	Standard	Certificate Name
CCA DEKRA Certification B.V.	EN 60947-7-4	NTR NL-7819	Railway WAGO GmbH & Co. KG	-	Z00004395.000
CCA DEKRA Certification B.V.	EN 60947-7-4	71-111131			
CCA DEKRA Certification B.V.	EN 60838	NTR NL-7720			
KEMA/KEUR DEKRA Certification B.V.	EN 60838	71-106226			

Downloads	
Environmental Product Compliance	
Compliance Search	
Environmental Product Compliance 2059-322/998-403	

Documentation			
Additional Information			
Technical Section	03.04.2019	pdf 2027.26 KB	



CAD/CAE-Data	
CAD data	PCB Design
2D/3D Models 2059-322/998-403	Symbol and Footprint via SamacSys 2059-322/998-403
	Symbol and Footprint via Ultra Librarian 2059-322/998-403

1 Compatible Products
1.1 Optional Accessories
1.1.1 Board-to-board link
1.1.1.1 Board-to-board link



Item No.: 2059-902
Board-to-Board Link; Pin spacing 3 mm;
2-pole; Length: 15.3 mm; white



Item No.: 2059-902/018-000
Board-to-Board Link; Pin spacing 3 mm;
2-pole; Length: 17.5 mm; white



Item No.: 2059-902/021-000
Board-to-Board Link; Pin spacing 3 mm;
2-pole; Length: 20.5 mm; white

1.1.2 Tool
1.1.2.1 Operating tool



Item No.: 206-859
Operating tool; for 2059 Series; multico-
loured



Item No.: 2059-189
Operating tool; made of insulating materi-
al; for 2059 Series

Installation Notes
Conductor termination



Insert solid conductors via push-in termi-
nation.

Conductor termination



Easy conductor removal, e.g., via operating
tool (Item No. 206-859) or “twist & pull”
(max. 10 x, no reconnection of smaller
conductors possible)

Subject to changes. Please also observe the further product documentation!

Current addresses can be found at: www.wago.com