


PC 5/ 4-STF1-7,62 BK BDWH:NZ 1CP - PCB connector



1700424  
<https://www.phoenixcontact.com/ae/products/1700424>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



PCB connector, nominal cross section: 6 mm<sup>2</sup>, color: black, nominal current: 32 A, rated voltage (III/2): 1000 V, contact surface: Sn, contact connection type: Socket, number of rows: 1, number of positions: 4, product range: PC 5/..-STF1, pitch: 7.62 mm, connection method: Screw connection with tension sleeve, screw head form: H1L Slotted Phillips recess, conductor/PCB connection direction: 0 °, locking clip: - without locking clip, plug-in system: COMBICON PC 5, locking: Screw locking mechanism, mounting method: Screw flange, type of packaging: packed in cardboard

Your advantages

- Well-known connection principle allows worldwide use
- Low temperature rise, thanks to maximum contact force
- Allows connection of two conductors
- Integrated double steel spring provides additional safety in the event of temperature and power fluctuations
- 600 V UL approval in the smallest of dimensions
- Screwable flange for superior mechanical stability

Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1700424       |
| Packing unit                         | 50 pc         |
| Minimum order quantity               | 1 pc          |
| Sales key                            | AA            |
| Product key                          | AADABB        |
| GTIN                                 | 4046356666718 |
| Weight per piece (including packing) | 21.113 g      |
| Weight per piece (excluding packing) | 19.946 g      |
| Customs tariff number                | 85366990      |
| Country of origin                    | DE            |

# PC 5/ 4-STF1-7,62 BK BDWH:NZ 1CP - PCB connector



1700424

<https://www.phoenixcontact.com/ae/products/1700424>

## Technical data

### Product properties

|                     |                       |
|---------------------|-----------------------|
| Product type        | PCB connector         |
| Product family      | PC 5/...-STF1         |
| Product line        | COMBICON Connectors L |
| Number of positions | 4                     |
| Pitch               | 7.62 mm               |
| Number of rows      | 1                     |
| Mounting type       | Screw flange          |

### Electrical properties

#### Properties

|                             |        |
|-----------------------------|--------|
| Nominal current $I_N$       | 32 A   |
| Nominal voltage $U_N$       | 1000 V |
| Contact resistance          | 0.4 mΩ |
| Rated voltage (III/3)       | 1000 V |
| Rated surge voltage (III/3) | 8 kV   |
| Rated voltage (III/2)       | 1000 V |
| Rated surge voltage (III/2) | 8 kV   |
| Rated voltage (II/2)        | 1000 V |
| Rated surge voltage (II/2)  | 6 kV   |

### Connection data

#### Connection technology

|                         |                   |
|-------------------------|-------------------|
| Type                    | Standard          |
| Connector system        | COMBICON PC 5     |
| Nominal cross section   | 6 mm <sup>2</sup> |
| Contact connection type | Socket            |

#### Interlock

|                   |                         |
|-------------------|-------------------------|
| Locking type      | Screw locking mechanism |
| Mounting type     | Screw flange            |
| Tightening torque | 0.3 Nm ... 0.7 Nm       |

#### Conductor connection

|                                                                       |                                            |
|-----------------------------------------------------------------------|--------------------------------------------|
| Connection method                                                     | Screw connection with tension sleeve       |
| Conductor/PCB connection direction                                    | 0 °                                        |
| Conductor cross-section rigid                                         | 0.2 mm <sup>2</sup> ... 10 mm <sup>2</sup> |
| Conductor cross-section flexible                                      | 0.2 mm <sup>2</sup> ... 6 mm <sup>2</sup>  |
| Conductor cross-section AWG                                           | 24 ... 10                                  |
| Conductor cross-section flexible, with ferrule without plastic sleeve | 0.25 mm <sup>2</sup> ... 6 mm <sup>2</sup> |
| Conductor cross-section, flexible, with ferrule, with plastic sleeve  | 0.25 mm <sup>2</sup> ... 4 mm <sup>2</sup> |

# PC 5/ 4-STF1-7,62 BK BDWH:NZ 1CP - PCB connector



1700424

<https://www.phoenixcontact.com/ae/products/1700424>

|                                                                                           |                                                                                                        |
|-------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------|
| 2 conductors with same cross section, solid                                               | 0.2 mm² ... 2.5 mm²                                                                                    |
| 2 conductors with same cross section, flexible                                            | 0.2 mm² ... 4 mm²                                                                                      |
| 2 conductors with same cross section, flexible, with ferrule without plastic sleeve       | 0.25 mm² ... 1.5 mm²                                                                                   |
| 2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve | 0.25 mm² ... 2.5 mm²                                                                                   |
| Cylindrical gauge a x b / diameter                                                        | 3.6 mm x 3.1 mm / 3.4 mm                                                                               |
| Stripping length                                                                          | 10 mm                                                                                                  |
| Drive form screw head                                                                     | Slotted Phillips recess (H1L)                                                                          |
| Tightening torque                                                                         | 0.5 Nm ... 0.8 Nm ( $\leq 4 \text{ mm}^2$ is 0.5 Nm to 0.6 Nm, $> 4 \text{ mm}^2$ is 0.7 Nm to 0.8 Nm) |

## Material specifications

### Material data - contact

|                                          |                                                                                  |
|------------------------------------------|----------------------------------------------------------------------------------|
| Note                                     | WEEE/RoHS-compliant, free of whiskers according to IEC 60068-2-82/JEDEC JESD 201 |
| Contact material                         | Cu alloy                                                                         |
| Surface characteristics                  | hot-dip tin-plated                                                               |
| Metal surface terminal point (top layer) | Tin (4 - 8 $\mu\text{m}$ Sn)                                                     |
| Metal surface contact area (top layer)   | Tin (4 - 8 $\mu\text{m}$ Sn)                                                     |

### Material data - housing

|                                                                   |              |
|-------------------------------------------------------------------|--------------|
| Color (Housing)                                                   | black (9005) |
| Insulating material                                               | PA           |
| Insulating material group                                         | I            |
| CTI according to IEC 60112                                        | 600          |
| Flammability rating according to UL 94                            | V0           |
| Glow wire flammability index GWFI according to EN 60695-2-12      | 850          |
| Glow wire ignition temperature GWIT according to EN 60695-2-13    | 775          |
| Temperature for the ball pressure test according to EN 60695-10-2 | 125 °C       |

## Dimensions

|                     |                                                                                      |
|---------------------|--------------------------------------------------------------------------------------|
| Dimensional drawing |  |
| Pitch               | 7.62 mm                                                                              |
| Width [w]           | 45.7 mm                                                                              |
| Height [h]          | 19.7 mm                                                                              |
| Length [l]          | 35.25 mm                                                                             |

## Mounting

# PC 5/ 4-STF1-7,62 BK BDWH:NZ 1CP - PCB connector



1700424

<https://www.phoenixcontact.com/ae/products/1700424>

## Flange

|                   |                   |
|-------------------|-------------------|
| Tightening torque | 0.3 Nm ... 0.7 Nm |
|-------------------|-------------------|

## Notes

|                    |                                                                                                                                                                                          |
|--------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Notes on operation | In accordance with IEC 61984, COMBICON connectors have no switching power (COC). During designated use, they must not be plugged in or disconnected when carrying voltage or under load. |
|--------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

## Mechanical tests

### Test for conductor damage and slackening

|               |                     |
|---------------|---------------------|
| Specification | IEC 60999-1:1999-11 |
| Result        | Test passed         |

### Pull-out test

|                                                                             |                                         |
|-----------------------------------------------------------------------------|-----------------------------------------|
| Specification                                                               | IEC 60999-1:1999-11                     |
| Conductor cross-section/conductor type/tractive force setpoint/actual value | 0.2 mm <sup>2</sup> / solid / > 10 N    |
|                                                                             | 0.2 mm <sup>2</sup> / flexible / > 10 N |
|                                                                             | 10 mm <sup>2</sup> / solid / > 90 N     |
|                                                                             | 6 mm <sup>2</sup> / flexible / > 80 N   |
|                                                                             | 6 mm <sup>2</sup> / solid / > 80 N      |
|                                                                             | 4 mm <sup>2</sup> / flexible / > 60 N   |

### Insertion and withdrawal forces

|                                     |                        |
|-------------------------------------|------------------------|
| Specification                       | IEC 60512-13-2:2006-02 |
| Result                              | Test passed            |
| No. of cycles                       | 50                     |
| Insertion strength per pos. approx. | 8 N                    |
| Withdraw strength per pos. approx.  | 6.5 N                  |

### Torque test

|               |                     |
|---------------|---------------------|
| Specification | IEC 60999-1:1999-11 |
|---------------|---------------------|

### Resistance of inscriptions

|               |                        |
|---------------|------------------------|
| Specification | IEC 60068-2-70:1995-12 |
| Result        | Test passed            |

### Polarization and coding

|               |                        |
|---------------|------------------------|
| Specification | IEC 60512-13-5:2006-02 |
| Result        | Test passed            |

### Visual inspection

|               |                       |
|---------------|-----------------------|
| Specification | IEC 60512-1-1:2002-02 |
| Result        | Test passed           |

### Dimension check

|               |                       |
|---------------|-----------------------|
| Specification | IEC 60512-1-2:2002-02 |
| Result        | Test passed           |

# PC 5/ 4-STF1-7,62 BK BDWH:NZ 1CP - PCB connector



1700424

<https://www.phoenixcontact.com/ae/products/1700424>

## Environmental and real-life conditions

### Vibration test

|                        |                             |
|------------------------|-----------------------------|
| Specification          | IEC 60068-2-6:2007-12       |
| Frequency              | 10 - 150 - 10 Hz            |
| Sweep speed            | 1 octave/min                |
| Amplitude              | 0.35 mm (10 Hz ... 60.1 Hz) |
| Acceleration           | 5g (60.1 Hz ... 150 Hz)     |
| Test duration per axis | 2.5 h                       |
| Test directions        | X-, Y- and Z-axis           |

### Durability test

|                                        |                     |
|----------------------------------------|---------------------|
| Specification                          | IEC 60512-5:1992-08 |
| Impulse withstand voltage at sea level | 7.3 kV              |
| Contact resistance $R_1$               | 0.4 mΩ              |
| Contact resistance $R_2$               | 0.5 mΩ              |
| Insertion/withdrawal cycles            | 50                  |

### Climatic test

|                                   |                                                                           |
|-----------------------------------|---------------------------------------------------------------------------|
| Specification                     | ISO 6988:1985-02                                                          |
| Corrosive stress                  | 0.2 dm <sup>3</sup> SO <sub>2</sub> on 300 dm <sup>3</sup> /40 °C/1 cycle |
| Thermal stress                    | 100 °C/168 h                                                              |
| Power-frequency withstand voltage | 3.31 kV                                                                   |

### Shocks

|                 |                                   |
|-----------------|-----------------------------------|
| Specification   | IEC 60068-2-27:2008-02            |
| Pulse shape     | Semi-sinusoidal                   |
| Acceleration    | 30g                               |
| Shock duration  | 18 ms                             |
| Test directions | X-, Y- and Z-axis (pos. and neg.) |

### Ambient conditions

|                                         |                                                     |
|-----------------------------------------|-----------------------------------------------------|
| Ambient temperature (operation)         | -40 °C ... 100 °C (dependent on the derating curve) |
| Ambient temperature (storage/transport) | -40 °C ... 70 °C                                    |
| Relative humidity (storage/transport)   | 30 % ... 70 %                                       |
| Ambient temperature (assembly)          | -5 °C ... 100 °C                                    |

## Electrical tests

### Thermal test | Test group C

|                            |                       |
|----------------------------|-----------------------|
| Specification              | IEC 60512-5-1:2002-02 |
| Tested number of positions | 12                    |

### Insulation resistance

|                                              |                       |
|----------------------------------------------|-----------------------|
| Specification                                | IEC 60512-3-1:2002-02 |
| Insulation resistance, neighboring positions | >10 <sup>12</sup> Ω   |

# PC 5/ 4-STF1-7,62 BK BDWH:NZ 1CP - PCB connector



1700424

<https://www.phoenixcontact.com/ae/products/1700424>

## Air clearances and creepage distances |

|                                                        |                     |
|--------------------------------------------------------|---------------------|
| Specification                                          | IEC 60664-1:2007-04 |
| Insulating material group                              | I                   |
| Comparative tracking index (IEC 60112)                 | CTI 600             |
| Rated insulation voltage (III/3)                       | 1000 V              |
| Rated surge voltage (III/3)                            | 8 kV                |
| minimum clearance value - non-homogenous field (III/3) | 8 mm                |
| minimum creepage distance (III/3)                      | 12.5 mm             |
| Rated insulation voltage (III/2)                       | 1000 V              |
| Rated surge voltage (III/2)                            | 8 kV                |
| minimum clearance value - non-homogenous field (III/2) | 8 mm                |
| minimum creepage distance (III/2)                      | 8 mm                |
| Rated insulation voltage (II/2)                        | 1000 V              |
| Rated surge voltage (II/2)                             | 6 kV                |
| minimum clearance value - non-homogenous field (II/2)  | 5.5 mm              |
| minimum creepage distance (II/2)                       | 5.5 mm              |

## Packaging specifications

|                   |                     |
|-------------------|---------------------|
| Type of packaging | packed in cardboard |
|-------------------|---------------------|

# PC 5/ 4-STF1-7,62 BK BDWH:NZ 1CP - PCB connector



1700424

<https://www.phoenixcontact.com/ae/products/1700424>

## Drawings

Diagram



Type: PC 5/...-STF1-7,62 with PC 5/...-GF-7,62  
Conductor cross-section: 6 mm<sup>2</sup>

Diagram




Type: PC 5/...-STF1-7,62 with PC 5/...-GF-7,62  
Conductor cross-section: 10 mm<sup>2</sup>

# PC 5/ 4-STF1-7,62 BK BDWH:NZ 1CP - PCB connector




1700424

<https://www.phoenixcontact.com/ae/products/1700424>



Type: PC 5/...-STF1-7,62 with PCV 4/...-G-7,62 and BF-PC 4  
Conductor cross-section: 4 mm<sup>2</sup>




Type: PC 5/...-STF1-7,62 with PCV 4/...-G-7,62 and BF-PC 4  
Conductor cross-section: 6 mm<sup>2</sup>

# PC 5/ 4-STF1-7,62 BK BDWH:NZ 1CP - PCB connector




1700424

<https://www.phoenixcontact.com/ae/products/1700424>



Type: PC 5/...-ST(F)1-7,62 with PC 5/...-GU(F)-7,62

Conductor cross-section: 6 mm<sup>2</sup>



Type: PC 5/...-ST(F)1-7,62 with PC 5/...-G(F)U-7,62


Conductor cross-section: 10 mm<sup>2</sup>

# PC 5/ 4-STF1-7,62 BK BDWH:NZ 1CP - PCB connector




1700424

<https://www.phoenixcontact.com/ae/products/1700424>



Type: PC 5/...-STF1-7,62 with PC 4/...-G-7,62 and BF-PC 4  
Conductor cross-section: 4 mm<sup>2</sup>



Type: PC 5/...-STF1-7,62 with PC 4/...-G-7,62 and BF-PC 4  
Conductor cross-section: 6 mm<sup>2</sup>


# PC 5/ 4-STF1-7,62 BK BDWH:NZ 1CP - PCB connector



1700424


<https://www.phoenixcontact.com/ae/products/1700424>

Diagram



Type: PC 5/...-STF1-7,62 with PCV 5/...-GF-7,62

Diagram



Type: PC 5/...-STF1-7,62 with PCVK 4-7,62 and PCVK 4-7,62-F

# PC 5/ 4-STF1-7,62 BK BDWH:NZ 1CP - PCB connector



1700424  
<https://www.phoenixcontact.com/ae/products/1700424>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/ae/products/1700424>

|                                                                                                                                                       |                       |                       |                   |                             |
|-------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
| <div> <b>cULus Recognized</b><br/>Approval ID: E60425-19920722</div> |                       |                       |                   |                             |
|                                                                                                                                                       | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| B                                                                                                                                                     |                       |                       |                   |                             |
| Multi-conductor connection                                                                                                                            | 600 V                 | 41 A                  | 24 - 12           | -                           |
| Screw connection                                                                                                                                      | 600 V                 | 41 A                  | 24 - 8            | -                           |
| C                                                                                                                                                     |                       |                       |                   |                             |
| Multi-conductor connection                                                                                                                            | 600 V                 | 41 A                  | 24 - 12           | -                           |
| Screw connection                                                                                                                                      | 600 V                 | 41 A                  | 24 - 8            | -                           |

# PC 5/ 4-STF1-7,62 BK BDWH:NZ 1CP - PCB connector



1700424

<https://www.phoenixcontact.com/ae/products/1700424>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27460202 |
| ECLASS-15.0 | 27460202 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002638 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# PC 5/ 4-STF1-7,62 BK BDWH:NZ 1CP - PCB connector



1700424

<https://www.phoenixcontact.com/ae/products/1700424>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.0 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.142 kg CO2e |
|---------|---------------|

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Middle East FZ LLC  
1201N-1206N, Dubai Science Park Towers – North  
P.O. Box 345002, Dubai, United Arab Emirates  
(+971) 4 437-0324  
[info-me@phoenixcontact.com](mailto:info-me@phoenixcontact.com)