

Keylock switch, 16.2 mm, round collar, 1 NO, Gold, Solder terminal, 2 x 90°, latching, key removal position 0

DISCONTINUED



fields of application

- Measurement-control-regulation
- Signalling systems
- Industrial robots

special features

- max. 35 V
- 100 mA
- Scope of delivery: 2 keys



description

The locking systems we use were created according to the DIN EN 1303 standard by well-known lock manufacturers. They are open, mechanical systems which, depending on the environmental conditions, require occasional maintenance (e.g. greasing & oiling) by the machine or system operator.

Keylock switches for mounting hole diameter of 16.2 mm, designed to fit LUMOTAST FK and LUMOTAST 75 IP40.

technical data

➤ general

Collar shape	round
Operating temperature, min.	-25 °C
Storage temperature, min.	-40 °C
Operating temperature, max.	70 °C
Storage temperature, max.	80 °C
illuminated	No
Soldering time for manual soldering, max.	3 sec
Soldering temperature for manual soldering	350 °C
Soldering	Manual soldering
Packaging	Box
Packaging unit	2 pcs.
Operating life	50,000 cycles
B10	65,000 cycles
MOQ order	10 pcs.
RoHS compliant	Yes
REACH compliant	Yes

direct links

- RAFI eCatalog

➤ mounting diameters

Mounting hole	16.2 mm
Mounting depth	39.5 mm
Installation height	7.5 mm

The information in this data sheet only contains general descriptions and / or performance features, which may not apply precisely as described to the respective application, and which may change due to further product enhancements. The technical data, illustrations and other information about our products are the mere results of individual technical testing. These descriptions and other product features are only binding if they expressly agreed upon at the time of the conclusion of a binding contract. In all other cases, we reserve the right to make technical changes as well as changes of availability. Pictures and other graphic illustrations are approximations only. All product names may be trademarks or brand names of the RAFI Group or any other sub-supplier of RAFI. The use of such by any third parties for their own purposes may infringe the rights of the respective entity holding those rights.

date: Sep 24, 2022 page: 1/2

RAFI GmbH & Co. KG

Ravensburger Str. 128-134
88276 Berg / Ravensburg
Germany
www.rafi-group.com,
info.headquarters@rafi-group.com

Outside dimension, length	18 mm
Outside dimension, width	18 mm
Collar dimension	18 mm

> mechanical data

Actuation function	latching
Operating torque, max.	1.8 Nm
Contact function	1 NO
Contact system	Bridge-sliding contact
Contact material	Gold
Locking position	5001
Key lock	Micromec
Key removal position	0
Rotating angle	2 x 90°
Fixing	Threaded ring
Threaded ring torque, max.	0.8 Nm
Terminal on the rear	Solder terminal
Solderability	Yes

> electrical data

Rated voltage, min.	5.000 V
Rated voltage, max.	35 V
Rated current, min.	0.05 A
Rated current, max.	0.1 A