

YSM14, Uninsulated Parallel Splice For 477 - 4,107 cmils

By Burndy
Catalog # [YSM14](#)



Uninsulated Parallel Splice For 477 - 4,107 cmils

Features

- Seamless tubing
- Beveled barrel for ease of wire entry
- Tin plated
- Parallel design results in only one crimp necessary
- Uninsulated barrel provides an economical termination solution when insulation is not specified

Application

HYLINK Type YSM seamless parallel splice connector permits wires to be laid parallel inside the connector and spliced together with the BURNDY family of HYTOOL installation tooling

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	No
Buy America(n) Qualified	Contact Manufacturer

Conductor

Conductor Size	477 - 4,107 cmils
Conductor - Copper Str Size	<ul style="list-style-type: none"> • 20 AWG • 18 AWG • 16 AWG • 14 AWG
Conductor - Copper Str Size Range	20 AWG-14 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Configuration

Connector Type	Parallel Splice
----------------	-----------------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Outside Diameter inch	0.16 in
Package Height	0.000 in
Dimension - Strip Length inch	5/16
Dimension - Length Overall inch	0.25 in

General

Sub Brand	HYLINK
Trade Name	HYLINK™
Plated	Y
Feature - Barrel Style	Chamfered
Type	YSM
UPC 12 Digit	781810805817
UPC 14 Digit GTIN	00781810805817
Material	Copper
Plating Type	Tin
UPC	781810805817

Logistics

Minimum Pack Quantity	1000
Carton Quantity	1000

Operational

Temperature Rating	90
--------------------	----

Product Assets

[Catalog \[English\]](#)