

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -,- .
© COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST
AD	00


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	F1	REVISED PER ECO-11-004587	11MAR11	RK	HMR





SECTION A–A
ROTATED 90° CW
INSULATION RANGE .054 MAX



SECTION B–B
ROTATED 90° CW
WIRE RANGE #22–#26

1. .000100–.000200 BRIGHT TIN–LEAD OVER .000030 NICKEL ENTIRE CONTACT
2. .000015 GOLD IN CONTACT AREA, .000050–.000100 BRIGHT TIN–LEAD IN CRIMP AREA, ALL OVER .000030 NICKEL ENTIRE CONTACT
3. .000030 GOLD IN CONTACT AREA, .000050–.000100 BRIGHT TIN–LEAD IN CRIMP AREA, ALL OVER .000030 NICKEL ENTIRE CONTACT
4. POINT OF MEASUREMENT FOR PLATING THICKNESS
5. GOLD PLATING NOT REQUIRED IN THIS AREA
6. .000100–.000200 BRIGHT TIN OVER .000030 NICKEL ENTIRE CONTACT.
7. .000015 GOLD IN CONTACT AREA, .000050–.000100 BRIGHT TIN IN CRIMP AREA, ALL OVER .000030 NICKEL ENTIRE CONTACT.
8. .000030 GOLD IN CONTACT AREA, .000050–.000100 BRIGHT TIN IN CRIMP AREA, ALL OVER .000030 NICKEL ENTIRE CONTACT.
9. .000100–.000200 MATTE TIN OVER .000030 NICKEL ENTIRE CONTACT.
10. .000015 GOLD IN CONTACT AREA, .000050–.000100 MATTE TIN IN CRIMP AREA, ALL OVER .000030 NICKEL ENTIRE CONTACT.
11. .000030 GOLD IN CONTACT AREA, .000050–.000100 MATTE TIN IN CRIMP AREA, ALL OVER .000030 NICKEL ENTIRE CONTACT.

	LOOSE PIECE PART NUMBER	PART NUMBER
11	5-104505-7	5-104505-6
10	5-104505-5	5-104505-4
9	5-104505-3	5-104505-2
8	1-104505-3	1-104505-2
7	1-104505-1	1-104505-0
6	104505-9	104505-8
3	104505-7	104505-6
2	104505-5	104505-4
1	104505-3	104505-2
FINISH		

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± –
1 PLC ± –
2 PLC ± –
3 PLC ± .005
4 PLC ± –
ANGLES ± –

MATERIAL: PHOS BRONZE
FINISH: SEE TABLE

DWN D KEITZER 12-14-88
CHK S. SHUEY 12-15-88
APVD C.SINISI 12-16-88
PRODUCT SPEC —
APPLICATION SPEC —
WEIGHT —

TE Connectivity

NAME: PIN CONTACT, AMPMODU, MTE

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-104505	—

CUSTOMER DRAWING | SCALE 10:1 | SHEET 1 OF 1 | REV F1

104505

1471-9 (3/11)

Downloaded from Arrow.com.