
Part Number : 930370501
Product Description : 2.50mm Pitch Appli-Mate RAST 2.5 IDT Housing, Female, 4 Circuits, Beaded Terminal, Locking Pips, All Position Keys, Slotted Endwalls, Glow-Wire Capable
Series Number : 93037
Status : Active
Product Category : Connector Housings



Documents and Resources

Drawings

930370501_sd.pdf

STEP AP242

SOLIDWORKS

Creo

Specifications

990330008-000.pdf

PK-90871-001-001.pdf

PS-99020-0040-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains 1,1'-(Ethane-1,2-diyl)bis[pentabromobenzene] per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Downloaded from Arrow.com.

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	93037
Description	2.50mm Pitch Appli-Mate RAST 2.5 IDT Housing, Female, 4 Circuits, Beaded Terminal, Locking Pips, All Position Keys, Slotted Endwalls, Glow-Wire Capable
Comments	Various possibilities for temperature range: 4 Amp:-20°C to + 60°C with header 2 Amp:-20°C to +120°C double sided PCB or Header 2 Amp: -20°C to +110°C single sided PCB; This Molex product is manufactured from material that has the following ratings, tested by independent agencies: a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13. b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60695-2-12 and

Downloaded from Arrow.com.

	hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition - household and similar electrical appliances - safety, section 30 Resistance to heat and fire. The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable product end-use standard(s). If it is determined during the customer's evaluation of suitability, that higher performance is required, please contact Molex for possible product options.
Product Name	RAST 2.5
UPC	883906528287

Agency

CSA	LR19980
UL	E29179

Electrical

Voltage - Maximum	32V AC

Physical

Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Natural (White)
Durability (mating cycles max)	10
Gender	Female
Glow-Wire Capable	Yes
Lock to Mating Part	Yes

Downloaded from Arrow.com.

Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyamide
Net Weight	1.808/g
Number of Rows	1
Packaging Type	Tray
Panel Mount	No
Pitch - Mating Interface	2.50mm
Pitch - Termination Interface	2.50mm
Plating min - Mating	1.016µm
Plating min - Termination	1.016µm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-20° to +110°C, -20° to +120°C, -20° to +60°C
Termination Interface Style	IDT or Pierce
Wire Size (AWG)	22

Mates With / Use With

Use with Part(s)

Description	Part Number
Use With	RAST standard Interface

Application Tooling

Global

Description	Part Number
RAST 2.5 and R-Power Semi-Automatic IDC Machine	2166580100
Hand Tool for Appli-Mate RAST 2.5, RAST Signal, and R-Power Connectors	638272900

Downloaded from Arrow.com.

This document was generated on Apr 13, 2026

Downloaded from Arrow.com.