



Certifications & Ratings

- RoHS compliant

Application

The 606 Series LED Panel Mount Indicators are designed for a variety of applications such as:

- Main power indication
- Remote power indication
- Status indication
- Maintenance and warning indication
- Instrumentation
- ... and many more!

Dimensions

inches [mm]

Figure 1




Figure 2





Figure 3



Mechanical Information

Mounting Hole Size: 0.244" (6.2 mm)

Max Panel Thickness: 0.138" (3.5 mm)

Mounting Torque: 0.362 lbs/ft (5 kg/cm) torque

Specifications

Voltage Options: 2 VDC (resistor required)
6 and 12 VDC / bi-color
(no resistor required)

Operating temp: -25 °C to +85 °C (-13 °F to +185 °F)

Storage Temp: -25 °C to +100 °C (-13 °F to +212 °F)

Electrical Connection: Through hole and 26AWG wire leads
(bi-color only)

Housing: Brass—Chrome Plated


Terminals: Copper—Nickel Plated

Wire Leads: 6" on bi-color only

Lock washer: Iron—Nickel Plated

Nut: Brass—Nickel Plated

Figure 4



Ordering Information 606 Series

Part Number	Color	Voltage (VDC)	Current (mA)	Typical Intensity* (mcd)	LED Position	Finish	Figure
606-1111-110F	Red	2	5	45	Protruding	Chrome	1
606-1211-110F	Green		15	70			
606-1311-110F	Yellow			60			
606-1215-110F	Green			70			1 w/ Wire Leads
606-1415-110F	Red/Green	3	10	40/50			2
606-1415-120F	Red/Green	6		40/50			
606-1415-130F	Red/Green	12		40/50			
606-2111-110F	Red	2	5	45	Recess		3
606-2211-110F	Green		15	70			
606-2311-110F	Yellow			60			
606-2415-110F	Red/Green		10	40/50			4
606-2415-120F	Red/Green	6		40/50			
606-2415-130F	Red/Green	12		40/50			

*Bi-color intensity (Red/Green)