


SPECIFICATION CONTROL DRAWING		7724C3864
CHEMINAX	77 OHM, AWG 24, 19 STRANDS OF AWG 36, OPTIMIZED DOUBLE SHIELDS, DATA BUS CABLE, MIL-STD-1553	Date: 9-21-22 Revision: F
THIS SPECIFICATION SHEET FORMS A PART OF THE LATEST ISSUE OF RAYCHEM SPECIFICATION 1200.		
CONSTRUCTION DETAILS		ELECTRICAL CHARACTERISTICS
DIMENSIONS ARE NOMINAL VALUES IN INCHES, UNLESS OTHERWISE DESIGNATED.  CONDUCTORS AWG 24, 19 Strands of AWG 36, Silver-Coated High- Strength Copper Alloy DIELECTRICS Radiation-Crosslinked, Modified ETFE Colors - Light Blue/White FILLERS Radiation-Crosslinked, Modified ETFE 1st SHIELD AWG 38, Tin-Coated Copper, Optimized 2nd SHIELD AWG 38, Tin-Coated Copper, Optimized JACKET Zerohal		CHARACTERISTIC IMPEDANCE 77 ± 5 ohms, Method C at 1 MHz MUTUAL CAPACITANCE 30.0 pF/ft. (maximum) ATTENUATION 1.4 dB/100 ft. (maximum) at 1 MHz SURFACE TRANSFER IMPEDANCE 10 milliohms/meter (maximum) at 30 MHz
		ADDITIONAL REQUIREMENTS
		COMPONENT WIRE PRIOR TO CABLING (Test procedures per SAE AS22759)
		CONDUCTOR RESISTANCE 26.5 ohms/1000 ft. (nominal) CROSSLINKING PROOF TEST 300 ± 3°C for 1 hour, .625 inch mandrel, .375 lb, 2.5 kV dielectric test INSULATION (DIELECTRIC) ELONGATION 50% (minimum) TENSILE STRENGTH 5000 lbf/in ² (minimum) INSULATION FLAWS SPARK TEST 3.0 kV (rms) IMPULSE TEST 8.0 kV (peak) INSULATION RESISTANCE 5000 megohms for 1000 ft. (minimum) LOW TEMPERATURE-COLD BEND -65 ± 3°C for 4 hours, .750 inch mandrel, 1.00 lb, 2.5 kV dielectric test SHRINKAGE 200 ± 3°C for 1 hour, .125 inch (maximum) in 12 inches
		FINISHED CABLE
		CABLE LAY LENGTH .75 inch (minimum), 1.25 inches (maximum) FLAMMABILITY Method B, except 45 seconds (maximum) HEAT SHOCK 225°C JACKET ELONGATION 150% (minimum) TENSILE STRENGTH 1200 lbf/in ² (minimum) JACKET FLAWS SPARK TEST 1.0 kV (rms) IMPULSE TEST 6.0 kV (peak) JACKET THICKNESS .030 inch (nominal) LOW TEMPERATURE-COLD BEND -30°C/5.00 inch mandrel VOLTAGE WITHSTAND (DIELECTRIC) 1500 volts (rms) VOLTAGE WITHSTAND (Post Environmental) 1000 volts (rms), 1 minute
Designate outer jacket color with a dash number in accordance with MIL-STD-681. Unless otherwise specified, outer jacket color will be black (designated by a "-0" appended to the part number, e.g. 7724C3864-0). Other codes and suffixes may be added to the part number, as necessary, to capture any additional requirements imposed by the purchase order.		WEIGHT 29.6 lbs/1000 ft. (nominal)
		ENGINEERING REFERENCE
		TEMPERATURE RATING 105°C (maximum)
Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice. Tyco Electronics Corporation also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.		
Page 1 of 1	Zerohal, Cheminox, Raychem, TE Connectivity, TE connectivity (logo), and TE (logo) are trademarks.	



Raychem Wire & Cable
501 Oakside Avenue
Redwood City, California 94063-3800
Phone: 1-800-227-8816

THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN. REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.

© 2007-2022 TE Connectivity Corporation. All rights reserved.