



PRODUCT NUMBER	DESCRIPTION
10123196-200LXXX	STRAIGHT BOOT

PRODUCT NUMBER DESCRIPTION:




10123196-200LXXX

LENGTH
XXX= METERS
EXAMPLE:005 = 5 METERS (DIM "L")
100 = 100 METERS (DIM "L")
L=LOW SMOKE ZERO HALOGEN JACKET
S=STANDARD JACKET FIBER (OFNP).
0=STRAIGHT BOOT EXIT
1=RIGHT ANGLE BOOT EXIT
TYPE OF FIBER
2=OM2(LENGTH UP TO 20M)
3=OM3(LENGTH LONGER THAN 20M)



spec ref	-	dr	Sun Shine	2013/01/15	projection	mm	size	A3	scale	1:3
tolerance std	ISO 406 ISO 1101	eng	Sun Shine	2014/01/06	chr	-	ecn no	ELX-N-16563-1	rel level	Released
surface	ISO 1302	appr	Wei-Zhong Hu	2014/01/06	product family	-	rel level	Released	rev	F
linear	0.X ±0.3 0.XX ±0.10 0.XXX ±0.005	angular	0° ±2°	www.fci.com	cat. no.	-	Product - Customer Drw	sheet 1 of 3	dwg no	10123196


PRODUCT NUMBER	DESCRIPTION
10123196-201LXXX	RIGHT ANGLE BOOT



spec ref	-	dr	Sun Shine	2013/01/15	projection	mm	size	A3	scale	1:3
tolerance std	ISO 406 ISO 1101	eng	Sun Shine	2014/01/06	chr	-	ecn no	ELX-N-16563-1	rel level	Released
surface	ISO 1302	appr	Wei-Zhong Hu	2014/01/06	product family	-	rel level	Released	rev	F
linear	0.X ±0.3 0.XX ±0.10 0.XXX ±0.005	www.fci.com	cat. no.	-	Product - Customer Drw	sheet 2 of 3	dwg no	10123196	rev	F
angular	0° ±2°									



Copyright FCI.




VIEW A-A
PIN ASSIGNMENTS

EDGE CONNECTOR PAD DESCRIPTION			
POSITION	SYMBOL	POSITION	SYMBOL
D9	GROUND	B9	GROUND
D8	Tx2-	B8	Rx2-
D7	Tx2+	B7	Rx2+
D6	GROUND	B6	GROUND
D5	Tx0-	B5	Rx0-
D4	Tx0+	B4	Rx0+
D3	GROUND	B3	GROUND
D2	Vman	B2	ModPrs l
D1	Vact	B1	Vact
C1	SCL	A1	Reserved
C2	SDA	A2	Int l
C3	GROUND	A3	GROUND
C4	Tx1+	A4	Rx1+
C5	Tx1-	A5	Rx1-
C6	GROUND	A6	GROUND
C7	Tx3+	A7	Rx3+
C8	Tx3-	A8	Rx3-
C9	GROUND	A9	GROUND

NOTES:

- ①. MATERIAL:
COVERS : ZINC ALLOY/ COPPER UNDERPLATE/ NICKEL OVERPLATE
PULL TAB: THERMOPLASTIC POLYMER
LATCH : STAINLESS STEEL
EMI SKIRT: STAINLESS STEEL
STRAIN RELIEF BOOT : THERMOPLASTIC
PADDLE CARD: PRINTED CIRCUIT SUBSTRATE-FR4
DUST COVER : POLY ETHYLENE
2. THIS PRODUCT MEETS THE RESTRICTION OF HAZARDOUS SUBSTANCES IN ELECTRICAL AND ELECTRONIC EQUIPMENT (RoHS).DIRECTIVE 2002/95/EC.
3. THIS DIMENSION IS A FINISHED PRODUCT LENGTH.
4. A "△" SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW, OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION. THE CURRENT REVISION WILL BE SHOWN IN THE SYMBOL.
5. REFERENCE TO PRODUCT SPECIFICATION GS-12-1122

spec ref		-		dr	Sun Shine	2013/01/15			size	A3	scale	1:3
tolerance std ISO 406 ISO 1101	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Sun Shine	2014/01/06			ecn no	ELX-N-16563-1		
				chr	-	-			rel levelReleased			
				appr	Wei-Zhong Hu	2014/01/06						product family
surface ISO 1302	linear	0.X	±0.3		title	MINISAS HD AOC			dwg no	10123196		rev F
		0.XX	±0.10									
		0.XXX	±0.005									
	angular	0°	±2°	www.fci.com	cat. no.	-	Product - Customer Drw			sheet 3 of 3		