



106DCN2R7M

High pulse power, extends battery life

Parts are RoHS compliant

APPLICATIONS: Battery backup, Battery alternative, LED displays, Mechanical actuators

ELECTRICAL SPECIFICATIONS

Capacitance: 10 F

Temperature Range: -40°C to +60°C

ESR (AC): 80 milliOhms Max at 20°C and 1 kHz

ESR (DC): 130 milliOhms Max at 20°C and DC

Tolerance: -20 % , +20 %

WVDC: 2.7 Volts DC

SVDC: 2.8 Volts DC

Weight: 3.01 grams

Volume: 2.356 ml

Maximum Stored Energy: 10.125 mWH

Maximum Current: 5.87 Amps (1 second discharge to 1/2 the rated voltage)

Operating Current: 1.4 Amps (5 sec discharge to 1/2 rated voltage)

Leakage Current: 0.03 mA after 72 hours

Specific Energy:

Specific Power:

Gravimetric Density: 3.3638 Wh/kg

Gravimetric Density: 2.2356 kW/kg

Volumetric Density: 4.2972 Wh/l

Volumetric Density: 2.856 kW/l

Load Life: 1000 hours at 60°C with 100% of rated voltage applied

Max Capacitance Change: ≤30% of initially measured value

ESR Change: ≤200% of maximum specified value

PHYSICAL DIMENSIONS

Diameter (D): 10 mm, +/- 0.5 mm

Length (L): 30 mm, +/- 2 mm

Height (H): mm, +/- mm


Thickness (T): mm, +/- mm

Termination Finish: Matte Tin

Lead Spacing (S): 5 mm, +/-0.5 mm

Lead Diameter (d): 0.6 mm, +/-0.05 mm

Lead Length (LL): 15mm, +/- Min mm



3757 W. Touhy Ave. Lincolnwood, IL 60712 (847) 675-1760 FAX (847) 673-2850
Illinois Capacitor (HK) Ltd., Tel: 85227930931, Fax: 85227930731, www.illcap.com.hk
© Copyright 2019 Illinois Capacitor. An affiliate of Cornell Dubilier, All Rights Reserved