







THIS INFORMATION IS CONFIDENTIAL AND IS DISCLOSED TO YOU ON CONDITION THAT NO FURTHER DISCLOSURE IS MADE BY YOU TO OTHER THAN AMP PERSONNEL WITHOUT WRITTEN AUTHORIZATION FROM AMP (TAIWAN) LTD. DIMENSIONS IN MILLIMETERS. DO NOT SCALE PRINT.

PRINT DIST
DW



METRIC




NUMBER
C-1734383




RECOMMENDED P.C.B. LAYOUT (1) (THICKNESS=1.6mm)
(GENERAL TOLERANCE: ±0.05)



DETAIL A



RECOMMENDED P.C.B. LAYOUT (2) (THICKNESS=1.6mm)
(GENERAL TOLERANCE: ±0.05)



RECOMMENDED USB CABLE

- NOTE:
- MATERIAL:
 - ①② HOUSING: THERMOPLASTIC W/ 30% G/F UL 94V-0 ; COLOR: BLACK.
 - THERMOPLASTIC HIGH TEMP. W/ 30% G/F UL 94V-0 ; COLOR: BLACK.
 - ③ CONTACT: PHOSPHOR BRONZE
 - ④ FRONT SHIELD: BRASS
 - ⑤ REAR SHIELD: BRASS
 - ⑥ GROUND FINGER: BRASS
 - FINISH:
 - CONTACT : (SEE TABLE) GOLD PLATED IN CONTACT AREA. 150μ"~250μ" TIN ON SOLDER TAILS, 50μ" MIN NICKEL UNDERPLATED ALL OVER.
 - FRONT SHIELD: 100μ" MIN. TIN PLATED ON ENTIRE 50μ" MIN. NICKEL UNDERPLATE OVER ALL.
 - REAR SHIELD: 120μ" MIN. NICKEL PLATED.
 - GROUND FINGER: 100μ" MIN. TIN PLATED ON ENTIRE 50μ" MIN. NICKEL UNDERPLATE OVER ALL. 100μ" MIN. NICKEL UNDERPLATE OVER ALL.
- REFLOW SOLDER CAPABLE TO 260°C PER TYCO SPEC. 109-201, CONDITION B.
- WAVE SOLDER CAPABLE TO 265°C PER TYCO SPEC. 109-202, CONDITION B.

	W/O			30μ"	3-1734383-2
	W/			30μ"	1-1734383-2
	W/			15μ"	1-1734383-1
				30μ"	1734383-2
	W/			15μ"	1734383-1
				30μ"	1734383-1
SOLDERING PROCESS	FRONT SPRING	GROUND FINGER	HOUSING MATERIAL	MIN. GOLD THICKNESS	PART NUMBER


TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.25 2 PLC ±0.20 3 PLC ± ANGLES ±3°	DWN S. HOU 29-JUN-2005	TYCO HOLDINGS (BERMUDA) VII LTD. TAIWAN BRANCH			
	CHK W.J. KE 29-JUN-2005				
MATERIAL SEE NOTE	APVD J. WU 29-JUN-2005	NAME RECEPTACLE ASS'Y, FOURFOLD STACKED, THRU-HOLE, RIGHT ANGLE, USB.			
	PRODUCT SPEC 108-57391				
FINISH SEE NOTE	QUALIFICATION TEST REPORT 501-57423	LOC DW	SIZE A ₃	DRAWING NO C-1734383	REV A
	WEIGHT 18 GRAM	SCALE --	SHEET 1 OF 2		

A	REVISED PACKING	ECR-05-005728	SH WK 29JUN 2005	
O	FIRST RELEASED	FZ00-0204-04	SH WK 17SEP 2004	
LTR	REVISION RECORD	ECN	DWN CHK DATE	

CUSTOMER DRAWING

THIS INFORMATION IS CONFIDENTIAL AND IS DISCLOSED TO YOU ON CONDITION THAT NO FURTHER DISCLOSURE IS MADE BY YOU TO OTHER THAN AMP PERSONNEL WITHOUT WRITTEN AUTHORIZATION FROM AMP (TAIWAN) LTD.
DIMENSIONS IN MILLIMETERS. DO NOT SCALE PRINT.

PRINT DIST
DW



METRIC

NUMBER

C-1734383

CARTON

AIR CAP

LABEL

COVER TRAY

TRAY

NOTES :

- MATERIAL :
 - TRAY : PS T=0.9
 - SHIPPING CARTON : CORRUGATED FIBERBOARD
- DIMENSION :
 - TRAY : L=443, W=279, H=38
 - SHIPPING CARTON : L=455, W=300, H=194
- QUANTITY :
 - PRIMARY PACKING: 50 PCS/TRAY
 - SECONARY PACKING: 4 TRAYS/CARTON(200PCS)
- WEIGHT :
 - NET WEIGHT : 3.60Kg
 - GROSS WEIGHT : 6.122Kg

LTR	SEE SHEET 1.	ECN	DWN CHK	DATE
	REVISION RECORD			

TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± ANGLES ±3'	DWN	S. HOU 29-JUN-2005				tyco Electronics TYCO HOLDINGS (BERMUDA) VII LTD. TAIWAN BRANCH			
	CHK	W.J. KE 29-JUN-2005							
MATERIAL SEE NOTE	APVD	J. WU 29-JUN-2005				NAME RECEPTACLE ASS'Y, FOURFOLD STACKED, THRU-HOLE, RIGHT ANGLE, USB.			
	PRODUCT SPEC								
FINISH SEE NOTE	APPLICATION SPEC					LOC DW	SIZE A ₃	DRAWING NO C-1734383	REV A
	WEIGHT								
						SCALE --		SHEET 2 OF 2	

CUSTOMER DRAWING