

MATERIAL

Insulator: Glass Filled Polyester UL94V-0
Contacts: Copper Alloy
Shell: Steel, Tin plated

ELECTRICAL

Operation Voltage: 250 V AC(r.m.s.)
Current Rating: 3 A
Contact Resistance: <20mΩ
Insulation Resistance: >5000 MΩ
Dielectric Withstanding Voltage: 1000 VAC/minute
Operating Temperature: -40C° ~ +105C°

RoHS Compliant

Mounting options

Part Number

A-4-40 Jack screws assembled
B-Board Locks
F-Ferrite
G-Grounding Straps
J-4-40 Jack Screws (bulk packed)
R-Riveted 4-40 Jack screws
T-Threaded Inserts

DMR-XXPX-(see options)

of circuits

09, 15, 25, 37


PLATING

1= Full Gold Flash/Nickel (STD)
6= Selective Gold flash/Nickel
7 = Selective 15u" Gold/Nickel
8 = Selective 30u" Gold/Nickel
NON-STD may require MOQ

OST ON-SHORE TECHNOLOGY, INC.

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF ON-SHORE TECHNOLOGY, INC. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF ON-SHORE TECHNOLOGY, INC.

TITLE				DMR Series - Male/Plug, .318 footprint			
PART NO.		DMR-XXPX-XXXX		DWG NO.		DMR-XXPX-XXXX.DWG	
APPROVED		CHECKED	DESIGNED	DRAWN	4050		Tolerance
Billy 2001.10.28		Johnn 2001.10.28	Tony 2001.10.28	Steven 2001.10.28			UNIT: mm/Inches SCALE: NONE REV: A
SHEET: 01/01						.X ±0.30/.012 .XX ±0.20/.010 .XXX ±0.10/.004	



Circuits	Dimension		
	A	B	C
9	25.00(.984)	30.8(1.213)	16.92(.666)
15	33.32(1.312)	39.2(1.543)	25.25(.994)
25	47.04(1.852)	53.1(2.091)	38.96(1.534)
37	63.50(2.500)	69.4(2.732)	55.42(2.182)