

DESCRIPTION	MATERIAL	FINISH
BODY	BRASS	GOLD
SOCKET	Be Cu	GOLD
INSULATION	PTFE	N/A


REVISIONS			
REV	DESCRIPTION	DATE	APPV
B	RECOMMENDED FOOTPRINT REVISED; GOLD & NICKEL FINISH OPTIONS	9/25/09	CJ
C	ADDED NEW TITLE BLOCK; UPDATED RECOMMENDED FOOTPRINT	19-JUL-13	BPM
D	ADDED DIMPLING TO PART; REMOVED FINISH OPTIONS	3-JUN-13	SAH
E	ADDED CONTACT TO STANDOFF DIMENSION; UPDATED NOTE 3	3-MAY-16	SAH
F	UPDATED OUTER BARREL DIMENSION WAS Ø0.200 IS Ø0.212	29-NOV-17	CLL




SIDE VIEW



BACK VIEW



RECOMMENDED FOOTPRINT



0.004
0.000
[0.10
0.00]
CENTER CONTACT TO MOUNTING PLANE STAND-OFF

DETAIL A
SCALE 12 : 1

NOTES: (UNLESS OTHERWISE SPECIFIED)
1. ALL DIMENSIONS ARE IN INCHES [mm].
2. DIMENSIONS APPLY AFTER FINISHING.
3. MANUFACTURE TO BE COMPLIANT WITH EU RoHS DIRECTIVE, USE MATERIALS THAT DO NOT CONTAIN REACH SUBSTANCES OF VERY HIGH CONCERN >1000ppm, AND USE DRC CONFLICT-FREE SOURCED MATERIALS.
4. SAFETY BREAK ALL SHARP CORNERS AND EDGES .02 MAXIMUM.

WARNING: THIS DRAWING CONTAINS PROPRIETARY INFORMATION THAT IS THE SOLE PROPERTY OF LINX TECHNOLOGIES, AND SHALL BE TREATED AS SUCH. NO DISCLOSURE OR REPRODUCTION OF THIS DOCUMENT IS PERMITTED, IN WHOLE OR IN PART, WITHOUT THE EXPRESS WRITTEN PERMISSION OF LINX TECHNOLOGIES OR ITS DESIGNATED AGENTS.

MATERIAL:
INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5.
PROJECTION:
SURFACE FINISH: 32 ANGLES: ±1°
TOLERANCES: .X ±.1 .XX ±.01 .XXX ±.005
FINISH:
DRAWN: B.MURPHY DT: 22-APR-13
ENGR: S.HOGAN DT: 3-JUN-13

TE connectivity

TITLE:
SMA FEMALE PCB MOUNT SURFACE MOUNT

SIZE	DWG. NO.	REV
B	CONSMA001-SMD-G	F

SCALE: 6:1 DO NOT SCALE DRAWING SHEET 1 OF 1

©2023 TE Connectivity. All Rights Reserved.

LDCFDFB_C

Downloaded from Arrow.com.