

15BJ

1500 W Transient voltage suppressor



Product features

- Low profile SMD package
- Excellent clamping capability
- 1500 W peak pulse power capability at 10/1000 μ s waveform
- Typical I_R less than 1 μ A above 11 V
- Fast response time: typically less than 1.0 ps from 0 V to V_{BR} minimum
- High temperature reflow soldering: +260 °C /40 s at terminal
- Plastic package meets UL 94 V-0 flammability rating
- Meets moisture sensitivity level (MSL) level 1
- Terminal: Solder plated leads, solderable per J-STD-002
- For surface mounted applications in order to optimize board space
- UL 497B recognized.
File No. : E198449 Guide QVGQ2

Applications

- Consumer electronics
- Telecommunications
- Computing and servers
- Appliances
- Industrial automation
- Mobile and wearables

Environmental compliance and general specifications



Ordering part number

15BJ 6-0 C A



Family name _____

V_R voltage ("-" indicates decimal point) _____

Bi-/Uni-Directional (Blank=Uni, C=Bi) _____

Voltage tolerance _____

PIN configuration

**EAT•N**

Powering Business Worldwide


Absolute maximum ratings

(+25 °C, RH=45%-75%, unless otherwise noted)

Parameter	Symbol	Value	Unit
Storage operating junction temperature range	T_{STG}/T_J	-55 to +150	°C
Steady state power dissipation at $T_L = +75$ °C	$P_{M(AV)}$	5.0	W
Peak pulse power dissipation on 10/1000 μ s waveform	P_{PP}	1500	W
Maximum instantaneous forward voltage at 50 A for unidirectional	V_F	5.0	V
Peak forward surge current, 8.3 ms single half sine wave ¹	I_{FSM}	200	A


1. Measured on 8.3 ms single half sine wave or equivalent square wave for unidirectional device only, duty cycle = 4 per minute maximum

Mechanical parameters, pad layout- mm



Dimension	Millimeters		Inches	
	Minimum	Maximum	Minimum	Maximum
A	3.90	4.50	0.154	0.177
B	4.65	5.15	0.183	0.203
C	1.85	2.15	0.073	0.085
D	0.60		0.024	
E	5.60	6.00	0.220	0.236
F	2.05	2.35	0.081	0.093
G	0.12	0.28	0.005	0.011
J	2.00		0.079	
K		3.20		0.126
L	2.30		0.091	


Part marking



Packaging information (mm)

Drawing not to scale.

Supplied in tape and reel packaging, 3,000 parts per 13" diameter reel (EIA-481 compliant)



Dimensions	Millimeters	Inches
A0	4.50 ± 0.3	0.177 ± 0.012
B0	6.10 ± 0.3	0.240 ± 0.012
C	330.0	13.0
D0	1.55 ± 0.1	0.061 ± 0.004
E	1.75 ± 0.2	0.069 ± 0.008
E1	13.3 ± 0.3	0.524 ± 0.012
F	5.5 ± 0.2	0.217 ± 0.008
P0	4.00 ± 0.2	0.157 ± 0.008
P1	8.00 ± 0.2	0.315 ± 0.008
P2	2.00 ± 0.2	0.079 ± 0.008
W	12.0 ± 0.2	0.472 ± 0.008
W1	15.7 ± 2.0	0.618 ± 0.079

15BJ

1500 W Transient voltage suppressor


Technical Data 11206
Effective November 2020

Electrical characteristics (+25 °C)


Part number		Marking		V_R	$I_R @ V_R$	$V_{BR} @ I_T$		I_T	$V_C @ I_{PP}$	I_{PP}
Uni-polar	Bi-polar	Uni	Bi	(V)	(μA)	min (V)	max (V)	(mA)	max (V)	(A)
15BJ5-0A	15BJ5-0CA	GDE	BDE	5	300	6.4	7	10	9.2	163
15BJ6-0A	15BJ6-0CA	GDG	BDG	6	250	6.67	7.37	10	10.3	145.6
15BJ6-5A	15BJ6-5CA	GDK	BDK	6.5	150	7.22	7.98	10	11.2	134
15BJ7-0A	15BJ7-0CA	GDM	BDM	7	100	7.78	8.6	10	12	125
15BJ7-5A	15BJ7-5CA	GDP	BDP	7.5	50	8.33	9.21	1	12.9	116.3
15BJ8-0A	15BJ8-0CA	GDR	BDR	8	30	8.89	9.83	1	13.6	110.3
15BJ8-5A	15BJ8-5CA	GDT	BDT	8.5	20	9.44	10.4	1	14.4	104.2
15BJ9-0A	15BJ9-0CA	GDV	BDV	9	10	10	11.1	1	15.4	97.4
15BJ10A	15BJ10CA	GDX	BDX	10	5	11.1	12.3	1	17	88.2
15BJ11A	15BJ11CA	GDZ	BDZ	11	2	12.2	13.5	1	18.2	82.4
15BJ12A	15BJ12CA	GEE	BEE	12	1	13.3	14.7	1	19.9	75.4
15BJ13A	15BJ13CA	GEG	BEG	13	1	14.4	15.9	1	21.5	69.8
15BJ14A	15BJ14CA	GEK	BEK	14	1	15.6	17.2	1	23.2	64.7
15BJ15A	15BJ15CA	GEM	BEM	15	1	16.7	18.5	1	24.4	61.5
15BJ16A	15BJ16CA	GEP	BEP	16	1	17.8	19.7	1	26	57.7
15BJ17A	15BJ17CA	GER	BER	17	1	18.9	20.9	1	27.6	54.4
15BJ18A	15BJ18CA	GET	BET	18	1	20	22.1	1	29.2	51.4
15BJ20A	15BJ20CA	GEV	BEV	20	1	22.2	24.5	1	32.4	46.3
15BJ22A	15BJ22CA	GEX	BEX	22	1	24.4	26.9	1	35.5	42.3
15BJ24A	15BJ24CA	GEZ	BEZ	24	1	26.7	29.5	1	38.9	38.6
15BJ26A	15BJ26CA	GFE	BFE	26	1	28.9	31.9	1	42.1	35.6
15BJ28A	15BJ28CA	GFG	BFG	28	1	31.1	34.4	1	45.4	33.1
15BJ30A	15BJ30CA	GFK	BFK	30	1	33.3	36.8	1	48.4	31
15BJ33A	15BJ33CA	GFM	BFM	33	1	36.7	40.6	1	53.3	28.2
15BJ36A	15BJ36CA	GFP	BFP	36	1	40	44.2	1	58.1	25.8
15BJ40A	15BJ40CA	GFR	BFR	40	1	44.4	49.1	1	64.5	23.3
15BJ43A	15BJ43CA	GFT	BFT	43	1	47.8	52.8	1	69.4	21.6
15BJ45A	15BJ45CA	GFV	BFV	45	1	50	55.3	1	72.7	20.6
15BJ48A	15BJ48CA	GFX	BFX	48	1	53.3	58.9	1	77.4	19.4
15BJ51A	15BJ51CA	GFZ	BFZ	51	1	56.7	62.7	1	82.4	18.2
15BJ54A	15BJ54CA	GGE	BGE	54	1	60	66.3	1	87.1	17.2
15BJ58A	15BJ58CA	GGG	BGG	58	1	64.4	71.2	1	93.6	16.1
15BJ60A	15BJ60CA	GGK	BGK	60	1	66.7	73.7	1	96.8	15.5
15BJ64A	15BJ64CA	GGM	BGM	64	1	71.1	78.6	1	103	14.6
15BJ70A	15BJ70CA	GGP	BGP	70	1	77.8	86	1	113	13.3
15BJ75A	15BJ75CA	GGR	BGR	75	1	83.3	92.1	1	121	12.4
15BJ78A	15BJ78CA	GGT	BGT	78	1	86.7	95.8	1	126	11.9
15BJ85A	15BJ85CA	GGV	BGV	85	1	94.4	104	1	137	11
15BJ90A	15BJ90CA	GGX	BGX	90	1	100	111	1	146	10.3
15BJ100A	15BJ100CA	GGZ	BGZ	100	1	111	123	1	162	9.3
15BJ110A	15BJ110CA	GHE	BHE	110	1	122	135	1	177	8.5
15BJ120A	15BJ120CA	GHG	BHG	120	1	133	147	1	193	7.8
15BJ130A	15BJ130CA	GHK	BHK	130	1	144	159	1	209	7.2
15BJ150A	15BJ150CA	GHM	BHM	150	1	167	185	1	243	6.2
15BJ160A	15BJ160CA	GHP	BHP	160	1	178	197	1	259	5.8
15BJ170A	15BJ170CA	GHR	BHR	170	1	189	209	1	275	5.5
15BJ180A	15BJ180CA	GHT	BHT	180	1	201	222	1	292	5.2
15BJ190A	15BJ190CA	GHU	BHU	190	1	211	234	1	307	4.9
15BJ200A	15BJ200CA	GHV	BHV	200	1	224	247	1	324	4.7
15BJ210A	15BJ210CA	GHX	BHX	210	1	233	258	1	337	4.5
15BJ220A	15BJ220CA	GHZ	BHZ	220	1	246	272	1	356	4.2
15BJ250A	15BJ250CA	GIE	BIE	250	1	279	309	1	405	3.7
15BJ300A	15BJ300CA	GIG	BIG	300	1	335	371	1	486	3.1
15BJ350A	15BJ350CA	GIK	BIK	350	1	391	432	1	567	2.6
15BJ400A	15BJ400CA	GIM	BIM	400	1	447	494	1	648	2.3
15BJ440A	15BJ440CA	GIP	BIP	440	1	492	543	1	713	2.1

Ratings and V-I characteristic curves (+25 °C unless otherwise noted)

V- I curve characteristics (Uni-directional)



V- I curve characteristics (Bi-directional)



Surge waveform: 10/1000 μ s

V_R : Stand-off voltage – Maximum voltage that can be applied

V_{BR} : Breakdown voltage


V_C : Clamping voltage – Peak voltage measured across the suppressor at a specified I_{PP}

I_R : Reverse leakage current


I_T : Test current

V_F : Forward voltage drop for Uni-directional TVS diode

Pulse waveform



Pulse derating curve



Solder reflow profile



Table 1 - Standard SnPb solder (T_C)

Package thickness	Volume mm^3 <350	Volume mm^3 ≥ 350
<2.5 mm	235 °C	220 °C
≥ 2.5 mm	220 °C	220 °C

Table 2 - Lead (Pb) free solder (T_C)

Package thickness	Volume mm^3 <350	Volume mm^3 350 - 2000	Volume mm^3 >2000
<1.6 mm	260 °C	260 °C	260 °C
1.6 – 2.5 mm	260 °C	250 °C	245 °C
>2.5 mm	250 °C	245 °C	245 °C

Reference J-STD-020

Profile feature	Standard SnPb solder	Lead (Pb) free solder
Preheat and soak		
• Temperature min. (T_{smin})	100 °C	150 °C
• Temperature max. (T_{smax})	150 °C	200 °C
• Time (T_{smin} to T_{smax}) (t_s)	60-120 seconds	60-180 seconds
Ramp up rate T_L to T_p	3 °C/ second max.	3 °C/ second max.
Liquidous temperature (T_L)	183 °C	217 °C
Time (t_L) maintained above T_L	60-150 seconds	60-150 seconds
Peak package body temperature (T_p)*	Table 1	Table 2
Time (t_p)* within 5 °C of the specified classification temperature (T_C)	20 seconds*	40 seconds*
Ramp-down rate (T_p to T_L)	6 °C/ second max.	6 °C/ second max.
Time 25 °C to peak temperature	6 minutes max.	8 minutes max.

* Tolerance for peak profile temperature (T_p) is defined as a supplier minimum and a user maximum.

Life Support Policy: Eaton does not authorize the use of any of its products for use in life support devices or systems without the express written approval of an officer of the Company. Life support systems are devices which support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin.

Eaton
Electronics Division
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com/electronics

© 2020 Eaton
All Rights Reserved
Printed in USA
Publication No. 11206 BU-MC20184
November 2020

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

