

## Han 1HC-M-TC800 with retaining ring



Image is for illustration purposes only. Please refer to product description.

Part number	97 00 000 0070
Specification	Han 1HC-M-TC800 with retaining ring
HARTING eCatalogue	<a href="https://harting.com/97000000070">https://harting.com/97000000070</a>

### Identification

Category	Inserts
Series	Han <sup>®</sup> HC Modular
Identification	800

### Version

Termination method	Crimp termination
Gender	Male
Details	Please ensure to hold up the contact with a wrench size 24 to apply the tightening torque Please order crimp contacts separately.
Details	The vibration and shock resistance can only be met if the cables are fixed at an appropriate distance. Instructions for the spacing of strain relief can be found in the document in eCatalogue under the section Instructions.

### Technical characteristics

Conductor cross-section (mm <sup>2</sup> )	95 ... 185 mm <sup>2</sup>
Rated current	800 A
Rated voltage	3,600 V
Pollution degree	3
Insulation resistance	>10 <sup>10</sup> Ω
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500
Vibration resistance	Category 1B acc. to IEC 61373



Pushing Performance  
Since 1945

## Technical characteristics

Shock resistance	Category 1B acc. to IEC 61373
------------------	-------------------------------

## Material properties

Material (insert)	Polyamide (PA) Polycarbonate (PC)
Colour (insert)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

## Specifications and approvals

Specifications	EN 45545-2 Fire protection on railway vehicles
----------------	--

## Commercial data

Packaging size	1
Net weight	104.444 g
Country of origin	China
European customs tariff number	85389099
eCl@ss	27440205 Contact insert for industrial connectors
UNSPSC 24.0	39121522