



Part Number : [MK-352-051-335-410S](#)

Product Description : AirBorn M Series, Micro-D Board Mount Plug, 0.050" (1.27mm) Pitch, Right-Angle, Through Hole, Narrow Footprint, with Mounting Holes, Aluminum Shell, 0.140" Tail Length, Tin/Lead Alloy Termination Plating, Turning Jackscrews, 51 Circuits

Status : Active

Product Category : I/O Connectors



Documents and Resources

Specifications

[M Series Micro-D Materials Specification](#)

[Performance Specification](#)

[PC Board Layout - Standard Polarization \(009 - 37 Contacts\)](#)

[PC Board Layout - Standard Polarization \(51 - 100 Contacts\)](#)

[Hardware Details](#)

[Hardware Keying Chart](#)

[Contact Type, Positions, and Polarization](#)

[Hardware Details \(page 2\)](#)

[Hardware Details \(page 3\)](#)

[Dimensional Information](#)

[Part Number Buildup](#)

Part Details

General

Status	Active
Category	I/O Connectors
Description	AirBorn M Series, Micro-D Board Mount Plug, 0.050" (1.27mm) Pitch, Right-Angle, Through Hole, Narrow Footprint, with Mounting Holes, Aluminum Shell, 0.140" Tail Length, Tin/Lead Alloy

	Termination Plating, Turning Jackscrews, 51 Circuits
Application	Wire-to-Board
Component Type	Plug
Contact Type	Pin
Product Name	AirBorn M Series

Electrical

Current - Maximum per Contact	3.0A
Data Rate	3.0 Gbps
Voltage - Maximum	600V

Physical

Circuits Detail	Pin, Right Angle, PCB Leads, .140"
Circuits (Loaded)	51
Circuits (maximum)	51
Durability (mating cycles max)	500
Gender	Male
Keying to Mating Part	None
Lock to Mating Part	Yes
Locking Type	Two Turning Jackscrews, Allen Head, Retaining Ring
Material - Insulator	Polyphenylene Sulfide
Material - Metal	Beryllium Copper
Material - Plating Mating	Gold
Material - Plating Termination	Tin/Lead Alloy (Not RoHS Compliant)
Material - Shell	Aluminum Alloy
Mounting Style	With Mounting Holes
Number of Rows	3
Orientation	Right Angle
Packaging Type	Tray, Embossed Tape on Reel
Panel Mount	No
PC Tail Length	0.140"
Pitch - Mating Interface	0.050" (1.27mm)
Pitch - Termination Interface	0.050" (1.27mm)

Plating min - Mating	50μ"
Plating - Shell	Electroless Nickel
Polarized to Mating Part	Yes
Temperature Range - Operating	-55° to +125°C
Termination Interface Style	Through Hole

Mates With / Use With

Mates with Part(s)

Description
<u>Vertical Surface Mount PCB Connector (RECEPTACLE)</u>
<u>Vertical Plated Thru Hole PCB Metal Connector with Mounting Holes and a Narrow Footprint (RECEPTACLE)</u>
<u>Vertical Plated Thru Hole PCB Metal Connector (RECEPTACLE)</u>
<u>Micro-D, Metal, Board Mount, Right Angle Receptacle, Narrow Footprint</u>
<u>Micro-D, Metal, Board Mount, Right Angle Receptacle</u>
<u>Rear Panel Mount Vertical Plated Thru Hole PCB Connector (RECEPTACLE)</u>
<u>Micro-D, Metal, Rear Panel Mount, Board Mount, Right Angle Receptacle</u>
<u>Micro-D, Metal, Board Mount, Card Edge Receptacle</u>
<u>Micro-D, Metal, Board Mount, Right Angle Receptacle, Compressed Footprint</u>
<u>Micro-D, Metal, Board Mount, Right Angle Receptacle, Narrow Footprint, Blind Clearance Cut</u>
<u>Micro-D, Plastic, Board Mount, Vertical Receptacle, Narrow Footprint</u>
<u>Micro-D, Plastic, Board Mount, Vertical Receptacle</u>
<u>Micro-D, Plastic, Board Mount, Right Angle Receptacle, Narrow Footprint</u>
<u>Micro-D, Plastic, Board Mount, Right Angle Receptacle</u>
<u>Micro-D, Metal, Sealed Rear Panel Mount, Cable Mount Receptacle, Interfacial Seal</u>
<u>Micro-D, Metal, Cable Mount Receptacle</u>
<u>Micro-D, Metal, Rear Panel Mount, Cable Mount Receptacle, Interfacial Seal</u>
<u>Micro-D, Metal, Jumper Cable</u>

<u>Micro-D, Metal, Cable Mount Receptacle, Integrated Shield Termination</u>
<u>Micro-D, Metal, Cable Mount Receptacle, Integrated Shield Termination</u>
<u>Micro-D, Plastic, Cable Mount Receptacle</u>
<u>Micro-D, Plastic, Jumper Cable</u>

This document was generated on Mar 02, 2026