

DELPHI Connection Systems

Catalog

Customer Service

Comparison List (0)

Samples Request

Find by Feature

Browse by Category

Browse by Application

Share

12066271

Search

Enter part number or keyword

Search Results (1)

Search

Options

- 1 Result(s): [All] - 12066271
- ☐

Compare
- 12066271 - Metri-Pack 280 Series Male

☐ Unsealed Tin Plating Tang Terminal,
Cable Range 0.35 - 0.50 mm2

☐

Compare

Metri-Pack 280 Series Male Unsealed Tin Plating Tang
Terminal, Cable Range 0.35 - 0.50 mm2

Part # 12066271



Question about this product?

Attributes	
Documents (2)	
Part # :	12066271
Part # :	12066271
Part # :	12066271
Part # :	✔ 12066271
Part # :	12066271
Part # :	12066271
Part # :	12066271
Part # :	12066271
Part # :	12066271
Part # :	12066271
Part # :	12066271
Part # :	12066271
Part # :	12066271
Part # :	12066271
Part # :	12066271
Description :	Metri-Pack 280 Series Male Unsealed Tin Plating Tang Terminal, Cable Range 0.35 - 0.50 mm2
Description :	Metri-Pack 280 Series Male Unsealed Tin Plating Tang Terminal, Cable Range 0.35 - 0.50 mm2
Description :	Metri-Pack 280 Series Male Unsealed Tin Plating Tang Terminal, Cable Range 0.35 - 0.50 mm2
Description :	✔ Metri-Pack 280 Series Male Unsealed Tin Plating Tang Terminal, Cable Range 0.35 - 0.50 mm2
Description :	Metri-Pack 280 Series Male Unsealed Tin Plating Tang Terminal, Cable Range 0.35 - 0.50 mm2
Description :	Metri-Pack 280 Series Male Unsealed Tin Plating Tang Terminal, Cable Range 0.35 - 0.50 mm2
Description :	Metri-Pack 280 Series Male Unsealed Tin Plating Tang Terminal, Cable Range 0.35 - 0.50 mm2
Description :	Metri-Pack 280 Series Male Unsealed Tin Plating Tang Terminal, Cable Range 0.35 - 0.50 mm2

Description :	Metri-Pack 280 Series Male Unsealed Tin Plating Tang Terminal, Cable Range 0.35 - 0.50 mm2
Description :	Metri-Pack 280 Series Male Unsealed Tin Plating Tang Terminal, Cable Range 0.35 - 0.50 mm2
Description :	Metri-Pack 280 Series Male Unsealed Tin Plating Tang Terminal, Cable Range 0.35 - 0.50 mm2
Description :	Metri-Pack 280 Series Male Unsealed Tin Plating Tang Terminal, Cable Range 0.35 - 0.50 mm2
Description :	Metri-Pack 280 Series Male Unsealed Tin Plating Tang Terminal, Cable Range 0.35 - 0.50 mm2
Description :	Metri-Pack 280 Series Male Unsealed Tin Plating Tang Terminal, Cable Range 0.35 - 0.50 mm2
Description :	Metri-Pack 280 Series Male Unsealed Tin Plating Tang Terminal, Cable Range 0.35 - 0.50 mm2
Description :	Metri-Pack 280 Series Male Unsealed Tin Plating Tang Terminal, Cable Range 0.35 - 0.50 mm2
Product Type :	Terminal
Product Type :	Terminal
Product Type :	Terminal
Product Type :	✔ Terminal
Product Type :	Terminal
Product Type :	Terminal
Product Type :	Terminal
Product Type :	Terminal
Product Type :	Terminal
Product Type :	Terminal
Product Type :	Terminal
Product Type :	Terminal
Product Type :	Terminal
Product Type :	Terminal
Product Type :	Terminal
Product Type :	Terminal
Status :	Active
Status :	Active
Status :	Active
Status :	✔ Active
Status :	Active
Status :	Active
Status :	Active
Status :	Active
Status :	Active
Status :	Active
Status :	Active
Status :	Active
Status :	Active
Status :	Active
Status :	Active
Status :	Active
Status :	Active
Blade size [mm] :	2.8
Blade size [mm] :	2.8
Blade size [mm] :	2.8

Blade size [mm] :	 2.8
Blade size [mm] :	2.8
Blade size [mm] :	2.8
Blade size [mm] :	2.8
Blade size [mm] :	2.8
Blade size [mm] :	2.8
Blade size [mm] :	2.8
Blade size [mm] :	2.8
Blade size [mm] :	2.8
Blade size [mm] :	2.8
Blade size [mm] :	2.8
Blade size [mm] :	2.8
Blade size [mm] :	2.8
Blade size [mm] :	2.8
Terminal Family :	M/P
Terminal Family :	M/P
Terminal Family :	M/P
Terminal Family :	 M/P
Terminal Family :	M/P
Terminal Family :	M/P
Terminal Family :	M/P
Terminal Family :	M/P
Terminal Family :	M/P
Terminal Family :	M/P
Terminal Family :	M/P
Terminal Family :	M/P
Terminal Family :	M/P
Terminal Family :	M/P
Terminal Family :	M/P
Terminal Family :	M/P
Terminal Family :	M/P
Terminal Family :	M/P
Series :	280
Series :	280
Series :	280
Series :	 280
Series :	280
Series :	280
Series :	280
Series :	280
Series :	280
Series :	280
Series :	280
Series :	280
Series :	280
Series :	280
Series :	280
Series :	280
Series :	280
Gender :	Male
Gender :	Male

Gender :	Male
Gender :	 Male
Gender :	Male
Gender :	Male
Gender :	Male
Gender :	Male
Gender :	Male
Gender :	Male
Gender :	Male
Gender :	Male
Gender :	Male
Gender :	Male
Gender :	Male
Gender :	Male
Gender :	Male
Gender :	Male
Sealable :	Unsealed
Sealable :	Unsealed
Sealable :	Unsealed
Sealable :	 Unsealed
Sealable :	Unsealed
Sealable :	Unsealed
Sealable :	Unsealed
Sealable :	Unsealed
Sealable :	Unsealed
Sealable :	Unsealed
Sealable :	Unsealed
Sealable :	Unsealed
Sealable :	Unsealed
Sealable :	Unsealed
Sealable :	Unsealed
Sealable :	Unsealed
Sealable :	Unsealed
Material :	CuSn3Zn9
Material :	CuSn3Zn9
Material :	CuSn3Zn9
Material :	 CuSn3Zn9
Material :	CuSn3Zn9
Material :	CuSn3Zn9
Material :	CuSn3Zn9
Material :	CuSn3Zn9
Material :	CuSn3Zn9
Material :	CuSn3Zn9
Material :	CuSn3Zn9
Material :	CuSn3Zn9
Material :	CuSn3Zn9
Material :	CuSn3Zn9
Material :	CuSn3Zn9
Material :	CuSn3Zn9
Weight [g] :	1
Weight [g] :	1

Weight [g] :	1
Weight [g] :	 1
Weight [g] :	1
Weight [g] :	1
Weight [g] :	1
Weight [g] :	1
Weight [g] :	1
Weight [g] :	1
Weight [g] :	1
Weight [g] :	1
Weight [g] :	1
Weight [g] :	1
Weight [g] :	1
Weight [g] :	1
Weight [g] :	1
Plating :	Tin
Plating :	Tin
Plating :	Tin
Plating :	 Tin
Plating :	Tin
Plating :	Tin
Plating :	Tin
Plating :	Tin
Plating :	Tin
Plating :	Tin
Plating :	Tin
Plating :	Tin
Plating :	Tin
Plating :	Tin
Plating :	Tin
Plating :	Tin
Plating :	Tin
Minimum Cable Core Cross Section [mm2] :	0.35
Minimum Cable Core Cross Section [mm2] :	0.35
Minimum Cable Core Cross Section [mm2] :	0.35
Minimum Cable Core Cross Section [mm2] :	 0.35
Minimum Cable Core Cross Section [mm2] :	0.35
Minimum Cable Core Cross Section [mm2] :	0.35
Minimum Cable Core Cross Section [mm2] :	0.35
Minimum Cable Core Cross Section [mm2] :	0.35
Minimum Cable Core Cross Section [mm2] :	0.35
Minimum Cable Core Cross Section [mm2] :	0.35

Temperature Range :	-40 to 125
Temperature Range :	-40 to 125
Temperature Range :	-40 to 125
Temperature Range :	-40 to 125
Temperature Range :	-40 to 125
Voltage Drop :	Less than 3.0
Voltage Drop :	Less than 3.0
Voltage Drop :	Less than 3.0
Voltage Drop :	✔ Less than 3.0
Voltage Drop :	Less than 3.0
Voltage Drop :	Less than 3.0
Voltage Drop :	Less than 3.0
Voltage Drop :	Less than 3.0
Voltage Drop :	Less than 3.0
Voltage Drop :	Less than 3.0
Voltage Drop :	Less than 3.0
Voltage Drop :	Less than 3.0
Voltage Drop :	Less than 3.0
Voltage Drop :	Less than 3.0
Voltage Drop :	Less than 3.0
Voltage Drop :	Less than 3.0
Voltage Drop :	Less than 3.0
Voltage Drop :	Less than 3.0
Voltage Drop :	Less than 3.0
Voltage Drop :	Less than 3.0
RoHs compliant :	✔ Yes
ELV compliant :	✔ Yes

Certain products listed on this website may be subject to restricted usage or distribution or may not be available. For additional information, please contact your local sales office.

