


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
© COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

| REVISIONS | | | | | |
|---|---|---|---|---|---|
| P | LTR | DESCRIPTION | DATE | DWN | APVD |
| | A | INITIAL RELEASE | 30DEC2015 | DL | CW |
| | B | ECR-21-122216 | 09DEC2021 | WQR | CW |
| | | | | | |
| | | | | | |

















H24BP-T6-M
T2071244101-000
DOCKING FRAME FOR HMN INSERTS_FLOATING
6 MODULES





OTHER SPEC REFER TO
PN T2071244101-000




H24BP-T6-F
T2071244201-000
DOCKING FRAME FOR HMN INSERTS_FIXED
6 MODULES

NOTES:
1. TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
FLAMMABILITY: UL94V-0
MATING CYCLES: 500

注释：
1. 技术参数：
绝缘材料： PC
阻燃等级： UL94V-0
插拔次数： 500次




PANEL CUT OUT




SPACING OF TWO PANELS
AT CLOSE STATUS

| | |
|---|---|
| T2071244201-000 | H24BP-T6-F<br>DOCKING FRAME FOR HMN INSERTS_FIXED<br>HMN塑胶框架_固定端 |
| T2071244101-000 | H24BP-T6-M<br>DOCKING FRAME FOR HMN INSERTS_FLOATING<br>HMN塑胶框架_浮动端 |
| PART NUMBER<br>料 号 | PART DESCRIPTION<br>描 述 |

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±-
2 PLC ±-
3 PLC ±-
4 PLC ±-
ANGLES ±-

MATERIAL -
FINISH -

DWN DAVID LI 30DEC2015
CHK CHRIS WANG 30DEC2015
APVD XU XIANG 30DEC2015
PRODUCT SPEC 108-137168
APPLICATION SPEC 114-137168
WEIGHT -

TE Connectivity

NAME H24BP-T6-M/F
DOCKING FRAME FOR HMN INSERTS
6 MODULES

| SIZE | CAGE CODE | DRAWING NO | RESTRICTED TO |
|---|---|---|---|
| A2 | - | C-T2071244X01000 | - |

CUSTOMER DRAWING | SCALE 4:5 | SHEET 1 OF 1 | REV B

1471-9 (3/13)

Downloaded from Arrow.com.